

1		2		3		4		5	
					TECHNICAL CHARACTERISTICS				
					MATERIAL INSULATOR MATERIAL: PET (WHITE) SUPPORT TAPE: PET (BLUE) CONTACT MATERIAL: COPPER CONTACT PLATING: TIN QUALITY CLASS: 20 MATING CYCLES MIN. PITCH: 1.00 MM				
					ENVIRONMENTAL OPERATING TEMPERATURE: -30°C UP TO 85°C HEAT RESISTANCE: 105°C x 95 HRS FLAMMABILITY RATING UL SUB.758 MOISTURE RESISTANCE: 40°C, 95% RH x 96 HRS COMPLIANCE: LEAD FREE AND ROHS				
					ELECTRICAL CURRENT RATING: 1.0 A MAX WORKING VOLTAGE: 60V INSULATION RESISTANCE: >1000 MOHM/M (500 VDC) DIELECTRIC STRENGTH: 500 VAC/MN NO BREAKDOWN CONDUCTOR RESISTANCE: <0.33 OHM/M CONTACT RESISTANCE: <20 mOHMS				
					STANDARD UL CERTIFIED: E328849				
					MECHANICAL ELONGATION OF INSULATOR: > 60 % TENSIL STRENGTH OF INSULATION: >3.5KG/MM² FLEXING TEST: 180° >20 TIMES ABRASION: >10000 TIMES PULL/OUT: >20 TIMES				
					PACKAGING BAG				
					DIMENSION & TOLERANCE W= (N+1) x P Pt=(N-1) x P				