



RECOMMENDED CABLE
STRIPPING DIM'S



REV.	DATE	ECR NO.	DESCRIPTION
NC	02/17/98	—	INITIAL RELEASE
A	01/05/06	—	UPDATE DRAWING FORMAT
B	03/24/09	—	SEPERATE BODY AND SHELL

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
8					DRAWN	GRS	03/24/09											
7					CHECKED													
6					ISSUED				PART DESCRIPTION UHF SOLDER PLUG (FOR RG-8/U, RG-213/U CABLE)									
5	CONTACT PIN	BRASS	SILVER		1	SHEET	1 OF 1											
3	INSULATOR	P.T.F.E.	NATURAL	1					PART NO. 182120									
2	BODY	BRASS	SILVER	1														
1	SHELL	BRASS	SILVER	1														
DESCRIPTION				MATERIAL	FINISH	QTY	CAD FILE C:/182/182120.DWG		DWG. NO.		182120.DWG		REV.	B	SIZE	A	SCALE	NA