



2.5W USB Adapter with Interchangeable Plugs PSC03R Adapter Meets CEC and EISA Requirements



Features

- USB Socket
- Field Changeable AC Plugs
- ECOC Compliance
- Low Leakage Current
- UL 94 Vo Flammability
- Efficiency Level IV Compliance

Applications

- Wireless Communications
- Portable Equipment
- Peripherals
- Networking

Safety Approvals

- cUL/UL
- C-Tick
- SAA

Mechanical Characteristics

- Length: 75.32mm (2.97in)
- Height: 31.67mm (1.25in)
- Width: 45.96mm (1.81in)
- Weight: 61.1g (2.16oz)

Output Specifications

Model ⁽¹⁾	DC Output Voltage	Load		Ripple ⁽²⁾ P-P (max.)	Regulation Line & Load	Efficiency Level ⁽³⁾
		Min.	Max.			
PSC03R-050	5V	0A	0.5A	55mV	±5%	IV

(1) Minimum order quantity of 4000 pieces

(2) Measured after 10 minutes warm up at 25°C with 12-inch twisted pair terminated with a 10uF capacitor and 0.1uF ceramic in parallel.

(3) Level IV efficient products do not qualify for CE marking and therefore cannot be sold to countries in the EU

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

Input:**AC Input Voltage Rating**

100 to 240V AC

AC Input Voltage Range

90 to 264V AC

AC Input Frequency

47 to 63Hz

Input Current

0.15A (RMS) 115V AC at maximum load

0.08A (RMS) 230V AC at maximum load

Leakage Current

0.02mA maximum at 254V AC, 50Hz

Inrush Current

30A for 120V AC at maximum load

50A for 240V AC at maximum load

(Cold start at ambient 25°C)

Input Power Saving

0.3W maximum, no load

Output:**Efficiency**

63% average; meets CEC level IV

Hold-up Time

10mS minimum, at maximum load at 120V AC

Over-Voltage Protection

8V DC maximum

Over-Current Protection

0.75A maximum

Short-Circuit Protection

Output can be shorted permanently without damage

Environmental:**Temperature**

Operation

0 to +45°C

Non-operation

-40 to +85°C

Humidity

10 to 95% Non condensing

Emissions

FCC Part 15 Class B

EN55022 Class B

Immunity

EN61000-4-2

EN61000-4-3

EN61000-4-4

EN61000-4-5

EN61000-4-6

EN61000-4-8

EN61000-4-11

Dielectric Withstand (Hi-pot) Test

Primary to Secondary: 3000V AC for 1 min., 10mA

DC Output Connector

USB Type A, receptacle, single.

Dimension Diagram Unit: mm (inch)