

Actuating element															
WO								Domed plunger							
RB								Roller plunger							
KB								Roller arm							
HB								Lever arm							
AV								Hinged actuator							
AL								Hinged actuator							
AG								Hinged actuator							
AK								Hinged actuator							
								Connection							
								M							
								SM4							
								Thread M16x1.5 for cable glands							
								Plug connector M12 4-pin							
								Housing							
								Short							
								Long							
								Switching element							
								One contact							
								1 NC ⊖							
								Two contacts							
								1 NC ⊖ + 1 NO ⊕							
								2 NC ⊖							
								Three contacts							
								2 NC ⊖ + 1 NO ⊕							
								3 NC ⊖							
Actuating element								Connection		Housing					

Safety switch NM..WO with domed plunger



Approach direction




Vertical

Switching elements

- ▶ **ES01** Slow-action switching element
1 NC $\ominus$
- ▶ **ES11** Slow-action switching element
1 NC $\ominus$ + 1 NO
- ▶ **ES02** Slow-action switching element
2 NC $\ominus$
- ▶ **ES12** Slow-action switching element
2 NC $\ominus$ + 1 NO
- ▶ **ES03** Slow-action switching element
3 NC $\ominus$


Cable entry M16 x 1.5
Short housing

Dimension drawing





For cable glands see page 104

Cable entry M16 x 1.5
Long housing



For cable glands see page 104

Wiring diagrams Switch not actuated



Ordering table

Series	Actuator	Connection	Housing	Switching element	Order No. / Item
NM	WO Domed plunger	Cable entry 1 x M16 x 1.5	Short 	01 1 NC $\ominus$	084495 NM01WOK-M
				11 1 NC $\ominus$ + 1 NO	095375 NM11WOK-MC2069
				02 2 NC $\ominus$	095374 NM02WOK-MC2069
		Cable entry 3 x M16 x 1.5	Long 	11 1 NC $\ominus$ + 1 NO	084496 NM11WOK-M
				02 2 NC $\ominus$	084497 NM02WOK-M
				12 2 NC $\ominus$ + 1 NO	084498 NM12WOK-M
				03 3 NC $\ominus$	084499 NM03WOK-M

Safety switch NM..RB with roller plunger



Approach direction




Horizontal
Can be adjusted in 90° steps.

Switching elements

- ▶ **ES01** Slow-action switching element
1 NC $\ominus$
- ▶ **ES11** Slow-action switching element
1 NC $\ominus$ + 1 NO
- ▶ **ES02** Slow-action switching element
2 NC $\ominus$
- ▶ **ES12** Slow-action switching element
2 NC $\ominus$ + 1 NO
- ▶ **ES03** Slow-action switching element
3 NC $\ominus$


Cable entry M16 x 1.5
Short housing

Dimension drawing





For cable glands see page 104

Cable entry M16 x 1.5
Long housing



For cable glands see page 104

Wiring diagrams



Ordering table

Series	Actuator	Connection	Housing	Switching element	Order No. / Item
NM	RB Roller plunger	Cable entry 1 x M16 x 1.5	Short 	01 1 NC 	084515 NM01RBA-M
				11 1 NC  + 1 NO	095373 NM11RBA-MC2069
				02 2 NC 	095372 NM02RBA-MC2069
		Cable entry 3 x M16 x 1.5	Long 	11 1 NC  + 1 NO	084516 NM11RBA-M
				02 2 NC 	084517 NM02RBA-M
				12 2 NC  + 1 NO	084518 NM12RBA-M
				03 3 NC 	084519 NM03RBA-M

Safety switch NM..KB with roller arm



Approach direction



Horizontal


Can be adjusted in 90° steps.

Switching elements

- ▶ **ES01** Slow-action switching element
1 NC $\ominus$
- ▶ **ES11** Slow-action switching element
1 NC $\ominus$ + 1 NO
- ▶ **ES02** Slow-action switching element
2 NC $\ominus$
- ▶ **ES12** Slow-action switching element
2 NC $\ominus$ + 1 NO
- ▶ **ES03** Slow-action switching element
3 NC $\ominus$


Cable entry M16 x 1.5
Short housing

Dimension drawing




For cable glands see page 104


Wiring diagrams



Cable entry M16 x 1.5
Long housing



For cable glands see page 104



Ordering table

Series	Actuator	Connection	Housing	Switching element	Order No. / Item
NM	KB Roller arm	Cable entry 1 x M16 x 1.5	Short 	01 1 NC $\ominus$	084522 NM01KBA-M
				11 1 NC $\ominus$ + 1 NO	095371 NM11KBA-MC2069
				02 2 NC $\ominus$	095370 NM02KBA-MC2069
		Cable entry 3 x M16 x 1.5	Long 	11 1 NC $\ominus$ + 1 NO	084523 NM11KBA-M
				02 2 NC $\ominus$	084524 NM02KBA-M
				12 2 NC $\ominus$ + 1 NO	084525 NM12KBA-M
				03 3 NC $\ominus$	084526 NM03KBA-M

Safety switch NM..HB with lever arm



Approach direction




Horizontal
Can be adjusted in 90° steps.

Switching elements

- ▶ **ES01** Slow-action switching element
1 NC ⊖
- ▶ **ES11** Slow-action switching element
1 NC ⊖ + 1 NO
- ▶ **ES02** Slow-action switching element
2 NC ⊖
- ▶ **ES12** Slow-action switching element
2 NC ⊖ + 1 NO
- ▶ **ES03** Slow-action switching element
3 NC ⊖


Cable entry M16 x 1.5 Short housing

Dimension drawing





For cable glands see page 104

Cable entry M16 x 1.5 Long housing



For cable glands see page 104

Wiring diagrams Switch not actuated



Ordering table

Series	Actuator	Connection	Housing	Switching element	Order No. / Item
NM	HB Lever arm	Cable entry 1 x M16 x 1.5		01 1 NC ⊖	084527 NM01HBA-M
				11 1 NC ⊖ + 1 NO	095369 NM11HBA-MC2069
				02 2 NC ⊖	095368 NM02HBA-MC2069
				11 1 NC ⊖ + 1 NO	084528 NM11HBA-M
		Cable entry 3 x M16 x 1.5		02 2 NC ⊖	084529 NM02HBA-M
				12 2 NC ⊖ + 1 NO	084530 NM12HBA-M
				03 3 NC ⊖	084531 NM03HBA-M

Safety switch NM..AV / NM..AL



- ▶ Hinged actuator as solid shaft
- ▶ Shaft length 75 mm or 110 mm

Cable entry M16 x 1.5
Short housing

Cable entry M16 x 1.5
Long housing


Plug connector M12
4-pin, long housing




Switching elements

- ▶ **ES01** Slow-action switching element 1 NC ⊖
- ▶ **ES11** Slow-action switching element 1 NC ⊖ + 1 NO
- ▶ **ES02** Slow-action switching element 2 NC ⊖
- ▶ **ES12** Slow-action switching element 2 NC ⊖ + 1 NO
- ▶ **ES03** Slow-action switching element 3 NC ⊖


Dimension drawing



For cable glands see page 104






For cable glands see page 104



For plug connectors see page 99

Wiring diagrams Switch not actuated



Ordering table

Series	Actuator	Connection	Housing	Switching element	Order No. / Item
NM	AV Hinged actuator solid shaft length 75 mm	Cable entry 1 x M16 x 1.5	Short	01 1 NC ⊖	084545 NM01AV-M
				11 1 NC ⊖ + 1 NO	095367 NM11AV-MC2069
				02 2 NC ⊖	095366 NM02AV-MC2069
		Cable entry 3 x M16 x 1.5	Long	11 1 NC ⊖ + 1 NO	084546 NM11AV-M
				02 2 NC ⊖	084547 NM02AV-M
				12 2 NC ⊖ + 1 NO	084548 NM12AV-M
	AL Hinged actuator solid shaft length 110 mm	Cable entry 1 x M16 x 1.5	Short	03 3 NC ⊖	084549 NM03AV-M
				01 1 NC ⊖	079117 NM01AL-M
				11 1 NC ⊖ + 1 NO	095365 NM11AL-MC2069
		Cable entry 3 x M16 x 1.5	Long	02 2 NC ⊖	095364 NM02AL-MC2069
				11 1 NC ⊖ + 1 NO	079118 NM11AL-M
				02 2 NC	079119 NM02AL-M
	Plug connector M12		Long	12 2 NC ⊖ + 1 NO	079120 NM12AL-M
				03 3 NC ⊖	079121 NM03AL-M
				02 2 NC ⊖	093246 NM02AL-SM4

Safety switch NM..AG


- ▶ Hinged actuator as hollow shaft
- ▶ Internal diameter 10.2 mm




Switching elements

- ▶ **ES01** Slow-action switching element 1 NC ⊖
- ▶ **ES11** Slow-action switching element 1 NC ⊖ + 1 NO
- ▶ **ES02** Slow-action switching element 2 NC ⊖
- ▶ **ES12** Slow-action switching element 2 NC ⊖ + 1 NO
- ▶ **ES03** Slow-action switching element 3 NC ⊖


Cable entry M16 x 1.5 Short housing




Cable entry M16 x 1.5 Long housing



Plug connector M12 4-pin, long housing



Wiring diagrams Switch not actuated



Ordering table

Series	Actuator	Connection	Housing	Switching element	Order No. / Item
NM	AG Hinged actuator hollow shaft ∅ 10.2 mm	Cable entry 1 x M16 x 1.5	Short	01 1 NC ⊖	084553 NM01AG-M
				11 1 NC ⊖ + 1 NO	095361 NM11AG-MC2069
				02 2 NC ⊖	095360 NM02AG-MC2069
		Cable entry 3 x M16 x 1.5	Long	11 1 NC ⊖ + 1 NO	084554 NM11AG-M
				02 2 NC ⊖	084555 NM02AG-M
				12 2 NC ⊖ + 1 NO	084556 NM12AG-M
				03 3 NC ⊖	084557 NM03AG-M
		Plug connector M12	Long	02 2 NC ⊖	084565 NM02AG-SM4

Safety switch NM..AK

- ▶ Hinged actuator as hollow shaft
- ▶ Internal diameter 8.2 mm




Switching elements

- ▶ **ES01** Slow-action switching element
1 NC $\ominus$
- ▶ **ES11** Slow-action switching element
1 NC $\ominus$ + 1 NO
- ▶ **ES02** Slow-action switching element
2 NC $\ominus$
- ▶ **ES12** Slow-action switching element
2 NC $\ominus$ + 1 NO
- ▶ **ES03** Slow-action switching element
3 NC $\ominus$


Cable entry M16 x 1.5
Short housing

Dimension drawing





For cable glands see page 104

Cable entry M16 x 1.5
Long housing



For cable glands see page 104

Wiring diagrams Switch not actuated



Ordering table

Series	Actuator	Connection	Housing	Switching element	Order No. / Item
NM	AK Hinged actuator hollow shaft Ø 8.2 mm	Cable entry 1 x M16 x 1.5	Short	01 1 NC $\ominus$	084559 NM01AK-M
				11 1 NC $\ominus$ + 1 NO	095363 NM11AK-MC2069
				02 2 NC $\ominus$	095362 NM02AK-MC2069
		Cable entry 3 x M16 x 1.5	Long	11 1 NC $\ominus$ + 1 NO	084560 NM11AK-M
				02 2 NC $\ominus$	084561 NM02AK-M
				12 2 NC $\ominus$ + 1 NO	084562 NM12AK-M
				03 3 NC $\ominus$	084563 NM03AK-M

Safety switch NM...



The technical data on switches and switching elements apply to all connections. Further technical data are given for the connection selected.

Reliability values acc. to EN ISO 13849-1

Parameter	Value	Unit
B10d	2 x 10 ⁷ operating cycles	

Switch



Parameter	Value	Unit						
Housing material	Reinforced thermoplastic							
Mechanical life	<table border="1"> <tr> <th>WO/RB</th><th>KB/HB</th><th>AV/AL/AG/AK</th></tr> <tr> <td>30 x 10⁶</td><td>20 x 10⁶</td><td>> 4 x 10⁶</td></tr> </table>	WO/RB	KB/HB	AV/AL/AG/AK	30 x 10 ⁶	20 x 10 ⁶	> 4 x 10 ⁶	Operating cycles
WO/RB	KB/HB	AV/AL/AG/AK						
30 x 10 ⁶	20 x 10 ⁶	> 4 x 10 ⁶						
Weight	approx. 0.1	kg						
Actuator material	Plastic; hinged actuators steel (stainless)							
Approach speed, max.	60	m/min						
Actuating force	15	N						

Switching element



Parameter	Value				Unit
Switching principle	Slow-action switching element				
Switching elements with 1 switching element	ES01 1 NC 				
Switching elements with 2 switching elements	ES11 1 NC  + 1 NO	ES02 2 NC 	ES12 2 NC  + 1 NO	ES03 3 NC 	
Switching current, min., at DC 24 V	1				mA
Switching voltage, min.	12				V
Contact material	Silver alloy, gold flashed				

Connection, cable entry M16 x 1.5



Parameter		Value	Unit
Ambient temperature		- 20 ... + 80	°C
Connection		Screw terminal	
Version		M16 x 1.5	
Conductor cross-section		0.34 ... 1.5	mm²
Degree of protection according to IEC 60529		IP 67	
Rated insulation voltage U _i		250	V AC/DC
Rated impulse withstand voltage U _{imp}		2.5	kV
Conventional thermal current I _{th}		4	A
Short circuit protection according to IEC 60269-1 (control circuit fuse)		4	A gG
Utilization category to IEC 60947-5-1	AC-15	I _e 4 A U _e 230 V	
	DC-13	I _e 4 A U _e 24 V	


Connection, plug connector SM 4 (M12)




Parameter		Value	Unit
Ambient temperature		- 20 ... + 60	°C
Connection		Plug connector	
Version		M12 (4-pin)	
Degree of protection according to IEC 60529		IP 67 ¹⁾	
Rated insulation voltage U _i		250	V AC/DC
Rated impulse withstand voltage U _{imp}		2.3	kV
Conventional thermal current I _{th}		1.5	A
Short circuit protection according to IEC 60269-1 (control circuit fuse)		4	A gG
Utilization category to IEC 60947-5-1	AC-15	I _e 4 A U _e 230 V	
	DC-13	I _e 4 A U _e 24 V	

1) Screwed tight with the related plug connector (see page 99)


Travel diagram NM.WO/NM.RB



Travel diagram NM.KB



Travel diagram NM.HB



Travel diagram NM.AV/NM.AL/NM.AG/NM.AK

