





This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

PRODUCT NUMBER
85854-YYY OR 85854-YYYY
85854-YYLFF OR 85854-YYLFF



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date		0.X ± 0.3	COPY		www.fciconnect.com	
DE	V06-0492	DCH	2006-05-23	linear	0.XX ± 0.13	projection		title	METRAL SIGNAL HEADER
DF	DG07-0487	Cen	12/05/07		.XXX ± .051				4 MOD, 5 ROW PRESS-FIT
DG	DG09-0344	TER	2009-11-10	angles	0° ± 2°			product family	METRAL
-	-	-	-	dr	T.BRUNGARD 11/19/99	MIM		size	213
DB	V04-0353	DAI	05/04/04	enr	M.STRAWER 11/19/99			dwg no	85854
DC	V04-0560	HTB	06/01/04	chr	M.STRAWER 11/19/99	scale	2:1	sheet	1 of 20
DD	V04-1100	DAI	01/26/05	appd	M.STRAWER 02/29/00				
sheet	revision	DG	...	DG					
index	sheet	I	...	20					




This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

1 | 2

3 |

4

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
11	6.50	17.00
16	7.00	4.30
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00
25	5.75	15.60
39	8.00	14.40
44	5.75	12.10
49	5.75	15.10
52	8.00	15.10
54	5.00	11.50

A

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3			COPY		title	METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT		
DG					0.XX ±0.13			projection					
					.XXX ±.051								
				angles	0° ±2°					product family	METRAL		code
				dr	T.BRUNGARD	11/19/99		MM ←————→ scale			size	dwg no	213
				enrg	M.STRAWSER	11/19/99							
				chr	M.STRAWSER	11/19/99							
				appd	M.STRAWSER	02/29/00		1:1		A	85854	sheet	2
sheet	revision												
index	sheet												

B

1 | 2

Pro/E

3 |

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X01 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X02 SEE NOTE 10 LEAD FREE OPTION	E	19	3	19	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19
	D	3	19	19	19	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3
	C	19	3	19	19	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3
	B	3	19	19	19	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3
	A	19	19	19	19	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3	19	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X03 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	19	19	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X04 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	
85854-X05 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	
	C	19	19	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X06 SEE NOTE 10 LEAD FREE OPTION	E	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
	D	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X07 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	C	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	B	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X08 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	19	19	19
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	www.fciconnect.com	
DG					0.XX ±0.13			title	
					.XXX ±.051			METRAL SIGNAL HEADER	
				angles	0° ±2°	MIM	scale	product family	
				dr	T.BRUNGARD 11/19/99			METRAL	
				engr	M.STRAWSE 11/19/99			code	
				chr	M.STRAWSE 11/19/99	1:1	A	size	
				appd	M.STRAWSE 02/29/00			dwg no	
sheet	revision							85854	
index	sheet							213	
								sheet	
								3	

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X09 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	4	4	19	19
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X10 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
	B	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X11 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8
	B	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X12 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	1	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	1
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ±0.3	projection 	COPY	www.fciconnect.com	
DG					0.XX ±0.13			title	
					.XXX ±.051			METRAL SIGNAL HEADER	
					angles 0° ±2°			4 MOD, 5 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99		scale 1:1	product family	
				enrg	M.STRAWSE 11/19/99			METRAL	
				chr	M.STRAWSE 11/19/99			size	dwg no
				appd	M.STRAWSE 02/29/00			A	85854
sheet index	revision sheet								code
									213
									sheet 4

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X17 SEE NOTE 10 LEAD FREE OPTION	E	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	1
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3	1
	A	3	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	3	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X18 SEE NOTE 10 LEAD FREE OPTION	E	6	7	6	7	6	7	6	7	6	7	6	7	6	6	6	6	6	7	6	7	6	7	6	7
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X19 SEE NOTE 10 LEAD FREE OPTION	E	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19	19	19
	D	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19	19	19
	C	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19	19	19
	B	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19	19	19
	A	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X20 SEE NOTE 10 LEAD FREE OPTION	E	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49
	D	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49
	C	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49
	B	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49
	A	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49	49

mat'l code				tolerances unless otherwise specified				CUSTOMER		 www.fciconnect.com						
lfr	ecn no.	dr	date	linear	0.X ±0.3				COPY		title					
DG					0.XX ±0.13				projection		METRAL SIGNAL HEADER					
					.XXX ±.051						4 MOD, 5 ROW PRESS-FIT					
				angles	0° ±2°					scale	product family		METRAL	code		
				dr	T.BRUNGARD 11/19/99						size	dwg no		213		
				engr	M.STRAWSE 11/19/99						85854		sheet	5		
				chr	M.STRAWSE 11/19/99				1:1	A						
				appd	M.STRAWSE 02/29/00											
sheet index	revision sheet										cage code		22526			

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X25 SEE NOTE 10 LEAD FREE OPTION	E	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	C	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	A	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X26 SEE NOTE 10 LEAD FREE OPTION	E	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	2	2	2
	C	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	2	2	2
	A	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X27 SEE NOTE 10 LEAD FREE OPTION	E	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	6	6	6	6	6
	C	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	6	6	6	6
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	6	6	6	6	6
	A	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X28 SEE NOTE 10 LEAD FREE OPTION	E	9	11	10	10	10	10	10	10	10	10	10	9	11	10	10	10	10	10	10	10	10	11	11	9
	D	9	11	10	10	10	10	10	10	10	10	10	9	11	10	10	10	10	10	10	10	10	11	11	9
	C	9	11	10	10	10	10	10	10	10	10	10	9	11	10	10	10	10	10	10	10	10	11	11	9
	B	9	11	10	10	10	10	10	10	10	10	10	9	11	10	10	10	10	10	10	10	10	11	11	9
	A	1	3	2	2	2	2	2	2	2	2	2	1	3	2	2	2	2	2	2	2	2	3	3	3

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	www.fciconnect.com	
DG					0.XX ±0.13			title	
					.XXX ±.051			METRAL SIGNAL HEADER	
					angles 0° ±2°			4 MOD, 5 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99	MIM	scale	product family	
				engr	M.STRAWER 11/19/99			METRAL	
				chr	M.STRAWER 11/19/99			size	code
				appd	M.STRAWER 02/29/00			dwg no	213
sheet	revision							85854	sheet
index	sheet							6	

cage code				22526				4			
-----------	--	--	--	-------	--	--	--	---	--	--	--

Pro/E

3

A

B

1 | 2

3

4

1 | 2

3

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A



B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X33 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	3	3	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3	2	2
	C	3	3	3	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3	3	2
	B	2	2	2	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3	3	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X34 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	19	3	3	3	3	3	3	3	3	19	3	3	3	3	3	3	4
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4
	C	3	3	3	3	3	3	3	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4
	B	3	19	3	3	19	3	3	3	19	3	19	3	19	3	3	3	3	3	3	3	3	3	3	4
	A	3	3	3	3	3	3	3	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X35 SEE NOTE 10 LEAD FREE OPTION	E	4	4	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	3	19	19
	D	4	4	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	3	19	19
	C	4	4	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	3	19	19
	B	4	4	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	3	19	19
	A	4	4	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	3	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X36 SEE NOTE 10 LEAD FREE OPTION	E	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54
	D	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54
	C	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54
	B	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54
	A	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
litr	ecn no.	dr	date	linear	0.X ±0.3		COPY			title	
DG					0.XX ±0.13		projection			METRAL SIGNAL HEADER	
					.XXX ±.051					4 MOD, 5 ROW PRESS-FIT	
				angles	0° ±2°					product family	
				dr	T.BRUNGARD 11/19/99		MM			METRAL	
				engr	11/19/99		MM			code	
				chr	M.STRAWER 11/19/99		scale			213	
				appd	M.STRAWER 02/29/00		1:1		A		sheet
sheet index		revision sheet									7

A

B

1 | 2

Pro/E

3 |

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X49 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X50 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	D	3	1	1	1	1	1	1	1	1	1	1	1	3	1	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	3	1	1	1	1	1	1	1	1	1	1	1	3	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X51 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	4	4	4	4	4	4	4	4	4	4	4	1	1	1	1	1	1	1	4	4	4	4	4	4
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X52 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2
	D	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2
	C	1	1	2	2	2	2	1	1	2	2	2	2	1	1	2	2	2	2	1	1	2	2	2	2
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

3																											
METRAL P/N			CONTACT MOD. 1						MOD. 2						MOD. 3						MOD. 4						
		ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	
85854-X53 SEE NOTE 10 LEAD FREE OPTION		E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	
		D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	
		C	1	1	1	2	2	2	1	1	2	2	2	2	1	1	2	2	2	2	1	1	2	2	2	2	2
		B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	
		A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X54 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	-	-	-	1
	D	-	1	1	-	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	-	-	-	1
	C	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1
	B	-	-	-	-	1	1	-	1	1	-	1	1	-	-	-	-	1	1	-	1	1	-	1	1
	A	-	1	1	-	-	1	-	1	1	-	1	1	-	1	1	-	-	1	-	1	1	-	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X55 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	3	3	-	-	3	3	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	3	3	-	-	3	3	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	3	3	-	-	3	3	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	3	3	-	-	3	3	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	19	19	-	-	19	19	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X56 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com													
litr	ecn no.	dr	date	linear		0.X ±0.3		COPY				title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT													
DG						0.XX ±0.13		projection																	
						.XXX ±.051																			
						angles 0° ±2°																			
				dr		T.BRUNGARD 11/19/99				product family		METRAL		code											
				engr		M.STRAWSE 11/19/99				size		dwg no		213											
				chr		M.STRAWSE 11/19/99				scale		85854		sheet											
				appd		M.STRAWSE 02/29/00				1:1		A		9											
sheet index		revision sheet																							

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A




B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X57 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	1	1	-	1	1
	D	-	1	1	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	-	-	-	1	1
	C	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1
	B	-	-	-	1	1	-	1	1	-	1	1	-	-	-	1	1	-	1	1	-	1	1	1	1
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	-	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X58 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	-	-	-	-
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X59 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
	D	1	1	1	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	C	1	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
	B	1	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
	A	1	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X60 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	3	2	2	2	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		FCi www.fciconnect.com									
ltr	ecn no.	dr	date	linear	0. X ±0.3			COPY		title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT									
DG					0. XX ±0.13			projection											
					. XXX ±.051														
				angles	0° ±2°					product family METRAL									
				dr	T.BRUNGARD 11/19/99			MM											
				engr	M.STRAWER 11/19/99					213		sheet		10					
				chr	M.STRAWER 11/19/99			scale		A		85854							
				appd	M.STRAWER 02/29/00			1 : 1											
sheet index	revision sheet																		

Pro/E

cage code 22526

B

1 | 2

3 |

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X65 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	1
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X66 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	-	-	-	-	2	2	-	-	-	-	2	2	-	-	-	-	2	2	-	-	-	-	2
	A	2	-	2	-	-	2	2	-	2	-	-	2	2	-	2	-	-	2	2	-	2	-	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X67 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	4	2	2	3	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X68 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	4
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	4
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	4
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	4
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	4

3																									
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X69 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X70 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X71 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5	5	5	5	5	6	5	5	5	5	5	5	5	5	6
	D	5	5	6	5	5	5	5	5	6	5	5	5	5	5	6	5	5	5	5	5	5	5	5	6
	C	5	5	6	5	5	5	5	5	6	5	5	5	5	5	6	5	5	5	5	5	5	5	5	6
	B	5	5	6	5	5	5	5	5	6	5	5	5	5	5	6	5	5	5	5	5	5	5	5	6
	A	5	5	6	5	5	5	5	5	6	5	5	5	5	5	6	5	5	5	5	5	5	5	5	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X72 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	3	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code				- -				tolerances unless otherwise specified				CUSTOMER								www.fciconnect.com					
litr	ecn no.		dr	date	linear	0.X ±0.3				COPY				title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT											
DG						0.XX ±0.13				projection 															
						.XXX ±.051				angles 0° ±2°															
					dr	T.BRUNGARD 11/19/99				 MM scale 1:1				product family METRAL				code 213							
					enrg	M.STRAWER 11/19/99								size A				dwg no 85854				sheet 11			
					chr	M.STRAWER 11/19/99																			
					appd	M.STRAWER 02/29/00																			
sheet index		revision sheet																							

cage code 22526

Pro/E

3

4

[illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X76 SEE NOTE 10 LEAD FREE OPTION	E	4	4	4	4	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	D	1	4	4	4	4	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	1	3
	C	3	4	4	4	4	4	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	3
	B	3	3	3	4	4	4	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	3
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	3	4	4	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X77 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	4	2	2
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	4	2	2	2	
	C	2	-	4	-	2	-	2	-	2	-	2	-	4	-	2	-	2	2	2	4	4	4	
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	4	4	4	4	
	A	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	4	2	2	2	

[illegible][illegible][illegible]

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

[illegible]



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X81 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	D	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	C	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	B	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	A	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X82 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2	2
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	2	2	2	2
	C	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2	2
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	2	2	2	2
	A	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X83 SEE NOTE 10 LEAD FREE OPTION	E	3	19	3	19	3	19	3	19	19	1	1	19	19	19	19	1	19	1	19	19	19	19	19	19
	D	4	19	3	19	3	19	3	19	19	1	1	19	19	4	19	1	19	1	19	19	1	19	1	19
	C	1	19	19	19	19	19	3	19	19	1	1	19	19	19	19	19	1	19	1	19	19	19	19	19
	B	4	19	4	19	1	19	1	19	1	1	19	19	19	1	19	19	19	19	19	19	19	19	19	19
	A	19	1	1	1	1	1	1	1	1	1	19	19	19	19	19	19	1	19	1	1	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X84 SEE NOTE 10 LEAD FREE OPTION	E	4	-	-	-	3	3	4	4	3	4	3	4	4	2	2	2	2	4	4	4	4	2	2	2
	D	4	-	-	-	3	3	4	4	3	4	3	4	4	4	4	4	2	2	4	2	2	4	2	2
	C	4	-	-	-	3	3	4	4	3	4	3	4	4	2	2	4	2	2	4	2	2	4	2	2
	B	4	-	-	-	3	3	4	4	3	4	3	4	4	2	2	4	4	2	4	2	2	4	2	2
	A	4	-	-	-	3	3	4	4	3	4	3	4	4	2	2	4	4	2	4	2	2	4	2	2

3																									
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X85 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
	D	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	C	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
	B	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	A	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X86 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	4
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X87 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	1	3	3	3	3	3	19	19	19	19	19	19	19
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X88 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI			
litr	ecn no.	dr	date	linear	0.X ±0.3				COPY	www.fciconnect.com			
DG					0.XX ±0.13				projection	title			
					.XXX ±.051					METRAL SIGNAL HEADER			
				angles	0° ±2°					4 MOD, 5 ROW PRESS-FIT			
				dr	T.BRUNGARD 11/19/99					product family		METRAL	code
				engr	M.STRAWSE 11/19/99					size	dwg no		213
				chr	M.STRAWSE 11/19/99						85854		sheet
				appd	M.STRAWSE 02/29/00				scale		1:1		13
sheet index	revision sheet												

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X89 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-
	D	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	C	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-
	B	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	A	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X90 SEE NOTE 10 LEAD FREE OPTION	E	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59
	D	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59
	C	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59
	B	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59
	A	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X91 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	8	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	8	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	8	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X92 SEE NOTE 10 LEAD FREE OPTION	E	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7
	D	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7
	C	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7
	B	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7
	A	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7

3																									
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X93 SEE NOTE 10 LEAD FREE OPTION	E	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3
	D	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3
	C	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3
	B	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3
	A	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3	19	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X94 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	20	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X95 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	1	19	1	2	2	1	2	2	2	2	2	2	19	19	2	4	4	2	1
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	19	19	2	4	4	2	1
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	19	19	2	4	4	2	1
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	19	19	2	4	4	2	1
	A	2	2	2	2	2	1	2	1	2	2	2	2	2	2	2	2	2	19	19	2	4	4	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X96 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	19	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com													
litr	ecn no.	dr	date	linear		0.X ±0.3		COPY				title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT													
DG						0.XX ±0.13		projection																	
						.XXX ±.051																			
						angles 0° ±2°																			
				dr		T.BRUNGARD 11/19/99				product family		METRAL		code											
				enrg		M.STRAWER 11/19/99				size		dwg no		213											
				chr		M.STRAWER 11/19/99				scale		85854		sheet											
				appd		M.STRAWER 02/29/00				1:1		A		14											
sheet index		revision sheet																							

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X97 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	2	1	1	2	2	2	2	2	2	2	2	2	2	2	1	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X98 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	2	2	3	1	3	3	2	2	2	3	3	4	2	4	3	4	3	3	3	3
	D	3	3	3	3	2	2	3	1	3	3	2	2	2	3	3	4	2	4	3	4	3	3	3	3
	C	3	3	3	3	2	2	3	1	3	3	1	2	2	3	3	4	4	4	4	4	3	3	3	3
	B	3	3	3	3	2	2	3	1	3	3	2	2	2	3	3	4	2	4	3	4	3	3	3	3
	A	3	3	3	3	2	2	3	1	3	3	2	2	2	3	3	4	2	4	3	4	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X99 SEE NOTE 10 LEAD FREE OPTION	E	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4
	D	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4
	C	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
	B	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4
	A	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X100 SEE NOTE 10 LEAD FREE OPTION	E	3	3	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8
	D	3	3	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8
	C	3	3	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8
	B	3	3	6	8	6	8	6	8	6	8	6	8	6	8	6	8	6	8	6	8	6	8	6	8
	A	3	3	6	8	6	8	6	8	6	8	6	8	6	8	6	8	6	8	6	8	6	8	6	8

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X101 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	2	1	1	2	2	1	1	1	1	2	2	2	2	2	1	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X102 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X103 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5	5	5	5	6	5	6	5	5	5	6	5	6	6	5
	D	5	5	6	5	5	5	5	5	6	5	5	5	5	5	6	6	5	5	5	6	5	5	6	5
	C	5	5	6	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	5	6	5	6	6	5
	B	5	5	6	5	5	5	5	5	6	5	5	5	5	5	5	5	5	5	5	6	5	6	6	5
	A	5	5	6	5	5	5	5	5	6	5	5	5	5	5	5	5	5	5	5	5	6	5	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X104 SEE NOTE 10 LEAD FREE OPTION	E	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	D	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-
	C	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	B	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-
	A	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2

mat'l code				- -				tolerances unless otherwise specified				CUSTOMER				 www.fciconnect.com					
lfr	ecn no.	dr	date	linear	0.X ±0.3				projection 	title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT	product family				METRAL				code 213 sheet 15		
DG					0.XX ±0.13						MM 	size A	dwg no				85854				
					.XXX ±.051								scale 1:1								
				angles	0° ±2°																
				dr	T.BRUNGARD 11/19/99																
				enrg	M.STRAWER 11/19/99																
				chr	M.STRAWER 11/19/99																
				appd	M.STRAWER 02/29/00																
sheet index	revision sheet																				

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X105 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	3	3	3
	C	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	3	3	3	3
	B	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	2	1	3	3	3	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X106 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4
	D	3	3	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4
	C	3	3	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
	B	3	3	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4
	A	3	3	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X107 SEE NOTE 10 LEAD FREE OPTION	E	7	20	7	20	7	20	7	20	20	5	5	20	20	20	20	5	20	5	20	20	20	20	20	20
	D	8	20	7	20	7	20	7	20	20	5	5	20	20	8	20	5	20	5	20	20	5	20	5	20
	C	5	20	20	20	20	20	7	20	20	5	5	20	20	20	20	5	20	5	20	20	20	20	20	20
	B	8	20	8	20	5	20	5	20	5	5	20	20	5	20	20	20	20	20	20	20	20	20	20	20
	A	20	5	5	5	5	5	5	5	5	5	20	20	20	20	20	20	5	20	5	20	5	5	20	20


METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X108 SEE NOTE 10 LEAD FREE OPTION	E	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	D	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-
	C	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	B	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-
	A	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X109 SEE NOTE 10 LEAD FREE OPTION	E	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	D	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-
	C	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	B	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-
	A	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X110 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X111 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X112 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	5	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3		COPY			title	
DG					0.XX ±0.13		projection			METRAL SIGNAL HEADER	
					.XXX ±.051					4 MOD, 5 ROW PRESS-FIT	
					angles		0° ±2°				
					dr		T.BRUNGARD 11/19/99				
				engr	M.STRAWER 11/19/99				product family		
				chr	M.STRAWER 11/19/99				size		
				appd	M.STRAWER 02/29/00				dwg no		
sheet		revision								code	
index		sheet								213	
										sheet	
										16	

Pro/E

cage code 22526

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X113 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X114 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	4	2	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X115 SEE NOTE 10 LEAD FREE OPTION	E	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	D	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	C	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	B	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	A	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X116 SEE NOTE 10 LEAD FREE OPTION	E	2	4	4	2	19	6	6	6	6	2	19	2	2	2	6	6	6	6	6	6	2	1	2	
	D	2	4	4	2	19	6	6	6	6	2	19	2	2	2	6	6	6	6	6	6	2	3	2	
	C	2	4	4	2	19	6	6	6	6	2	19	2	2	2	6	6	6	6	6	6	2	2	2	
	B	2	4	4	2	19	6	6	6	21	6	2	19	2	2	2	6	6	6	6	21	6	2	2	2
	A	2	4	4	2	19	6	6	6	6	2	19	2	2	2	6	6	6	6	6	6	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X117 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	6	6	6	2	6	2	2	2	2	2	2	6	6	6	6	6	2	2	2	2	2
	D	2	2	2	6	6	6	2	6	2	2	2	2	2	2	6	6	6	6	6	2	2	2	2	2
	C	2	2	2	6	6	6	2	6	2	2	2	2	2	2	6	6	6	6	6	2	2	2	2	2
	B	2	2	2	6	6	6	21	6	2	2	2	2	2	2	2	6	6	6	6	21	6	2	2	2
	A	2	2	2	6	6	6	2	6	2	2	2	2	2	2	2	6	6	6	6	6	2	2	2	2

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com			
lfr	ecn no.	dr	date			linear	0.X ±0.3		COPY						
DG							0.XX ±0.13		projection		title		METRAL SIGNAL HEADER		
							.XXX ±.051						4 MOD, 5 ROW PRESS-FIT		
						angles	0° ±2°				product family		METRAL		
						dr	T.BRUNGARD 11/19/99		scale		size		dwg no		
						engr	M.STRAWER 11/19/99		1:1		A		85854		
						chr	M.STRAWER 11/19/99						213		
						appd	M.STRAWER 02/29/00						sheet		
sheet		revision												17	
index		sheet													

A

B

1 | 2

Pro/E

3 |

cage code
22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X123 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	3	3
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X124 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	3	3
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X125 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X126 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X127 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat

lfr

DG

</

mat'l code				tolerances unless otherwise specified		CUSTOMER					
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com			
DG					0.XX ±0.13	projection		title METRAL SIGNAL HEADER			
					.XXX ±.051			4 MOD, 5 ROW PRESS-FIT			
				angles	0° ±2°			product family METRAL			
				dr	T.BRUNGARD 11/19/99	MIM		size	dwg no		
				enrg	M.STRAWER 11/19/99						
				chr	M.STRAWER 11/19/99						
				appd	M.STRAWER 02/29/00	scale		A	85854		
sheet		revision									
index		sheet									



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X133 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	1	1	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	1	1	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X134 SEE NOTE 10 LEAD FREE OPTION	E	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1
	D	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1
	C	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1
	B	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1
	A	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X135 SEE NOTE 10 LEAD FREE OPTION	E	7	7	7	7	7	7	7	7	7	7	7	7	7	7	20	7	7	20	7	7	8	7	20	
	D	7	7	7	7	7	7	7	7	7	7	7	7	7	7	20	7	7	20	7	7	8	7	20	
	C	7	7	7	7	7	7	7	7	7	7	7	7	7	7	20	7	7	20	7	7	8	7	20	
	B	7	7	7	7	7	7	7	7	7	7	7	7	7	7	20	7	7	20	7	7	8	7	20	
	A	7	7	7	7	7	7	7	7	7	7	7	7	7	7	6	6	7	7	20	7	7	8	7	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X136 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	19	3	3	4	3	19	
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	19	3	3	4	3	19	
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	19	3	3	4	3	19	
	B	3	3	3	4	4	4	4	4	4	4	4	4	4	4	19	3	3	19	3	3	4	3	19	
	A	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	3	3	19	3	3	4	3	19	

mat'l code				--		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com	
litr	ecn no.	dr	date	linear	0.X ±0.3		COPY			title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT			
DG					0.XX ±0.13		projection						
					.XXX ±.051								
				angles	0° ±2°					product family		METRAL	code
				dr	T.BRUNGARD	11/19/99				size	dwg no	213	sheet
				enrg	M.STRAWSE	11/19/99							
				chr	M.STRAWSE	11/19/99							
				appd	M.STRAWSE	02/29/00	scale		1:1	A	85854		19
sheet index		revision sheet											

Pro/E

cage code 22526



PRODUCT NUMBER
85854-XXX OR 85854-YYYY
85854-XXYLF OR 85854-XXYYLF


NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:
85854-XXX IS SnPb
85854-XXYLF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE BELOW.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP
- PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.

ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING IN CONTACT AREA		NOTES
DASH NUMBER	PERFORMANCE LEVEL	-
-PYY OR -PYYY	0.25 um GOLD MIN.	-
-NIYY OR -NIYYY	TELCORDIA CO (NXT)	-
-NSYY OR -NSYYY	TELCORDIA UE (NXT)	-
-IYY OR -IYYY	TELCORDIA CO	-
-2YY OR -2YYY	TELECOM CLASS	-
-3YY OR -3YYY	IEC CLASS I	-
-5YY OR -5YYY	TELCORDIA UE	-
-NIYYLF OR -NIYYLFF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 9
-NSYYLF OR -NSYYLFF	TELCORDIA UE (NXT)	SEE NOTE 9
-IYYLF OR -IYYLFF	TELCORDIA CO IEC CLASS I	SEE NOTE 9
-2YYLF OR -2YYLFF	TELECOM CLASS	SEE NOTE 9
-5YYLF OR -5YYLFF	TELCORDIA UE	SEE NOTE 9

10. FOR LEAD FREE PART NUMBERS ADD AN "LF" SUFFIX..
EXAMPLE: 85854-X0ILF

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com						
litr	ecn no.	dr	date	linear	0.X ±0.3		projection	COPY		title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT			product family	METRAL		code		
DG					0.XX ±0.13									MM	size		dwg no	213
					.XXX ±.051													
				angles	0° ±2°													
				dr	T.BRUNGARD 11/19/99													
				enrg	M.STRAWSER 11/19/99													
				chr	M.STRAWSER 11/19/99													
				appd	M.STRAWSER 02/29/00													
sheet	revision																	
index	sheet																	

cage code 22526