





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	18JUN2014	DW	CW
	A1	ECR-15-009407	01JUN2015	DW	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
CONTACT MATERIAL: BRASS
SURFACE PLATING:
SILVER PLATING: >= 2µm
GOLD PLATING: >= 0.75µm
CONTACT RESISTANCE: <=5 mΩ
WIRE RANGE: 0.14-4 mm² (26-12 AWG)
OPERATION TEMPERATURE: -40-+125°C

注释:
1. 技术参数:
母针材料: 黄铜
表面电镀:
镀银: >= 2µm
镀金: >= 0.75µm
接触电阻: <=5 mΩ
接线范围: 0.14-4 mm² (26-12 AWG)
工作温度: -40-+125°C

	PART NUMBER		d1	d2	WIRE GAUGE		STRIPPING LENGTH (mm)	IDENTIFICATION 1 (NUMBER OF GROOVES)	IDENTIFICATION 2 (NUMBER OF GROOVES)
	SILVER PLATING	GOLD PLATING			MM ²	AWG			
SOCKET CONTACT	T2030002002-000	T2030012002-000	0.90	2.50	0.14-0.37	26-22	7.5	1 GROOVE	1 GROOVE
	T2030002005-000	T2030012005-000	1.15	2.50	0.5	20		NO GROOVE	NO GROOVE
	T2030002008-000	T2030012008-000	1.30	2.50	0.75	18		NO GROOVE	1 GROOVE
	T2030002010-000	T2030012010-000	1.45	2.65	1.0	18		1 GROOVE	NO GROOVE
	T2030002015-000	T2030012015-000	1.75	3.00	1.5	16		2 GROOVES	NO GROOVE
	T2030002025-000	T2030012025-000	2.25	3.45	2.5	14		3 GROOVES	NO GROOVE
	T2030002030-000	T2030012030-000	2.55	3.75	3.0	12		1 WIDE GROOVE	1 GROOVE
	T2030002040-000	T2030012040-000	2.85	3.85	4.0	12		NO GROOVE	NO GROOVE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

-

DWN 18JUN2014
David Wang
CHK 18JUN2014
Chris Wang
APVD 18JUN2014
Xiang Xu

PRODUCT SPEC
108-106137
APPLICATION SPEC
114-106137
WEIGHT
-

Customer Drawing

TE Connectivity

NAME
CEF/DEF
HEE SOCKET CONTACT

SIZE
A3

CAGE CODE
00779

DRAWING NO
T20300X20XX000

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
A1