







Specification:


1. Electrical Char

Insulation Resistance: 500MΩ min. 500V DC for 1 minute
Contact Resistance: 20mΩ max.
Rating Current: 1.5A max.
Rating Voltage: 120V AC
Dielectric Voltage: 1000 Vrms at 1mA 60 sec. min.

2. Physical Char

Housing: PBT Glass filled (UL 94V-0) ,Soldering Temperature :235°C for 5 sec.
Nylon (UL-94V-0) Soldering Temperature :260°C for 5 sec.
Color: Black

- ① Spring Wire: 0.45mm Dia Phosphor Bronze
6u" full Gold plating over Nickel
Temperature Range: -40°C to +85°C
Durability: 750 mating cycles min.



PCB LAYOUT
(Top View)

RoHS compliant
Unit: mm

Scale	FREE					Date	Name	Customer-No.		G	
TOLERANCE					Drawn	08.06.2016	Joanna				
X.	±1				Approved	10.03.2025	Winnie	ASSMANN WSW-No.			
.XX	±0.25							A-2004-2-4-LP-N-R			
.XXX	±0.13							Drawing-No.			
.XXXX	±0.05	①	Add the thickness of plating gold	10.03.2025	Winnie				ASS 7273 CO	rev01	H
		②	Drawn	08.06.2016	Joanna						
Angle	TOL	Id.	Modification	Date	Name	A company of 			Replace	Sheet	

ASSMANN
WSW components
A company of **BCS**

ASS 7273 CO rev01