



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	22		B	REV PER ECR-10-018501	9SEP2010	DZ	MQ.W

D


C

B


A



- 1 MATERIAL: HOUSING – PCT POLYESTER, BLACK, IR COMPATIBLE, UL 94V-0.
TERMINALS – .013[0.33] THICK PHOS BRONZE PLATED WITH .000050[1.27μm] MIN THICK HARD GOLD IN LOCALIZED AREA AND .000150[3.81μm] MIN THICK MATTE TIN IN SOLDER AREA OVER .000050 [1.27μm] MIN THICK NICKEL UNDERPLATE.
SHIELD – .010[0.254] THICK COPPER ALLOY PLATED WITH .000050[1.27μm] MIN NICKEL, PCB GROUND TABS DIPPED WITH .000080[2.03μm] MIN TIN.
- 2 JACK CAVITY COMFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
4. ALL DIMENSIONS SHOWN IN BRACKETS [] ARE IN MILLIMETERS.
- 5 THIS HOLE IS REQUIRED FOR 557571-1.



SUGGESTED PC BOARD LAYOUT
(COMPONENT SIDE)
SEE APPLICATION SPECIFICATION

THIS DRAWING IS A CONTROLLED DOCUMENT.		3		3 GROUND TABS		5557571-1	
		NO. OF HOLES		DESCRIPTION		PART NUMBER	
DIMENSIONS: INCHES 		DWN 15JUN2005 G. ATTADIA - DOCK5		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
		CHK 15JUN2005 J. WESTMAN					
		APVD 15JUN2005 S. FLICKINGER		NAME			
		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01[0.25] 3 PLC ± .005[0.13] 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1163		MODULAR JACK ASSEMBLY, 4 PORT, 8 POSITION, RIGHT ANGLE, SHIELDED	
MATERIAL		APPLICATION SPEC 114-2048					
FINISH		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C-5557571	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 1:1	SHEET 1	OF 1	REV B