




ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
EC NO: MF2006-0318		DRWN: L.SADUSKI		2005/11/17		DRAWN BY		DATE		TITLE		SC FIBER CHANNEL DUPLEX CONNECTOR	
CHKD: 2005/11/18		APPR: I.GUMIN		2005/11/18		CHECKED BY		DATE		MOLEX INCORPORATED		SHEET NO.	
REV		DESCRIPTION		ANGULAR $\pm 1/2^\circ$		APPROVED BY		DATE		DOCUMENT NO.		1 OF 02	
A				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		SEE TABLE		SD-106034-XXX0			
						SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
						B							

	13		12		11		10		9		8		7		6		5		4		3		2		1					
J	CONNECTOR P/N	ØD µm	HOUSING COLOR	BOOT COLOR	CONNECTOR TYPE	FIBER OPTIC CABLE SIZE (mm)																				J				
	106034-0000	127 ^{+3.0} _{-0.0}	BEIGE	BEIGE	MULTIMODE	3.0																								
	106034-0900					2.0&1.6 DUPLEX																								
	106034-0100					1.6 SIMPLEX																								
	106034-0070					3.0																								
	106034-0970		BLACK	BLACK		MULTIMODE	2.0&1.6 DUPLEX																							
	106034-0170						1.6 SIMPLEX																							
	106034-0080						3.0																							
	106034-0980						2.0&1.6 DUPLEX																							
	106034-0180		RED	RED			MULTIMODE	1.6 SIMPLEX																						
	106034-2000	3.0																												
	106034-2900	2.0&1.6 DUPLEX																												
	106034-2100	1.6 SIMPLEX																												
	106034-3000	BEIGE	BEIGE	MULTIMODE	3.0																									
	106034-3900				2.0&1.6 DUPLEX																									
	106034-3910				1.6 SIMPLEX																									
	106034-3920				3.0																									
	106034-3100	BLACK	BLACK		MULTIMODE	2.0&1.6 DUPLEX																								
	106034-3070					1.6 SIMPLEX																								
	106034-3970					3.0																								
	106034-3170					2.0&1.6 DUPLEX																								
	106034-3080	RED	RED			MULTIMODE	1.6 SIMPLEX																							
	106034-3980			3.0																										
	106034-3180			2.0&1.6 DUPLEX																										
	106034-5000			1.6 SIMPLEX																										
	106034-5900	BLUE	BLUE	SINGLE MODE			3.0																							
	106034-5100				2.0&1.6 DUPLEX																									
	106034-6000				1.6 SIMPLEX																									
	106034-6900				3.0																									
	106034-6100	125.5 ^{+0.5} _{-0.0}						2.0&1.6 DUPLEX																						
							1.6 SIMPLEX																							
E																											E			
D																											D			
C																											C			
B																										B				
A																										A				
	ENTER DESCRIPTION EC NO.: MF2006-0318 DRAWN: SADAUSKIENE 2005/11/17 CHKD: 2005/11/18 APPR: IGUMIN 2005/11/18																													
	QUALITY SYMBOLS ▽=0 ▽=0																													
	GENERAL TOLERANCES (UNLESS SPECIFIED)																													
																	</													

ENTER DESCRIPTION
EC NO: MF2006-0318
DRAWN: SADAUSKIENE 2005/11/17
CHKD: 2005/11/18
APPR: IGUMIN 2005/11/18
REV
A

QUALITY SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±----	±----
3 PLACES	±----	±----
2 PLACES	±----	±----
1 PLACE	±----	±----

ANGULAR ±1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY	DATE
RPACIFICI	2005/10/04
CHECKED BY	DATE
APPROVED BY	DATE
I.GUMIN	2005/11/15

MATERIAL NO.	DOCUMENT NO.	SHEET NO.
SEE TABLE	SD-106034-XXX0	2 OF 02

DIMENSION STYLE
IN/MM

SCALE
4:1

DESIGN UNITS
INCH

THIRD ANGLE PROJECTION

SC FIBER CHANNEL DUPLEX CONNECTOR

MOLEX

MOLEX INCORPORATED