


UM 45-FLK50/AB-1756

Order No.: 2968357



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2968357>

VARIOFACE COMPACT LINE, interface module for Allen-Bradley
Controll-Logix, with Controll-Logix-specific labeling

Commercial data

GTIN (EAN)	4017918587772
sales group	I631
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.127 KG
Catalog page information	Page 199 (IF-2007)

Product notes

WEEE/RoHS-compliant since:
08/11/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per branch	1 A
Max. total current of voltage supply	2 A (/Byte)

Width	116 mm
Height	50 mm
Depth	45 mm
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Test voltage	500 V (50 Hz, 1 min)
Test voltage contact/contact	0.5 kV AC
Mounting position	Any
Standards/regulations	IEC 60664
	DIN VDE 0109-11
Pollution degree	2
Surge voltage category	II

Connection data

Connection 1	Field level
Type of connection	Screw connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Stripping length	6 mm
Screw thread	M3
Connection 2	Control system level
Number of connections	1
Type of connection	Flat-ribbon cable plug connector in acc. with IEC 60603-13
Number of positions	50

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Circuit diagram



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;