

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6458: USE NEW LOGO	10/12/12	D.FRISIELLO
F	ECN 6485: RETURN TO GLUED VERSION. PRODUCT NOT TOOLED.	10/24/12	D.FRISIELLO
G	ECN 6692: REVISED MODEL FROM GLUED TO SNAP-ON COVERS	2/19/13	D.FRISIELLO

D




C

B

A



USB TYPE "B"
JACK
"J1"



USB TYPE "A"
JACK
"J2"

NOTES:

MATERIAL:

COUPLER HOUSING: ABS, UL94V-0.
CONNECTOR INSULATORS: WHITE, PBT WITH GLASS FIBER.
TYPE "A" CONNECTOR CONTACTS: PHOSPHOR BRONZE.
TYPE "A" CONNECTOR SHELL: BRASS.
TYPE "B" CONNECTOR CONTACTS: PHOSPHOR BRONZE.
TYPE "B" CONNECTOR SHELL FRONT: BRASS.
TYPE "B" CONNECTOR SHELL BACK: STEEL.
PCB: EPOXY GLASS FP-4, 94V-0 FLAMMABILITY RATING.

FINISH:

COUPLER HOUSING: CHROME.
CONNECTOR CONTACTS: GOLD, 30μ INCHES.
CONNECTOR SHELLS: NICKEL.

ELECTRICAL:

CURRENT RATING: 2 AMP MAX.
VOLTAGE RATING: 140 VDC.



ENVIRONMENTAL:

OPERATING TEMPERATURE: -20° C TO +80° C.

MISCELLANEOUS:


COUPLER SHALL BE TESTED FOR CONTINUITY.
COUPLER SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM PACKAGING SPEC PS-0031.

WIRING MAP



RECOMMENDED
PANEL CUTOUT

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	11/12/2003		
	CHECKED BY D.PARHAM	11/12/2003	CATEGORY USB	
	APPROVED BY R. CARRICK	11/12/2003	PRODUCT DESCRIPTION USB B-A PANEL ADPT SHIELDED	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: ECF504-BAS.SLDDRW	REV. G
		DWG. NO. ECF504-BAS		SHEET 1 OF 1