

## 3.3 V FULL-DUPLEX RS-485/RS-422 DRIVERS AND BALANCED RECEIVERS

### FEATURES

- Designed for INTERBUS Applications
- Designed for RS-422 and RS-485 Networks
- Balanced Receiver Thresholds
- 1/2 Unit-Load (up to 64 nodes on the bus)
- Bus-Pin ESD Protection 15 kV HBM
- Bus-Fault Protection of –7 V to 12 V
- Thermal Shutdown Protection
- Power-Up/Down Glitch-free Bus Inputs and Outputs
- High Input Impedance With Low  $V_{CC}$
- Monotonic Outputs During Power Cycling
- 5-V Tolerant Inputs

### APPLICATIONS

- Digital Motor Control
- Utility Meters
- Chassis-to-Chassis Interconnections
- Electronic Security Stations
- Industrial, Process, and Building Automation
- Point-of-Sale (POS) Terminals and Networks
- DTE/DCE Interfaces

### DESCRIPTION


The SN65HVD379 is a differential line driver and differential-input line receiver that operates with a 3.3-V power supply. Each driver and receiver has separate input and output pins for full-duplex bus communication designs. They are designed for balanced transmission lines and interoperation with ANSI TIA/EIA-485A, TIA/EIA-422-B, ITU-T v.11, and ISO 8482:1993 standard-compliant devices.

These differential bus drivers and receivers are monolithic, integrated circuits designed for full-duplex bi-directional data communication on multipoint bus-transmission lines at signaling rates<sup>(1)</sup> up to 25 Mbps. The SN65HVD379 is fully enabled with no external enabling pins.

The 1/2 unit load receiver has a higher receiver input resistance. This results in lower bus leakage currents over the common-mode voltage range, and reduces the total amount of current that an RS-485 driver is forced to source or sink when transmitting.


The balanced differential receiver input threshold makes the SN65HVD379 more compatible with fieldbus requirements that define an external failsafe structure.

- (1) The signaling rate of a line is the number of voltage transitions that are made per second expressed in the units bps (bits per second).



### SN65HVD379

#### D PACKAGE (TOP VIEW)



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### ORDERING INFORMATION

| SIGNALING RATE | UNIT LOADS | PART NUMBER <sup>(1)</sup> | SOIC MARKING |
|----------------|------------|----------------------------|--------------|
| 25 Mbps        | 1/2        | SN65HVD379                 |              |

(1) These are The D package is available taped and reeled. Add an R suffix to the part number (ie. SN65HVD379DR).

### ABSOLUTE MAXIMUM RATINGS

over operating free-air temperature range unless otherwise noted<sup>(1) (2)</sup>

|                      |                                                                                                                | UNIT                              |
|----------------------|----------------------------------------------------------------------------------------------------------------|-----------------------------------|
| $V_{CC}$             | Supply voltage range                                                                                           | –0.3 V to 6 V                     |
| $V_A, V_B, V_Y, V_Z$ | Voltage range at any bus terminal (A, B, Y, Z)                                                                 | –9 V to 14 V                      |
| $V_{TRANS}$          | Voltage input, transient pulse through 100 $\Omega$ . See <a href="#">Figure 8</a> (A, B, Y, Z) <sup>(3)</sup> | –50 to 50 V                       |
| $V_I$                | Input voltage range (D, DE, $\overline{RE}$ )                                                                  | –0.5 V to 7 V                     |
| $P_{CONT}$           | Continuous total power dissipation                                                                             | Internally limited <sup>(4)</sup> |
| $I_O$                | Output current (receiver output only, R)                                                                       | 11 mA                             |

- (1) Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltage values, except differential I/O bus voltages, are with respect to network ground terminal.
- (3) This tests survivability only and the output state of the receiver is not specified.
- (4) The Thermal shutdown protection circuit internally limits the continuous total power dissipation. Thermal shutdown typically occurs when the junction temperature reaches 165°C.

### RECOMMENDED OPERATING CONDITIONS

over operating free-air temperature range unless otherwise noted

| PARAMETER         |                                                         | MIN               | NOM | MAX      | UNIT     |
|-------------------|---------------------------------------------------------|-------------------|-----|----------|----------|
| $V_{CC}$          | Supply voltage                                          | 3                 |     | 3.6      | V        |
| $V_I$ or $V_{IC}$ | Voltage at any bus terminal (separately or common mode) | –7 <sup>(1)</sup> |     | 12       |          |
| $1/t_{UI}$        | Signaling rate                                          |                   |     | 25       | Mbps     |
| $R_L$             | Differential load resistance                            | 54                | 60  |          | $\Omega$ |
| $V_{IH}$          | High-level input voltage                                | 2                 |     | $V_{CC}$ | V        |
| $V_{IL}$          | Low-level input voltage                                 | 0                 |     | 0.8      |          |
| $V_{ID}$          | Differential input voltage                              | –12               |     | 12       |          |
| $I_{OH}$          | High-level output current                               | Driver            |     | –60      | mA       |
|                   |                                                         | Receiver          |     | –8       |          |
| $I_{OL}$          | Low-level output current                                | Driver            |     | 60       | mA       |
|                   |                                                         | Receiver          |     | 8        |          |
| $T_A$             | Ambient still-air temperature                           | –40               |     | 85       | °C       |

(1) The algebraic convention, in which the least positive (most negative) limit is designated as minimum is used in this data sheet.

## ELECTROSTATIC DISCHARGE PROTECTION

| PARAMETER                           | TEST CONDITIONS       | MIN | TYP <sup>(1)</sup> | MAX | UNIT |
|-------------------------------------|-----------------------|-----|--------------------|-----|------|
| Human body model                    | Bus terminals and GND |     | 16                 |     | kV   |
| Human body model <sup>(2)</sup>     | All pins              |     | 4                  |     |      |
| Charged-device-model <sup>(3)</sup> | All pins              |     | 1                  |     |      |

(1) All typical values at 25°C with 3.3-V supply.

(2) Tested in accordance with JEDEC Standard 22, Test Method A114-A.

(3) Tested in accordance with JEDEC Standard 22, Test Method C101.

## DRIVER ELECTRICAL CHARACTERISTICS

over recommended operating conditions unless otherwise noted

| PARAMETER                                                                                           | TEST CONDITIONS                                                                                             | MIN                | TYP <sup>(1)</sup> | MAX                | UNIT    |
|-----------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|--------------------|--------------------|--------------------|---------|
| $V_{I(K)}$ Input clamp voltage                                                                      | $I_I = -18$ mA                                                                                              | -1.5               |                    |                    | V       |
| $ V_{OD(SS)} $ Steady-state differential output voltage                                             | $I_O = 0$                                                                                                   | 2                  |                    | $V_{CC}$           |         |
|                                                                                                     | $R_L = 54 \Omega$ , See <a href="#">Figure 1</a> <sup>(2)</sup> (RS-485)                                    | 1.5                | 2.0                |                    |         |
|                                                                                                     | $R_L = 100 \Omega$ , See <a href="#">Figure 1</a> (RS-422)                                                  | 2                  | 2.3                |                    |         |
|                                                                                                     | $V_{test} = -7$ V to 12 V, See <a href="#">Figure 2</a>                                                     | 1.5                |                    |                    |         |
| $\Delta V_{OD(SS)} $ Change in magnitude of steady-state differential output voltage between states | $R_L = 54 \Omega$ , See <a href="#">Figure 1</a> and <a href="#">Figure 2</a>                               | -0.2               |                    | 0.2                |         |
| $V_{OD(RING)}$ Differential output voltage overshoot and undershoot                                 | $R_L = 54 \Omega$ , $C_L = 50$ pF, See <a href="#">Figure 5</a> ( <a href="#">Figure 3</a> for definitions) |                    |                    | 10% <sup>(3)</sup> |         |
| $V_{OC(PP)}$ Peak-to-peak common-mode output voltage                                                | See <a href="#">Figure 3</a>                                                                                |                    | 0.5                |                    |         |
| $V_{OC(SS)}$ Steady-state common-mode output voltage                                                |                                                                                                             |                    | 1.6                | 2.3                |         |
| $\Delta V_{OC(SS)}$ Change in steady-state common-mode output voltage                               |                                                                                                             | -0.05              |                    | 0.05               |         |
| $I_{Z(Z)}$ or $I_{Y(Z)}$ High-impedance state output current                                        | $V_{CC} = 0$ V, $V_Z$ or $V_Y = 12$ V, Other input at 0 V                                                   |                    |                    | 90                 | $\mu$ A |
|                                                                                                     | $V_{CC} = 0$ V, $V_Z$ or $V_Y = -7$ V, Other input at 0 V                                                   | -10                |                    |                    |         |
| $I_{Z(S)}$ or $I_{Y(S)}$ Short-circuit output current <sup>(4)</sup>                                | $V_Z$ or $V_Y = -7$ V                                                                                       | Other input at 0 V | -250               | 250                | mA      |
|                                                                                                     | $V_Z$ or $V_Y = 12$ V                                                                                       |                    | -250               | 250                |         |
| $I_I$ Input current                                                                                 | D $V_I = 0$ or $V_I = 2.0$                                                                                  | 0                  |                    | 100                | A       |
| $C_{(OD)}$ Differential output capacitance                                                          | $V_{OD} = 0.4 \sin(4E6\pi t) + 0.5$ V, $V_{CC}$ at 0 V                                                      |                    | 16                 |                    | pF      |

(1) All typical values are at 25°C and with a 3.3-V supply.

(2)  $V_{CC}$  is 3.3 Vdc 5%.

(3) 10% of the peak-to-peak differential-output voltage swing, per TIA/EIA-485.

(4) Under some conditions of short-circuit to negative voltages, output currents exceeding the ANSI TIA/EIA-485-A maximum current of 250 mA may occur. Continuous exposure may affect device reliability.

## DRIVER SWITCHING CHARACTERISTICS

over recommended operating conditions unless otherwise noted

| PARAMETER                                                  | TEST CONDITIONS                                                 | MIN | TYP <sup>(1)</sup> | MAX | UNIT |
|------------------------------------------------------------|-----------------------------------------------------------------|-----|--------------------|-----|------|
| $t_{PLH}$ Propagation delay time, low-to-high-level output | $R_L = 54 \Omega$ , $C_L = 50$ pF, See <a href="#">Figure 5</a> | 4   | 10                 | 18  | ns   |
| $t_{PHL}$ Propagation delay time, high-to-low-level output |                                                                 |     |                    |     |      |
| $t_r$ Differential output signal rise time                 |                                                                 | 2.5 | 5                  | 12  | ns   |
| $t_f$ Differential output signal fall time                 |                                                                 |     |                    |     |      |
| $t_{sk(p)}$ Pulse skew ( $ t_{PHL} - t_{PLH} $ )           |                                                                 |     | 0.6                |     | ns   |
| $t_{sk(pp)}$ <sup>(2)</sup> Part-to-part skew              |                                                                 |     | 1                  |     | ns   |

(1) All typical values are at 25°C and with a 3.3-V supply.

(2)  $t_{sk(pp)}$  is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.

## RECEIVER ELECTRICAL CHARACTERISTICS

over recommended operating conditions unless otherwise noted

| PARAMETER                                                                  | TEST CONDITIONS                                                                | MIN                | TYP <sup>(1)</sup> | MAX   | UNIT |
|----------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------|--------------------|-------|------|
| V <sub>IT+</sub> Positive-going differential input threshold voltage       | I <sub>O</sub> = –8 mA                                                         |                    |                    | 0.2   | V    |
| V <sub>IT–</sub> Negative-going differential input threshold voltage       | I <sub>O</sub> = 8 mA                                                          | –0.2               |                    |       |      |
| V <sub>hys</sub> Hysteresis voltage (V <sub>IT+</sub> – V <sub>IT–</sub> ) |                                                                                |                    | 50                 |       | mV   |
| V <sub>O</sub> Output voltage                                              | V <sub>ID</sub> = 200 mV, I <sub>O</sub> = –8 mA, See <a href="#">Figure 7</a> | 2.4                |                    |       | V    |
|                                                                            | V <sub>ID</sub> = –200 mV, I <sub>O</sub> = 8 mA, See <a href="#">Figure 7</a> |                    |                    | 0.4   |      |
| I <sub>A</sub> or I <sub>B</sub> Bus input current                         | V <sub>A</sub> or V <sub>B</sub> = 12 V                                        | Other input at 0 V | 0.20               | 0.35  | mA   |
|                                                                            | V <sub>A</sub> or V <sub>B</sub> = 12 V, V <sub>CC</sub> = 0 V                 |                    | 0.24               | 0.40  |      |
|                                                                            | V <sub>A</sub> or V <sub>B</sub> = –7 V                                        |                    | –0.35              | –0.18 |      |
|                                                                            | V <sub>A</sub> or V <sub>B</sub> = –7 V, V <sub>CC</sub> = 0 V                 |                    | –0.25              | –0.13 |      |
| C <sub>ID</sub> Differential input capacitance                             | V <sub>ID</sub> = 0.4 sin (4E6πt) + 0.5 V, DE at 0 V                           |                    | 15                 |       | pF   |
| I <sub>CC</sub> Supply current                                             | D at 0 V or V <sub>CC</sub> and No Load                                        |                    |                    | 2.1   | mA   |

(1) All typical values are at 25°C and with a 3.3-V supply.

## RECEIVER SWITCHING CHARACTERISTICS

over recommended operating conditions unless otherwise noted

| PARAMETER                                                              | TEST CONDITIONS                                                                         | MIN | TYP <sup>(1)</sup> | MAX | UNIT |
|------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|-----|--------------------|-----|------|
| t <sub>PLH</sub> Propagation delay time, low-to-high-level output      | V <sub>ID</sub> = –1.5 V to 1.5 V, C <sub>L</sub> = 15 pF, See <a href="#">Figure 7</a> |     | 26                 | 45  | ns   |
| t <sub>PHL</sub> Propagation delay time, high-to-low-level output      |                                                                                         |     |                    |     |      |
| t <sub>sk(p)</sub> Pulse skew ( t <sub>PHL</sub> – t <sub>PLH</sub>  ) |                                                                                         |     |                    | 7   |      |
| t <sub>sk(pp)</sub> Part-to-part skew <sup>(2)</sup>                   |                                                                                         |     | 5                  |     |      |
| t <sub>r</sub> Output signal rise time                                 |                                                                                         |     |                    | 5   |      |
| t <sub>f</sub> Output signal fall time                                 |                                                                                         |     |                    | 6   |      |

(1) All typical values are at 25°C and with a 3.3-V supply

(2) t<sub>sk(pp)</sub> is the magnitude of the difference in propagation delay times between any specified terminals of two devices when both devices operate with the same supply voltages, at the same temperature, and have identical packages and test circuits.


## DEVICE POWER DISSIPATION – P<sub>D</sub>

| PARAMETER                               | TEST CONDITIONS                                                                                                                          | MIN | TYP | MAX | UNIT |
|-----------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|-----|-----|-----|------|
| P <sub>D</sub> Device power dissipation | R <sub>L</sub> = 60 Ω, C <sub>L</sub> = 50 pF, Input to D a 50% duty cycle square wave at indicated signaling rate T <sub>A</sub> = 85°C |     |     | 197 | mW   |


## FUNCTION TABLES

| DRIVER |         |   | RECEIVER                                         |         |
|--------|---------|---|--------------------------------------------------|---------|
| INPUT  | OUTPUTS |   | DIFFERENTIAL INPUTS                              | OUTPUTS |
| D      | Y       | Z | V <sub>ID</sub> = V <sub>A</sub> –V <sub>B</sub> | R       |
| H      | H       | L | V <sub>ID</sub> ≤ –0.2 V                         | L       |
| L      | L       | H | –0.2 V < V <sub>ID</sub> < 0.2 V                 | ?       |
| Open   | L       | H | 0.2 V ≤ V <sub>ID</sub>                          | H       |


## PARAMETER MEASUREMENT INFORMATION



**Figure 1. Driver  $V_{OD}$  Test Circuit and Voltage and Current Definitions**




**Figure 2. Driver  $V_{OD}$  With Common-Mode Loading Test Circuit**




### Figure 3. $V_{OD(RING)}$ Waveform and Definitions

$V_{OD(RING)}$  is measured at four points on the output waveform, corresponding to overshoot and undershoot from the  $V_{OD(H)}$  and  $V_{OD(L)}$  steady state values.




Input: PRR = 500 kHz, 50% Duty Cycle,  $t_r < 6$  ns,  $t_f < 6$  ns,  $Z_0 = 50 \Omega$




**Figure 4. Test Circuit and Definitions for the Driver Common-Mode Output Voltage**


## PARAMETER MEASUREMENT INFORMATION (continued)




**Figure 5. Driver Switching Test Circuit and Voltage Waveforms**



**Figure 6. Receiver Voltage and Current Definitions**




**Figure 7. Receiver Switching Test Circuit and Voltage Waveforms**



**Figure 8. Test Circuit, Transient Over Voltage Test**

## EQUIVALENT INPUT AND OUTPUT SCHEMATIC DIAGRAMS



|            | <b>R1/R2</b> | <b>R3</b> |
|------------|--------------|-----------|
| SN65HVD379 | 9 kΩ         | 45 kΩ     |

## TYPICAL CHARACTERISTICS




Figure 9.




Figure 10.




Figure 11.






Figure 12.



## TYPICAL CHARACTERISTICS (continued)


**Figure 13.**

**Figure 14.**

PACKAGING INFORMATION

| Orderable part number | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-----------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| SN65HVD379DR          | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | VP379               |
| SN65HVD379DR.A        | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | VP379               |


- (1) **Status:** For more details on status, see our [product life cycle](#).
- (2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.
- (3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.
- (4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- (5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- (6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


## TAPE AND REEL INFORMATION



\*All dimensions are nominal


| Device       | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN65HVD379DR | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device       | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN65HVD379DR | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |




**D0008A**

# PACKAGE OUTLINE

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



4214825/C 02/2019

## NOTES:


1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
4. This dimension does not include interlead flash.
5. Reference JEDEC registration MS-012, variation AA.

# EXAMPLE BOARD LAYOUT



D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:8X



SOLDER MASK DETAILS

4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON .005 INCH [0.125 MM] THICK STENCIL  
SCALE:8X

4214825/C 02/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025