




LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECO-09-021480	08OCT2009	CR	DG
			B2	REVISED PER ECO-10-016367	02AUG2010	JY	SY



1888861-2 AND 1888861-9
SHOWN WITHOUT PICK AND PLACE DEVICE



1888861-4 AND 1-1888861-0
SHOWN WITHOUT PICK AND PLACE DEVICE



1888861-8 AND 1-1888861-2
SHOWN WITHOUT PICK AND PLACE DEVICE

△ MATERIAL: LCP, BLACK.

△ MATERIAL: PHOSPHOR BRONZE PER ASTM B 103.

△ FINISH: 0.76um MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03um MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81um MIN NICKEL PLATE PER QQ-N-290.


△ MATERIAL: NICKEL-SILVER PER ASTM B 122.

△ DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.

6. REFER TO CUSTOMER DRAWING 1761987 FOR CONNECTOR DETAILS.

7. PACKAGED IN TAPE AND REEL PER EIA-481.




△ FINISH: 0.38um MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03um MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81um MIN NICKEL PLATE PER QQ-N-290.



1888861-6 AND 1-1888861-1
SHOWN WITHOUT PICK AND PLACE DEVICE


△	THRU HOLE	3.5	17.8	16	16	36	18.05	36	1-1888861-2
		2.8	17.8	16	16	36	18.05	36	1-1888861-1
	PRESS FIT	-	17.8	16	16	36	18.05	36	1-1888861-0
△	THRU HOLE	2	17.8	16	16	36	18.05	36	1888861-9
		3.5	17.8	16	16	36	18.05	36	1888861-8
	PRESS FIT	-	17.8	16	16	36	18.05	36	1888861-6
△	THRU HOLE	2	17.8	16	16	36	18.05	36	1888861-4
		2	17.8	16	16	36	18.05	36	1888861-2
FINISH	REMARKS	G	E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS TO BE RETURNED TO TYCO ELECTRONICS CORPORATION WHEN NO LONGER REQUIRED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS TO BE RETURNED TO TYCO ELECTRONICS CORPORATION WHEN NO LONGER REQUIRED.		DWN B. MCMASTER 21FEB07	Tyco Electronics Harrisburg, PA 17105-3608	
CHK D. GORENC 21FEB07		APVD D. GORENC 21FEB07	NAME EVERCLEAR Mini-SAS RIGHT ANGLE, INTERNAL RECEPTACLE ASSEMBLY, WITH UNKEYED SHELL	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH ±	PRODUCT SPEC 108-2234	SIZE A100779
MATERIAL SEE NOTES		FINISH SEE TABLE	APPLICATION SPEC -	RESTRICTED TO -
CUSTOMER DRAWING		WEIGHT -	SCALE 8:1	SHEET 1 OF 3
		REV B2		





$$0.05^{+0.08}_{-0.05}$$

1888861-2
PICK AND PLACE DEVICE OMITTED FOR CLARITY



1888861-4
SAME AS 1888861-2 EXPECT AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION AND IT IS NOT TO BE REPRODUCED OR COPIED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS CORPORATION IT SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN B. MCMASTER 21FEB07		 Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK D. GORENC 21FEB07		NAME EVERCLEAR Mini-SAS RIGHT ANGLE, INTERNAL RECEPTACLE ASSEMBLY, WITH UNKEYED SHELL	
		APVD D. GORENC 21FEB07		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		PRODUCT SPEC 108-2234 APPLICATION SPEC		A 00779 C 1888861 -	
MATERIAL SEE NOTES		WEIGHT -		SCALE 5:1 SHEET 2 of 3 REV B2	
SEE TABLE		CUSTOMER DRAWING			

