

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	ECR-14-002793	25FEB2014	GK	HMR

REPLACED BY OCEAN STYLE APPLICATOR PART
NUMBER 2150035-2


FOR REPLACEMENT PARTS FOR APPLICATOR 1339768
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
1339768

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	GOPALAKRISHNA HV		 TE Connectivity			
		CHK	RAGHAVENDRA					
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	RAGHAVENDRA			
		0 PLC ±		NAME END FEED HD-I APPLICATOR				
		1 PLC ±						
		2 PLC ±						
		3 PLC ±						
4 PLC ±		4 PLC ±		PRODUCT SPEC				
MATERIAL		FINISH		APPLICATION SPEC		RESTRICTED TO		
				WEIGHT		SIZE A 3		
				CUSTOMER DRAWING		CAGE CODE		
						DRAWING NO C- 1339768		
						SCALE		
						SHEET 1 OF 2		
						REV C1		

1339768 1339768

CRIMP DATA		AMP TERMINAL	AMP CRIMP SPECS
TERMINAL NAME: 6.3MM SERIES FASTIN-FASTON TAB			
CRIMP	SIZE	TYPE	RANGE
WIRE	2.03 [.080 IN]	F	0.35mm ² - 1.00mm ²
INSUL	3.30 [.130 IN]	F	1.3-2.3 [.051-.091 IN]
WIRE STRIP LENGTH			APPL INSTRUCTION 408-8323
5.50 [.217 IN]			

[illegible][illegible]

REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG. REVISION)

79	CUSTOMER AND ASSEMBLY DRAWING	=
----	-------------------------------	---