


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J	REVISED PER ECN 0G10-0114-98	10AUG98	SU	MB
	J1	REVISED PER ECO-17-014438	10OCT2017	RS	DR



AMP WIRE RANGE	E13288 Listed
8 AWG SOLID OR STRANDED	8 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
8 AWG SOLID OR STRANDED	NOT APPLICABLE

PRELIMINARY	M8 ⁵ / ₁₆	8.331 [.328]	100	LOOSE PIECE		322727-2
	M6 ¹ / ₄	6.731 [.265]	100	LOOSE PIECE		322727
	"B"	"A"	QTY.	PACKAGE TYPE	FINISH	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 11JUN97		 TE Connectivity						
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F]MAX		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -	CHK MJ SPICER 12JUN97	NAME						
		VOLTAGE RATING: NOT APPLICABLE						TERMINAL, RING TONGUE, FLAG, SOLISTRAND™ 8 AWG						
	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.54mm² [13,100-20,800] CIR MILS SOLID OR STRANDED		MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH SEE NOTES			APVD JL MECKLEY 12JUN97	PRODUCT SPEC —	APPLICATION SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO —
	FOR ORDER ENTRY 1-800-526-5142										A300779		C=322727	
CUSTOMER DRAWING							SCALE 4:1		SHEET 1 OF 1		REV J1			