

Customer Information Sheet

DRAWING No.: D01-967XXXX

SHEET 2 OF 2

IF IN DOUBT - ASK




(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

OBSOLETE



SPECIFICATIONS:

MATERIALS:

MOULDING = GLASS-FILLED POLYESTER,
BLACK, UL94V-0

CONTACT CLIP = BERYLLIUM COPPER

CONTACT SHELL = BRONZE

FINISH:

01 - CLIP = 0.25µ GOLD OVER 2-3µ NICKEL

SHELL = 5µ 90/10 TIN/LEAD OVER 2-3µ NICKEL

T6 - CLIP = 5µ 90/10 TIN/LEAD OVER 2-3µ NICKEL

SHELL = 5µ 90/10 TIN/LEAD OVER 2-3µ NICKEL

ELECTRICAL:

CURRENT RATING (PER CONTACT) = 1 AMP MAX

VOLTAGE RATING = 100V AC, 150V DC MAX

CONTACT RESISTANCE = 10 MILLIOHMS MAX

INSULATION RESISTANCE = 10,000 MEGOHMS MIN

AT 500V AC

DIELECTRIC STRENGTH = 1,000V AC MIN

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

MECHANICAL:

DURABILITY = 500 OPERATIONS

INSERTION FORCE (Ø0.46mm GAUGE) = 1.8N

WITHDRAWAL FORCE (Ø0.46mm GAUGE) = 1.0N

INSERTION FORCE IN PCB = 200N MAX

RETENTION FORCE IN PCB (INITIAL) = 25N MIN

RETENTION FORCE IN PCB AFTER 3 INSERTIONS
= 12.5N MIN

NOTES:

1. RECOMMENDED PLATED-THROUGH HOLE SIZE = Ø1.09-0.94mm.
2. RECOMMENDED PC BOARD THICKNESS = 1.5 TO 2.0mm.
3. RECOMMENDED MATING PIN DIAMETER = Ø0.56-0.40mm.
4. MATING PIN LENGTH = 2.40mm MIN, 3.65mm MAX.

ORDER CODE:

D01-967XXXX

No. OF WAYS

02 TO 64

FINISH

01 - GOLD CLIP, 90/10 TIN/LEAD SHELL

T6 - 90/10 TIN/LEAD CLIP AND SHELL

1 15.08.00 ----

ISS. DATE C/NOTE

APPROVED:

CHECKED:

DRAWN: W. J. BOURNE

CUSTOMER REF.:

ASSEMBLY DRG:

HARWIN

HARWIN INC
U.S.A.

TEL: (812) 285 0055
FAX: (812) 285 0056

HARWIN PLC
U.K.

TEL: 023 9237 0451
FAX: 023 9231 4590

HARWIN PTE
SINGAPORE

TEL: 65 7794909
FAX: 65 7793868

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm

X.X = ±0.25mm

X.XX = ±0.10mm

X.XXX = ±0.01mm

ANGLES = ±1°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE: 2.54mm PITCH SIL
VERTICAL PRESS-FIT PC TAIL
FEMALE SOCKET ASSEMBLY

DRAWING NUMBER:

D01-967XXXX

SHT
2 OF
2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Harwin:

[D01-9670801](#) [D01-9671201](#)