

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

D

REVISED PER 0G3B-0106-01

06SEP2001

EZ

DB



E

REVISED PER 0G3B-0119-01



06SEP2001

EZ

DB




282862-3 AS SHOWN



125	25	2-282862-5
120	24	2-282862-4
115	23	2-282862-3
110	22	2-282862-2
105	21	2-282862-1
100	20	2-282862-0
95	19	1-282862-9
90	18	1-282862-8
85	17	1-282862-7
80	16	1-282862-6
75	15	1-282862-5
70	14	1-282862-4
65	13	1-282862-3
60	12	1-282862-2
55	11	1-282862-1
50	10	1-282862-0
45	9	282862-9
40	8	282862-8
35	7	282862-7
30	6	282862-6
25	5	282862-5
20	4	282862-4
15	3	282862-3
10	2	282862-2


DIM. A N° OF POS. PART NUMBER

RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC $\pm .3$
1 PLC $\pm .3$
2 PLC $\pm .25$
3 PLC $\pm .3$
4 PLC $\pm .3$
ANGLES ± 2

MATERIAL



FINISH



DWN 06SEP2001

E. ZANOLINI

CHK 06SEP2001

D. BIEVENOUR

APVD 06SEP2001

D. BIEVENOUR

PRODUCT SPEC

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING

BUCHANAN

Tyco Electronics
Harrisburg, PA 17105-3608NAME
TERMINAL BLOCK PCB MOUNT
TOP ENTRY WIRE, STACKING
W/ INTERLOCK, 5mm PITCH

SIZE A3 CAGE CODE 00779 DRAWING NO C-282862 RESTRICTED TO -

SCALE 3:1 SHEET 1 OF 2 REV E

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

- 1

MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2

SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3

END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF
CENTERLINE SPACING.
- 4

WIRE SIZE RANGE
SOLID WIRE: 0,03-4mm² (11AWG).
STRANDED WIRE: 0,03-2,5mm² (13AWG).
- 5

RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC., FILE N° E60677.
- 6


IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 7

NOT CUMULATIVE TOLERANCE.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm



MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±.2

2 PLC ±.15

3 PLC ±-

4 PLC ±-

ANGLES ±2

FINISH -

DWN
E. ZANOLINI
CHK
D. BIEVENOUR
APVD
D. BIEVENOUR

06SEP2001
06SEP2001
06SEP2001

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

BUCHANAN

Tyco Electronics
Harrisburg, PA 17105-3608

NAME
TERMINAL BLOCK PCB MOUNT
TOP ENTRY WIRE, STACKING
W/ INTERLOCK, 5mm PITCH

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-282862

RESTRICTED TO
-

SCALE
3:1

SHEET
2

OF
2

REV
E

AMP 1470-19 REV 31MAR2000