






LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	EC 0G3C-0004-04	19JUL04	BSV	MSS

D

C

B

A



SPECIFICATIONS: UNLESS OTHERWISE SPECIFIED:

CONTACT RATING: 0.4VA @ 20VDC (MAX.).
INITIAL CONTACT RESISTANCE: 50 MILLIOHMS (MAX).
INSULATION RESISTANCE: 100 MEGOHMS (MIN.) @ 100VDC.
DIELECTRIC STRENGTH: 500VDC AT SEA LEVEL.
OPERATING FORCE: 400 GRAMS MAX..
LIFE EXPECTANCY: 1,000 CYCLES.
ACTUATOR TRAVEL: 30° .
OPERATING TEMPERATURE: -20°C TO +85°C
SOLDER HEAT RESISTANCE:
260°C ±5°C FOR TEN SECONDS WHEN MOUNTED
ON A .062" THICK PCB WITH SWITCH IN
"OFF" POSITION.
HAND SOLDERING: 500°F (260°C) -660°F (350°C)
UTILIZING A CONTROLLED 40 WATT
IRON FOR 3-5 SECONDS MAX.
STORAGE TEMPERATURE: -55°C TO +85°C

MATERIAL: UNLESS OTHERWISE SPECIFIED:

BASE: PPS UL94 V-0, BLACK.
HOUSING: PPS UL94 V-0, BLACK.
ACTUATOR: POLYIMIDE 94V-0, WHITE
CONTACTS: COPPER ALLOY, GOLD/NICKEL PLATE
TERMINALS: COPPER ALLOY, GOLD/NICKEL PLATE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	BSV	19JUL04	tyco Electronics		Tyco Electronics Corporation					
		CHK	-	-			Harrisburg, Pa 17105-3808					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	M.S. SARVER	NAME	DPU-SERIES DIP SWITCH					
		0 PLC ± -		PRODUCT SPEC		DPU06		RESTRICTED TO				
		1 PLC ± -		-								
		2 PLC ± -		APPLICATION SPEC								
		3 PLC ± .012		-								
MATERIAL		FINISH		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO				
SEE NOTES		-				A2	00779	C-1-1437583-4				
CUSTOMER DRAWING						SCALE		4:1	SHEET	1 OF 1	REV	B