

# MUR405, MUR410, MUR415, MUR420, MUR440, MUR460

## SWITCHMODE Power Rectifiers

These state-of-the-art devices are a series designed for use in switching power supplies, inverters and as free wheeling diodes.

### Features

- Ultrafast 25 ns, 50 ns and 75 ns Recovery Times
- 175°C Operating Junction Temperature
- Low Forward Voltage
- Low Leakage Current
- High Temperature Glass Passivated Junction
- Reverse Voltage to 600 V
- Shipped in Plastic Bags, 500 per Bag
- Available in Tape and Reel, 1500 per Reel, by Adding a “RLG” Suffix to the Part Number
- MUR460 available in Fan Fold Ammo Pak, 1000 per Box, by adding a “FFG” suffix to the part number
- These are Pb-Free Packages\*

### Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 1.1 Gram (Approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Polarity: Cathode indicated by Polarity Band



**ON Semiconductor®**


<http://onsemi.com>

## ULTRAFAST RECTIFIERS 4.0 AMPERES, 50–600 VOLTS



**AXIAL LEAD  
CASE 267  
STYLE 1**

### MARKING DIAGRAM



A = Assembly Location  
MUR4xx = Device Number  
x = 05, 10, 15, 20, 40, 60  
YY = Year  
WW = Work Week  
■ = Pb-Free Package  
(Note: Microdot may be in either location)

### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 3 of this data sheet.

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

# MUR405, MUR410, MUR415, MUR420, MUR440, MUR460

## MAXIMUM RATINGS

| Rating                                                                                                       | Symbol                          | MUR                              |     |     |     |                                  |     | Unit               |
|--------------------------------------------------------------------------------------------------------------|---------------------------------|----------------------------------|-----|-----|-----|----------------------------------|-----|--------------------|
|                                                                                                              |                                 | 405                              | 410 | 415 | 420 | 440                              | 460 |                    |
| Peak Repetitive Reverse Voltage<br>Working Peak Reverse Voltage<br>DC Blocking Voltage                       | $V_{RRM}$<br>$V_{RWM}$<br>$V_R$ | 50                               | 100 | 150 | 200 | 400                              | 600 | V                  |
| Average Rectified Forward Current (Square Wave)<br>(Mounting Method #3 Per Note 2)                           | $I_{F(AV)}$                     | 4.0 @ $T_A = 80^{\circ}\text{C}$ |     |     |     | 4.0 @ $T_A = 40^{\circ}\text{C}$ |     | A                  |
| Nonrepetitive Peak Surge Current<br>(Surge applied at rated load conditions, half wave, single phase, 60 Hz) | $I_{FSM}$                       | 125                              |     |     |     | 110                              |     | A                  |
| Operating Junction Temperature & Storage Temperature                                                         | $T_J, T_{stg}$                  | - 65 to +175                     |     |     |     |                                  |     | $^{\circ}\text{C}$ |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

## THERMAL CHARACTERISTICS

| Rating                                          | Symbol          | MUR        |     |     |     |     |     | Unit                 |
|-------------------------------------------------|-----------------|------------|-----|-----|-----|-----|-----|----------------------|
|                                                 |                 | 405        | 410 | 415 | 420 | 440 | 460 |                      |
| Maximum Thermal Resistance, Junction-to-Ambient | $R_{\theta JA}$ | See Note 2 |     |     |     |     |     | $^{\circ}\text{C/W}$ |

## ELECTRICAL CHARACTERISTICS

| Rating                                                                                                                                                                                                                     | Symbol     | MUR                  |     |     |     |                      |     | Unit          |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|----------------------|-----|-----|-----|----------------------|-----|---------------|
|                                                                                                                                                                                                                            |            | 405                  | 410 | 415 | 420 | 440                  | 460 |               |
| Maximum Instantaneous Forward Voltage (Note 1)<br>( $I_F = 3.0\text{ A}$ , $T_J = 150^{\circ}\text{C}$ )<br>( $I_F = 3.0\text{ A}$ , $T_J = 25^{\circ}\text{C}$ )<br>( $I_F = 4.0\text{ A}$ , $T_J = 25^{\circ}\text{C}$ ) | $V_F$      | 0.71<br>0.88<br>0.89 |     |     |     | 1.05<br>1.25<br>1.28 |     | V             |
| Maximum Instantaneous Reverse Current (Note 1)<br>(Rated dc Voltage, $T_J = 150^{\circ}\text{C}$ )<br>(Rated dc Voltage, $T_J = 25^{\circ}\text{C}$ )                                                                      | $I_R$      | 150<br>5             |     |     |     | 250<br>10            |     | $\mu\text{A}$ |
| Maximum Reverse Recovery Time<br>( $I_F = 1.0\text{ A}$ , $di/dt = 50\text{ A}/\mu\text{s}$ )<br>( $I_F = 0.5\text{ A}$ , $I_R = 1.0\text{ A}$ , $I_{REC} = 0.25\text{ A}$ )                                               | $t_{rr}$   | 35<br>25             |     |     |     | 75<br>50             |     | ns            |
| Maximum Forward Recovery Time<br>( $I_F = 1.0\text{ A}$ , $di/dt = 100\text{ A}/\mu\text{s}$ , Recovery to 1.0 V)                                                                                                          | $t_{fr}$   | 25                   |     |     |     | 50                   |     | ns            |
| Controlled Avalanche Energy (Maximum)                                                                                                                                                                                      | $W_{aval}$ |                      |     |     |     | 5                    |     | mJ            |
| Typical Peak Reverse Recovery Current<br>( $I_F = 1.0\text{ A}$ , $di/dt = 50\text{ A}/\mu\text{s}$ )                                                                                                                      | $I_{RM}$   | 0.8                  |     |     |     | 1.7                  |     | A             |

1. Pulse Test: Pulse Width = 300  $\mu\text{s}$ , Duty Cycle  $\leq 2.0\%$ .

## MUR405, MUR410, MUR415, MUR420, MUR440, MUR460

### ORDERING INFORMATION

| Device    | Package     | Shipping <sup>†</sup> |
|-----------|-------------|-----------------------|
| MUR405G   | Axial Lead* | 500 Units / Bag       |
| MUR410G   | Axial Lead* |                       |
| MUR410RLG | Axial Lead* | 1500 / Tape & Reel    |
| MUR415G   | Axial Lead* | 500 Units / Bag       |
| MUR415RLG | Axial Lead* | 1500 / Tape & Reel    |
| MUR420G   | Axial Lead* | 500 Units / Bag       |
| MUR420RLG | Axial Lead* | 1500 / Tape & Reel    |
| MUR440G   | Axial Lead* | 500 Units / Bag       |
| MUR440RLG | Axial Lead* | 1500 / Tape & Reel    |
| MUR460G   | Axial Lead* | 500 Units / Bag       |
| MUR460FFG | Axial Lead* | 1000 Units / Box      |
| MUR460RLG | Axial Lead* | 1500 / Tape & Reel    |

<sup>†</sup>For information on tape and reel and ammo pak specifications, including part orientation, tape sizes and box dimensions, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*These packages are inherently Pb-Free.

# MUR405, MUR410, MUR415, MUR420, MUR440, MUR460

## MUR405, MUR410, MUR415, MUR420




Figure 1. Typical Forward Voltage




Figure 2. Typical Reverse Current




Figure 3. Current Derating  
(Mounting Method #3 Per Note 2)




Figure 4. Power Dissipation




Figure 5. Typical Capacitance

# MUR405, MUR410, MUR415, MUR420, MUR440, MUR460

## MUR440, MUR460




Figure 6. Typical Forward Voltage




Figure 7. Typical Reverse Current




Figure 8. Current Derating  
(Mounting Method #3 Per Note 2)




Figure 9. Power Dissipation





Figure 10. Typical Capacitance

MUR440, MUR460



**Figure 11. Typical Non-Repetitive Surge Current**

\*Typical performance based on a limited sample size. ON Semiconductor does not guarantee ratings not listed in the Maximum Ratings table.

NOTE 2 — AMBIENT MOUNTING DATA


Data shown for thermal resistance junction-to-ambient ( $R_{\theta JA}$ ) for the mountings shown is to be used as typical guideline values for preliminary engineering or in case the tie point temperature cannot be measured.

TYPICAL VALUES FOR  $R_{\theta JA}$  IN STILL AIR

| Mounting Method |                 | Lead Length, L (IN) |     |     |     | Units |
|-----------------|-----------------|---------------------|-----|-----|-----|-------|
|                 |                 | 1/8                 | 1/4 | 1/2 | 3/4 |       |
| 1               | $R_{\theta JA}$ | 50                  | 51  | 53  | 55  | °C/W  |
| 2               |                 | 58                  | 59  | 61  | 63  | °C/W  |
| 3               |                 | 28                  |     |     |     | °C/W  |


MOUNTING METHOD 1

P.C. Board Where Available Copper Surface area is small.




MOUNTING METHOD 2

Vector Push-In Terminals T-28



MOUNTING METHOD 3


P.C. Board with 1-1/2" x 1-1/2" Copper Surface



# MUR405, MUR410, MUR415, MUR420, MUR440, MUR460

## PACKAGE DIMENSIONS

AXIAL LEAD  
CASE 267-03  
(DO-201AD)  
ISSUE G



- NOTES:  
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.  
2. CONTROLLING DIMENSION: INCH.

| DIM | INCHES |       | MILLIMETERS |      |
|-----|--------|-------|-------------|------|
|     | MIN    | MAX   | MIN         | MAX  |
| A   | 0.287  | 0.374 | 7.30        | 9.50 |
| B   | 0.189  | 0.209 | 4.80        | 5.30 |
| D   | 0.047  | 0.051 | 1.20        | 1.30 |
| K   | 1.000  | ---   | 25.40       | ---  |

STYLE 1:  
PIN 1. CATHODE (POLARITY BAND)  
2. ANODE

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marketing.pdf](http://www.onsemi.com/site/pdf/Patent-Marketing.pdf). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

N. American Technical Support: 800-282-9855 Toll Free  
USA/Canada  
Europe, Middle East and Africa Technical Support:  
Phone: 421 33 790 2910  
Japan Customer Focus Center  
Phone: 81-3-5817-1050

ON Semiconductor Website: [www.onsemi.com](http://www.onsemi.com)

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative