



8/16 Port IEEE802.3at/PoEPLUS Midspans PoE576U for 10/100/1000 Base-T Networks



Features

- Compliant with the IEEE802.3at Standard
- 2 finger classification
- SNMP Management Option
- Optional SSL with SNMPv3
- Windows GUI
- May power Cisco AP1250 with ACCY125X dongle
- Full Power of 576W—30W per Port, No Power Management required
- Full Protection OTP, OCP, OVP
- 1U Rack Mountable (Mounting Kit Ships with Unit)
- Limited Lifetime Warranty
- 10/100/1000 Base-T Compatible

Applications

- VoIP Phones
- Access Point
- Security Systems
- IP Cameras

Safety Approvals

- cUL/UL
- CE

Mechanical Characteristics

- Length: 438mm (17.25in)
- Width: 228mm (8.98in)
- Height: 44.5 mm (1.75in)
- Weight: 3.8Kg (8.5lbs)

Output Specifications

Model	Number of Ports
POE576U-16AT(y)	16
POE576U-8AT (y)	8

Options: y= N to add SNMP

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

INPUT:**AC Input**

Voltage Range 90 to 264VAC

Input Frequency 47-63Hz

Input Current:

9A (RMS) maximum for 90VAC

4.5A (RMS) maximum for 230VAC

Leakage Current: 3.5mA maximum @ 264VAC 60Hz

AC Inrush Current:

30A (RMS) maximum for 115VAC

60A (RMS) maximum for 230VAC

OUTPUT:**Total Output Power**

33.6W per port

Total Power 269W (8 ports) -538W (16 ports)

Ripple and Regulation

100mV maximum

Efficiency

75% (typical) at maximum load, and 120VAC 60Hz

Hold-up Time

16mS min. 120VAC and maximum load

Transient O/P Voltage Protection

60V maximum at switch on and off at any AC line Phase

Turn-On Delay Time

20 sec maximum at maximum load, and 120VAC 60Hz, 60Hz

ENVIRONMENTAL:**Temperature**

Operation 0 to +40°C

Non-operation -25 to +65°C

Humidity

Operation 5 to 90%

Non-Operation 5 to 90%

EMC

EN55022 Class A, FCC Class A with UTP cabling

EN55022 Class B, FCC Class B with FTP cabling

Isolation Test

Primary to Secondary: 4242VDC for 1 minute

Primary to Ground: 2121VDC for 1 minute

Secondary to Ground: 2121VDC for 1 minute

Immunity EN50082-1

ESD: EN61000-4-2. Level 3

RS: EN61000-4-3. Level 2

EFT: EN61000-4-4. Level 2

Surge: EN61000-4-5. Level 3

CS: EN61000-4-6. Level 2

Voltage Dips EN61000-4-11

Harmonic: EN61000-3-2 Class A

IEEE 802.3at Interoperability

UNH Interoperability report available on request

FEATURE:**Cisco Legacy detection**

No extern parts required for Legacy devices:

VoIP Phones:

7910, 7912, 7940, 7960

Access Points:

1040, 1140, 1260, 3500

Over Voltage/Current, Short Circuit Protection

Outputs equipped with short circuit protection and overload protection as per 802.3at specifications

The output can be shorted permanently without damage

Over Temperature Protection

Automatic Shutdown without damage

Indicators

Green LED: Power detected "CONNECT"

Flashing GREEN: IEEE802.3af detected "CONNECT" at 15.4W

Yellow LED: Fault detected

USB Diagnostics Port and NIC Interface

USB "B" port for diagnostics and manual port control
Windows GUI


NIC interface for remote management via secure IP access

Input Connector

AC Input IEC320 C14

Warranty

Limited Lifetime



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phihong:

[POE576U-16ATN-R](#) [POE576U-16AT-R](#) [POE576U-8ATN-R](#) [POE576U-8AT-R](#)