






SECT. J-J

SCALE 20:1




0.28 ^{+0.03}	13.65	17	12.5	18.2	54550-26 17	26
0.3 ^{+0.03}	12.65	16	11.5	17.2	54550-24 17	24
	11.65	15	10.5	16.2	54550-22 17	22
	11.15	14.5	10	15.7	54550-21 17	21
	10.65	14	9.5	15.2	54550-20 17	20
	10.15	13.5	9	14.7	54550-19 17	19
	9.65	13	8.5	14.2	54550-18 17	18
	9.15	12.5	8	13.7	54550-17 17	17
	8.65	12	7.5	13.2	54550-16 17	16
	8.15	11.5	7	12.7	54550-15 17	15
	7.65	11	6.5	12.2	54550-14 17	14
	7.15	10.5	6	11.7	54550-13 17	13
	6.65	10	5.5	11.2	54550-12 17	12
	6.15	9.5	5	10.7	54550-11 17	11
	5.65	9	4.5	10.2	54550-10 17	10
	5.15	8.5	4	9.7	54550-09 17	9
	4.65	8	3.5	9.2	54550-08 17	8
	4.15	7.5	3	8.7	54550-07 17	7
3.65	7	2.5	8.2	54550-06 17	6	
3.15	6.5	2	7.7	54550-05 17	5	

THICKNESS
OF FPC

54550-**-17

SERIAL NO.	SR.
MODEL NO.	



VIEW H

REVISED	EC NO: J2007-4760 DRAWN: YAOYAGI CHKD: K. TOYODA APPR: NUKITA	2007/02/14 2007/06/01 2007/06/06	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC		MODEL NO. THIRD ANGLE PROJECTION
				10 UNDER	± 0.2	M. FUJIKURA	1999/03/24	TITLE 0.5 FPC CONN. ZIF HOUSING ASSY -LEAD FREE-			
				10 OVER 30 UNDER	± 0.25	CHECKED BY	DATE				
				30 OVER	± 0.3	S. KUNISHI	1999/03/24				
				APPROVED BY		DATE	MOLEX INCORPORATED				
				M. FUKUSHIMA		1999/03/24					
				ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-54550-005		1 OF 2					
M	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

DWG. NO.
SD-54550-006

F

D

A

C

B

DO NOT SCALE DRAWING

8

7

6

5

4

3

2

1

F

E

D

C


B

SD-54550-006.S01

NOTES



- 製品詳細寸法については図面 54550-**17 を参照下さい。
RE DETAILED DIMENSION, SEE 54550-**17
- 梱包数量：3000個／リール
NUMBER OF CONNECTORS：3000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH

引き出し方向
PULL OUT




DETAIL "F"

引き出し方向
PULL OUT
DIRECTION



- トップテープの剥離強度：0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE：0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED ,DURING TRANSPORTATION.



- 材料(MATERIAL)
キャリアテープ(CARRIER TAPE)：ポリプロピレン(POLYPROPYLENE)
トップテープ(TOP TAPE)：PET , PE , PEF
リール(REEL)：ポリスチレン(P S) <リサイクル材を含む>
POLYSTYREN(PS) <RECYCLE MATERIAL CONTAINED>

EC NO. DRWN: CHK: APPR:			REVISED EC NO. J2004-0609 DRWN: R.SUMIYA '03/09/17 CHK: T.IITO '03/09/17 APPR: T.YAMAGUCHI '03/09/17			REVISED EC NO. J2003-2548 DRWN: M.FUJIKURA '03/04/03 CHK: K.KASAKAWA '03/04/04 APPR: T.YAMAGUCHI '03/04/04			REVISED EC NO. J2002-2828 DRWN: T.HANYU '02/5/15 CHK: M.SASAO '02/5/15 APPR: M.SASAO '02/5/15			MATERIAL 材料 注記参照 SEE NOTES		GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		54550-**90 SCALE — DESIGN UNITS —mm —mm —INCH		MODEL No. THIRD ANGLE PROJECTION		DIMENSIONS: mm INCH mm INCH mm ONLY		SHT REV		
			M			L			K			REV		10 UNDER 未満 ±0.2		DRAWN BY & DATE M.FUJIKURA '99/03/24		TITLE: 0.5 FPC Conn ZIF Hsg Assy SMT RA Upper Contact Embstp Pkg						
											FINISH 仕上げ		10 OVER 30 UNDER 以上 未満 ±0.25		CHECKED BY & DATE S.KUNISHI '99/03/24									
											WIRE RANGE 適用電線範囲		30 OVER 以上 ±0.3		APPROVED BY & DATE M.FUKUSHIMA '99/03/24		MOLEX INCORPORATED							
											INS. RANGE 被覆外径		ANGLE 角度		±3°		CAD FILENAME SD-54550-006.S01		MATERIAL NO. SEE CHART		DRAWING NO. SD-54550-006		SHEET NO. 1 OF 4	
																	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.						SIZE B	

8

7

6

5

4

3

2

EN-02J(097) MXJ-54

DWG. NO.
SD-54550-006

F

D

V

C

B

DO NOT SCALE DRAWING


EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	SEE SHEET 1 OF 4	EC NO. DRWN: CHK: APPR:
		M	L	K	

DESCRIPTION	MATERIAL 材料
FINISH 仕上げ	SHEET 1 OF 4 参照 REFER TO SHEET 1 OF 4
WIRE RANGE 適用電線範囲	—//—
INS. RANGE 被覆外径	—//—

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE —#	DESIGN UNITS mm INCH
10 UNDER 未満	±0.2	DRAWN BY & DATE M.FUJIKURA '99/03/24
10 OVER 30 UNDER 以上 未満	±0.25	CHECKED BY & DATE S.KUNISHI '99/03/24
30 OVER 以上	±0.3	APPROVED BY & DATE M.FUKUSHIMA '99/03/24
ANGLE 角度	±3°	CAD FILENAME SD-54550-006.S02



54550-**-90	MODEL No.	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY	SHT	REV
キャリアテープ幅 CARRIER TAPE WIDTH	D	THIRD ANGLE PROJECTION		
TITLE: 0.5 FPC Conn ZIF Hsg Assy SMT RA Upper Contact Embstp Pkg				
MOLEX INCORPORATED				
MATERIAL NO. SEE CHART		DRAWING NO. SD-54550-006	SHEET NO. 2 OF 4	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				
SIZE B				

SECT. Y-Y



16mm幅キャリアテープ
16mm WIDTH CARRIER TAPE

引き出し方向
PULL OUT DIRECTION



SECT. X-X

DWG. NO.
SD-54550-006

F

D


▽

C

B

DO NOT SCALE DRAWING

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	SEE SHEET 1 OF 4 EC NO. DRWN: CHK: APPR:	DESCRIPTION
		M	L	K	MATERIAL 材料 SHEET 1 OF 4 参照 REFER TO SHEET 1 OF 4
					FINISH 仕上げ //
					WIRE RANGE 適用電線範囲 //
					INS. RANGE 被覆外径 //



24	25.5	12.3	16.4	17.5	54550-2290	22
		11.8	15.9	17	54550-2190	21
		11.3	15.4	16.5	54550-2090	20
		10.8	14.9	16	54550-1990	19
		10.3	14.4	15.5	54550-1890	18
		9.8	13.9	15	54550-1790	17
		9.3	13.4	14.5	54550-1690	16
		8.8	12.9	14	54550-1590	15
		8.3	12.4	13.5	54550-1490	14
		7.8	11.9	13	54550-1390	13
		7.3	11.4	12.5	54550-1290	12
		6.8	10.9	12	54550-1190	11
		6.3	10.4	11.5	54550-1090	10
		5.8	9.9	11	54550-0990	9
		5.3	9.4	10.5	54550-0890	8
		4.8	8.9	10	54550-0790	7
キャリアテープ幅 CARRIER TAPE WIDTH	D	(C)	(B)	(A)	製品番号 MATERIAL No.	極数 Ck+

A	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	SEE SHEET 1 OF 4	DESCRIPTION	MATERIAL 材 料	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE —#—	DESIGN UNITS ☒ mm ☐ INCH	THIRD ANGLE PROJECTION	☐ mm INCH ☐ mm INCH ☒ mm ONLY	REVISE ON CAD ONLY			
	SHEET 1 OF 4 参照 REFER TO SHEET 1 OF 4						10 UNDER 未 満	±0.2	DRAWN BY & DATE M.FUJIKURA '99/03/24				TITLE: 0.5 FPC Conn ZIF Hsg Assy SMT RA Upper Contact Embstp Pkg		
	FINISH 仕 上 げ						10 OVER 以 上	30 UNDER 未 満	±0.25	CHECKED BY & DATE S.KUNISHI '99/03/24					
							30 OVER 以 上	±0.3	APPROVED BY & DATE M.FUKUSHIMA '99/03/24				MOLEX MOLEX INCORPORATED		
	WIRE RANGE 通用電線範圍						ANGLE	角度	±3°	CAD FILENAME SD-54550-006.S03		MATERIAL NO. SEE CHART		DRAWING NO. SD-54550-006	SHEET NO. 3 OF 4
		M	L	K	REV	INS. RANGE 被 覆 外 径		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				SIZE B			

SD-54550-006.S03

DWG. NO.
SD-54550-006

F

D

V

C

B

DO NOT SCALE DRAWING

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	SEE SHEET 1 OF 4
		M	L	K


DESCRIPTION	MATERIAL 材料
FINISH 仕上げ	SHEET 1 OF 4 参照 REFER TO SHEET 1 OF 4
WIRE RANGE 適用電線範囲	
INS. RANGE 被覆外径	

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE —#—
10 UNDER 未満	±0.2
10 OVER 30 UNDER 以上 未満	±0.25
30 OVER 以上	±0.3
ANGLE 角度	±3°

54550-**-90	MODEL No.
DRAWN BY & DATE N.YANO '99/10/25	THIRD ANGLE PROJECTION
CHECKED BY & DATE S.KUNISHI '99/10/25	TITLE: 0.5 FPC Conn ZIF Hsg Assy SMT RA Upper Contact Embstp Pkg
APPROVED BY & DATE M.FUKUSHIMA '99/10/25	MOLEX INCORPORATED
CAD FILENAME SD-54550-006.S04	MATERIAL NO. SEE CHART
	DRAWING NO. SD-54550-006
	SHEET NO. 4 OF 4



32	33.5	14.3	18.4	19.5	54550-2690	26
		13.3	17.4	18.5	54550-2490	24
キャリアテープ幅 CARRIER TAPE WIDTH	D	(C)	(B)	(A)	製品番号 MATERIAL No.	極数 Ckt

SECT. Y-Y



32mm幅キャリアテープ
32mm WIDTH CARRIER TAPE

引き出し方向
PULL OUT DIRECTION



SECT. X-X

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.

SD-54550-006.S04

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

54550-1190 BULK