








NOTES:

1. MATERIALS AND FINISHES:

BODY - BRASS, GOLD PLATING (.00000008 m [.000003 in] MIN THICK)
OVER NICKEL (.00000500 m [.000196 in] MIN THICK)
CONTACT 1 - BeB, GOLD PLATING (.00000002 m [.000008 in] MIN THICK)
OVER NICKEL (.00000500 m [.000196 in] MIN THICK)
CONTACT 2 - PB, GOLD PLATING (.00000002 m [.000008 in] MIN THICK)
OVER NICKEL (.00000500 m [.000196 in] MIN THICK)
INSULATOR - PA9T, BLACK
CAP - PA9T, BLACK

2. PACKAGING:

TAPE AND REEL
700 PCS PER REEL
330 DIAMETER REEL



SCALE 4.000

METRIC DRAWING

SINGLE POLE DOUBLE THROW SWITCH

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE METRIC AND TOLERANCES ARE: 1 PLACE DECIMAL 2 PLACE DECIMAL ANGLES ± 0.3MM (.012") ± .10 MM (.004") ± 1°	MATERIAL - REFERENCE EAR #2019 CONFIGURATION LEVEL: Released	DRAWN M. HOYACK	DATE 15-Jun-06	TITLE RF SWITCH, JACK PCB SURFACE MOUNT				Amphenol RF Danbury, CT, USA Tainan, Taiwan Shenzhen, China www.amphenolrf.com		
		ENGINEER M. HOYACK	DATE 15-Jun-06							
		APPROVED O. BARTHELMES	DATE 6/22/06							
		CAD FILE Root Folder/Switch/902-9024			CODE ID 74868	DWG SIZE B	DRAWING NO. 902-9024	REV A		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[902-9024](#)