





SEE CHART
SDA-90627



WAFER: 15% G.F. POLYESTER
TO UL 94V-0.
COLOUR : BLACK.



OPPOSING KINKS
VIEW SHOWS 1 X 2 CCT ONLY




STRAIGHT PINS
OMITTED FROM VIEW

CKT SIZE	DIM. "A"		DIM. "B" ^(+0.20) ±.008		CKT SIZE	DIM. "A"		DIM. "B" ^(+0.20) ±.008	
1X 1			(2.54)		1X21	(50.80)	2.000	(53.34)	2.100
1X 2	(2.54)	.100	(5.08)	.200	1X22	(53.34)	2.100	(55.88)	2.200
1X 3	(5.08)	.200	(7.62)	.300	1X23	(55.88)	2.200	(58.42)	2.300
1X 4	(7.62)	.300	(10.16)	.400	1X24	(58.42)	2.300	(60.96)	2.400
1X 5	(10.16)	.400	(12.70)	.500	1X25	(60.96)	2.400	(63.50)	2.500
1X 6	(12.70)	.500	(15.24)	.600	1X26	(63.50)	2.500	(66.04)	2.600
1X 7	(15.24)	.600	(17.78)	.700	1X27	(66.04)	2.600	(68.58)	2.700
1X 8	(17.78)	.700	(20.32)	.800	1X28	(68.58)	2.700	(71.12)	2.800
1X 9	(20.32)	.800	(22.86)	.900	1X29	(71.12)	2.800	(73.66)	2.900
1X10	(22.86)	.900	(25.40)	1.000	1X30	(73.66)	2.900	(76.20)	3.000
1X11	(25.40)	1.000	(27.94)	1.100	1X31	(76.20)	3.000	(78.74)	3.100
1X12	(27.94)	1.100	(30.48)	1.200	1X32	(78.74)	3.100	(81.28)	3.200
1X13	(30.48)	1.200	(33.02)	1.300	1X33	(81.28)	3.200	(83.82)	3.300
1X14	(33.02)	1.300	(35.56)	1.400	1X34	(83.82)	3.300	(86.36)	3.400
1X15	(35.56)	1.400	(38.10)	1.500	1X35	(86.36)	3.400	(88.90)	3.500
1X16	(38.10)	1.500	(40.64)	1.600	1X36	(88.90)	3.500	(91.44)	3.600
1X17	(40.64)	1.600	(43.18)	1.700	1X37	(91.44)	3.600	(93.98)	3.700
1X18	(43.18)	1.700	(45.72)	1.800	1X38	(93.98)	3.700	(96.52)	3.800
1X19	(45.72)	1.800	(48.26)	1.900	1X39	(96.52)	3.800	(99.06)	3.900
1X20	(48.26)	1.900	(50.80)	2.000	1X40	(99.06)	3.900	(101.60)	4.000

PINS: (0.635)±.025 SQ.
BRASS WIRE.
PLATED AS PER
SUBSEQUENT SHEETS

NOTES
1. FOR ASSY NUMBERS WITH FINISH OPTIONS
AND DIM'S C & D SEE SUBSEQUENT SHEETS.
2. PCB THICKNESS: (1.37-1.80)±.054-.071.



RECOMMENDED P.C. BOARD HOLE PATTERN

FOR PREVIOUS
DRAWING ISSUES
SEE MRI.

NEW RELEASE ECN E00166 10 SEPTEMBER 1990 RD	LTR	REVISIONS	DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1° INCH (METRIC) 3 PLACE ± .0004 ± .10 2 PLACE ± .004 ± .10 1 PLACE ± .25 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DESIGN DIMENSION (PRIMARY) ☒ (MM) ☐ IN. EQUIVALENT DIMENSION (SECONDARY) ☐ (MM) ☒ IN.	DRWG BY RD CHK'D BY APP'D BY SCALE 4:1	REVISE ONLY ON CAD SYSTEM		2 B 1 B SHL. REV.
					CAD/CAM FILENAME SA90627X1 DCN	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
					TITLE C-GRID III SINGLE ROW KINKED PIN HEADER		
					molex MOLEX EUROPE		SHEET NO. DATE 10F2 90/11/28
PART NO. SEE CHART		DWG NO. SDA-90627		SIZE B			

		10		9		8		7		6		5		4		3		2		1	
F		SEE CHART PART NO. DWG. NO.		SDA-90627		CIRCUIT SIZE		PLATING TYPE A PART NO.		PLATING TYPE E PART NO.		PLATING TYPE F PART NO.		KINKED PIN POSITION							
						1 X 1		90627-0121		90627-0761		90627-0921		嘴							
						1 X 2		90628-0121		90628-0761		90628-0921		SEE NOTE 1							
						1 X 3		90627-0123		90627-0763		90627-0923		嘴							
						1 X 4		↑ -0124		↑ -0764		↑ -0924		嘴							
						1 X 5		-0125		-0765		-0925		嗽							
						1 X 6		-0126		-0766		-0926		嗽							
						1 X 7		-0127		-0767		-0927		嘴							
						1 X 8		-0128		-0768		-0928		嘴							
						1 X 9		-0129		-0769		-0929		嗽							
						1 X 10		-0130		-0770		-0930		嗽							
						1 X 11		-0131		-0771		-0931		1.6 & 11							
						1 X 12		-0132		-0772		-0932		1.6 & 12							
						1 X 13		-0133		-0773		-0933		1.7 & 13							
						1 X 14		-0134		-0774		-0934		1.7 & 14							
						1 X 15		-0135		-0775		-0935		1.8 & 15							
						1 X 16		-0136		-0776		-0936		1.8 & 16							
						1 X 17		-0137		-0777		-0937		1.9 & 17							
						1 X 18		-0138		-0778		-0938		1.9 & 18							
						1 X 19		-0139		-0779		-0939		1.10 & 19							
						1 X 20		-0140		-0780		-0940		1.10 & 20							
						1 X 21		-0141		-0781		-0941		1.11 & 21							
						1 X 22		-0142		-0782		-0942		1.11 & 22							
						1 X 23		-0143		-0783		-0943		1.12 & 23							
						1 X 24		-0144		-0784		-0944		1.12 & 24							
						1 X 25		-0145		-0785		-0945		1.13 & 25							
						1 X 26		-0146		-0786		-0946		1.13 & 26							
						1 X 27		-0147		-0787		-0947		1.14 & 27							
						1 X 28		-0148		-0788		-0948		1.14 & 28							
						1 X 29		-0149		-0789		-0949		1.15 & 29							
						1 X 30		-0150		-0790		-0950		1.15 & 30							
						1 X 31		-0151		-0791		-0951		1.16 & 31							
						1 X 32		-0152		-0792		-0952		1.16 & 32							
						1 X 33		-0153		-0793		-0953		1.17 & 33							
						1 X 34		-0154		-0794		-0954		1.17 & 34							
						1 X 35		-0155		-0795		-0955		1.18 & 35							
						1 X 36		-0156		-0796		-0956		1.18 & 36							
						1 X 37		-0157		-0797		-0957		1.19 & 37							
						1 X 38		-0158		-0798		-0958		1.19 & 38							
						1 X 39		↓ -0159		↓ -0799		↓ -0959		1.20 & 39							
						1 X 40		90627-0160		90627-0800		90627-0960		1.20 & 40							
E		DIM C (±0.25) ±.00 (6.75) .266		DIM D (±0.30) ±.02 (2.90) .114																	
D																					
C																					
B																					
A																					

NOTES:		FOR PREVIOUS DRAWING ISSUES SEE MRI.		SEE SHEET I.		REVISIONS		DIMENSIONS SHOWN (METRIC) INCH		RD		REVISE ONLY ON CAD SYSTEM		SH.		REV.			
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2° INCH (METRIC) 3 PLACE ± . 2 PLACE ± . 1 PLACE ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DESIGN DIMENSION (PRIMARY) (MM) □ IN. EQUIVALENT DIMENSION (SECONDARY) (MM) □ IN.								CHK'D BY		TITLE		CADCAM FILENAME SA9062TX2 DCN		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. & SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
										APP'D BY		C-CGRID III SINGLE ROW KINKED PIN HEADER		SHEET NO. DATE		20F 90/08/11			
										SCALE		MOLEX EUROPE		PART NO. SEE CHART		DWG NO. SDA-90627		SIZE B	

7132-1283

		10		9		8		7		6		5		4		3		2		1	
--	--	----	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--