



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P8	REVISED PER ECO-17-002488	22FEB2017	RS	KR



- 1

2-6 μm TIN OVER NICKEL IN CRIMP AREA
2-6 μm Sn UBER NI IN DER CRIMPZONE
- 2

0.8 μm GOLD OVER NICKEL IN THE CONTACT ZONE
0.8 μm Au UBER NI IN DER KONTAKTZONE
3.


FOR INSULATIONS Ø 1.5-3.3 mm
FUR ISOLATIONS Ø 1.5-3.3mm GEELGNET
- 4

0.8 μm GOLD OVER 1.3 μm NICKEL ON INSIDE OF
WIRE BARREL AND THE CONTACT ZONE. OTHERWISE 1.3 μm NI
0.8 μm Au UBER 1.3 μm Ni IN DEN DRAHTCRIMP
UND KONTAKTZONEN, SORST 1.3 μm NI
- 5

DIRECTION OFF TOP OF REEL
- 6

OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI

6	OBSOLETE	-	926887-8	BRASS	5	PRETINNED
		926898-7	926898-7	BRASS	1	2
	SUPERSEDED BY 350687-6	926898-6	926887-6	PHOS BRONZE	1	2
6	OBSOLETE	926898-5	926887-5	COPPER ALLOY	PRETINNED	
	OBSOLETE	926898-4	926887-4	COPPER ALLOY	NONE	
		926898-3	926887-3	PHOS BRONZE	PRETINNED	
6	OBSOLETE	926898-2	926887-2	BRASS	4	
		926898-1	926887-1	BRASS	PRETINNED	
		LOOSE PIECE	PART-NUMBER	MATERIAL	PLATING/FINISH	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SMITH 22FEB2017	TE Connectivity				
DIMENSIONS: mm		CHK K. RANDOLPH 22FEB2017					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.2 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH ±-	APVD K. RANDOLPH 22FEB2017	NAME UNIVERSAL M-N-L STIFT DGB 0.5-2.1 mm^2 -				
		PRODUCT SPEC 108-1031					
		APPLICATION SPEC 114-1010	SIZE A2	CAGE CODE -	DRAWING NO C=926887	RESTRICTED TO -	
		MATERIAL SEE TABLE	WEIGHT -	CUSTOMER DRAWING			SCALE 5:1