

LXP-G LENSES FOR CREE XP-G LEDs



- Specially designed for Cree XLAMP XP-G series of LEDs.
- Special care taken to make a uniform white or warm white illumination.
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F). Allows use of high current and temperature conditions.
- Best available optical efficiency, more than 90%, with an extremely good cutoff of light
- Fastening to heat sink with a PU foam **adhesive tape** of automotive grade
- We advise customer to ensure the suitability and sufficiency of the bond in the end product. For example, mechanical stress, vibration and holes on the surface of the circuit board weaken the strength of the tape.
- Please check fastening details from this link:
(http://www.ledil.com/datasheets/DataSheet_TAPE.pdf)

LENS TYPES



NAME	ORDERING CODE	FWHM Angle
LXP-G REAL SPOT	FA10661_LXP-G-RS	±5.5°
LXP-G DIFFUSER	FA10663_LXP-G-D	±7.5°
LXP-G MEDIUM	FA10660_LXP-G-M	±13°
LXP-G MEDIUM ver.2	FA11451_LXP-G-M2	Coming soon
LXP-G OVAL	FA11116_LXP-G-O-90	±19° X ±10.5°
LXP-G RECTANGULAR	FA10662_LXP-G-REC	±19° x ±11.5°
LXP-G WIDE	FA10832_LXP-G-W	±23°

EULUMDAT & IES FILES AVAILABLE BY REQUEST

© Ledil Oy – PRELIMINARY - Subject to change without prior notice


MEASUREMENT DATA

Relative Intensity of FA10661_LXP-RS





© Ledil Oy – PRELIMINARY - Subject to change without prior notice


Relative Intensity of FA10663_LXP-D




Relative Intensity of FA10660_LXP-M




Relative Intensity of FA11116_LXP-O-90



Relative Intensity of FA10662_LXP-REC



Relative Intensity of FA10832_LXP-W




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Ledil Oy
Tehdaskatu 13
FIN-24100 SALO, Finland

www.ledil.com
email: ledil@ledil.com
FAX: +358-2-733 8001

2011-03-07

DRAWINGS



© Ledil Oy – PRELIMINARY - Subject to change without prior notice