

Single-Phase Monitored PDU, 3.2-3.8kW 16/20A 200-240V, 0U 70 in. Vertical Rackmount, 20 C13 and 4 C19 outlets, C20 inlet and NEMA L6-20P cable, TAA Compliant

MODEL NUMBER: PDUMNV20HV



Description

Tripp Lite Monitored PDU / Power Distribution Unit offers real-time remote monitoring of voltage, frequency and load levels via built-in network connection. PowerAlert interface supports custom notification of user-specified remote conditions via email, secure web, SNMP, Telnet or SSH interface. PDU output current consumption in amps is displayed via front panel lighted digital display and can be monitored remotely to warn of potential overloads before critical IT mains breakers trip.

Features

- 200/208/230/240V Monitored PDU with built-in web/network interface in 0U 70 in. / 178cm rackmount form factor; 20A maximum capacity (agency de-rated to 16A)
- C20 inlet supports user supplied input cabling; 10ft / 3m L6-20P power cord included
- 24 outlets (20 C13 & 4 C19)
- 0U 70in / 178cm vertical rackmount form factor
- Network interface provides PDU control and data regarding input voltage, frequency and loading information
- Digital display reports load level information in amps
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements

Highlights

- Monitored 16/20A 200-240V PDU; 0U 70in / 178cm vertical rackmount
- Reports voltage, frequency and load level via ethernet interface
- Visual current meter, Toolless button-mount installation
- C20 inlet, 10ft / 3m L6-20P power cable included
- 24 outlets (20 C13 & 4 C19) with included cord retention brackets
- Temperature, humidity and contact-closure monitoring options
- Federal Trade Agreements Act / TAA compliant for GSA schedule purchases

Applications

- Ideal for network configurations requiring a monitored PDU system

Package Includes

- Rackmount PDU
- Plug retention plates
- Rack mounting brackets
- Owner's manual



- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Included cord retention brackets
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications
- Federal Trade Agreements Act / TAA compliant for GSA schedule purchases

Specifications

General Info	
Product Group	PDUS
OVERVIEW	
PDU Type	Monitored
OUTPUT	
Output Capacity Details	3.3kW (208V input), 3.5kW (220V input), 3.7kW (230V input), 3.8kW (240V input), 3.2kW (200V input); 20A maximum (Agency de-rated to 16A continuous)
Frequency Compatibility	50 / 60 Hz
Output Nominal Voltage	200-240V nominal, single phase
Outlet Quantity / Type	20 C13, 4 C19
Outlet Type	C13; C19
INPUT	
PDU Input Voltage	200; 208; 220; 230; 240
Maximum Input Amps	20
Input Connection Type	C20 inlet accepts included L6-20P input cable. Alternate C19 input cordsets supported.
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Cord Length (ft.)	10
Input Cord Length (m)	3
Input Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Front Panel LEDs	Front panel digital display confirms power availability and PDU output current level in 1 amp increments
PHYSICAL	
Shipping Dimensions (hwd / in.)	72.5 x 4 x 6
Shipping Dimensions (hwd / cm)	184.2 x 10.2 x 15.2
Shipping Weight (lbs.)	13.5



Shipping Weight (kg)	6.1
Unit Dimensions (hwd / in.)	70 x 2.19 x 2.65
Unit Dimensions (hwd / cm)	177.8 x 5.6 x 6.7
Unit Weight (lbs.)	8.5
Unit Weight (kg)	3.9
Style	Vertical Rackmount
Form Factors Supported	0U vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
COMMUNICATIONS	
SNMP Compatibility	Pre-installed SNMPWEBCARD provides remote monitoring via web, Telnet, and SNMP management systems
CERTIFICATIONS	
Certifications	Tested to UL 60950-1 (USA, Canada), CE (International), Class A (Emissions), NOM (Mexico), RoHS compliant, TAA compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.