

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0513533000](#)
Status: **Active**
Description: 2.00mm (.079") Pitch MicroClasp™ Wire-to-Board Receptacle Housing, Positive Lock, Dual Row, 30 circuits

Documents:
[3D Model](#) [Product Specification PS-51353-003 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Crimp Housings
Series [51353](#)
Product Name MicroClasp™

Physical
Circuits (maximum) 30
Color - Resin White
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Lock to Mating Part Yes
Material - Resin Nylon
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface (in) 0.079 In
Pitch - Mating Interface (mm) 2.00 mm
Stackable No
Temperature Range - Operating -25°C to +85°C

Electrical
UL E29179

Material Info

Reference - Drawing Numbers
Product Specification PS-51353-003
Product Specification RPS-501844-001
Product Specification RPS-51353-008
Product Specification RPS-51353-009
Product Specification RPS-51353-010
Product Specification RPS-51353-013
Product Specification RPS-51353-014
Product Specification RPS-51353-016
Product Specification RPS-51353-017
Product Specification RPS-51353-018
Product Specification RPS-51353-019
Product Specification RPS-51353-020
Product Specification RPS-51353-022
Product Specification RPS-51353-024
Product Specification RPS-51353-025
Product Specification RPS-51353-026
Product Specification RPS-51353-030
Sales Drawing SD-51353-002



Series image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[51353](#) Series

Mates With
[55917](#) Vertical Header with Kinked PC Tails,
[55959](#) Right Angle Header, [501844](#) Vertical Header

Use With
[56134](#) Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION