


REV.	DATE	DESCRIPTION
A	06/05/03	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
7						DRAWN	G.R.S.	06/05/03											
6						CHECKED													
5	NUT	BRASS	NICKEL	1			ISSUED				PART DESCRIPTION								
4	FERRULE	COPPER	NICKEL	1			SHEET	1 OF 1				BNC R/A CRIMP PLUG (FOR RG-223/U, 55/U, 142A/U, 400/U)							
3	CONTACT PIN	BRASS	GOLD	1								PART NO.							
2	INSULATOR	DELIRIN	NATURAL	1								112526							
1	SHELL/BODY	BRASS	NICKEL	1															
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE		C:/112/112526.DWG		DWG. NO.		112526.DWG		REV.	A	SIZE	A	SCALE	NA