

4



3

2


1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
U	-	-	-	-	-	-



SECTION A-A



NOTES:

INSULATOR DESIGNED FOR USE WITH
4.8 QC RECEPTACLE TYCO P/N 1627099
(UTILUX PART No. H2590)

NYLON 66 GF HEAT STABILISED	INSULATOR, POST-FIT H2801B	1-1627121-2
NYLON 66 NATURAL	INSULATOR, POST-FIT H2801	1-1627121-1
MATERIAL DESC.	DESCRIPTION	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: W.RIEDE 25.4.06	tyco Tyco Electronics Corporation Electronics AUSTRALIA			
		CHK: H.THA1 01.05.06				
ALL DIMENSIONS IN mm:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD: W.RIEDE 01.06.06	NAME: INSULATOR, POST-FIT			
	DIMENSION (mm) TOLERANCE(+/-mm) LESS THAN 10 0.4 OVER 10 TO 30 0.5 OVER 30 TO 80 0.7 OVER 80 TO 250 1.0 ANGLES ±2°	PRODUCT SPEC:				
		APPLICATION SPEC:				
MATERIAL	FINISH	WEIGHT:	SIZE A3	CAGE CODE	DRAWING NO. C= 1627121	RESTRICTED TO -
-	-	-	CUSTOMER DRAWING			SCALE 5:1 SHEET 1 OF 1 REV 0

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION. HARRISBURG, PENNSYLVANIA, USA.