


REV.	DATE	ECR NO.	DESCRIPTION
NC	05/30/00	—	INITIAL RELEASE
NC	04/30/08	100012	UPDATE DRAWING FORMAT



NOTES:
1. CRIMPED FERRULE HEX CRIMP SIZE .213"

						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8					DRAWN		GRS	04/30/08							
7	FERRULE	COPPER	GOLD	1	CHECKED										
6	HEX NUT	BRASS	GOLD	1	ISSUED				PART DESCRIPTION						
5	LOCK WASHER	BRASS	GOLD	1	SHEET		1 OF 1		SMA BULKHEAD CRIMP JACK O-RING SEAL (FOR RG-58C/U, 58/U CABLE)						
4	GASKET	SILICONE	RED	1			PART NO.								
3	CONTACT PIN	BER. COPPER	GOLD	1			132280								
2	INSULATOR	PTFE	NATURAL	1			CAD FILE		DWG. NO.		REV.	SIZE	SCALE		
1	BODY	BRASS	GOLD	1			C:/132/132280.DWG		132280.DWG		A	A	NA		
DESCRIPTION		MATERIAL	FINISH	QTY											