

AVAILABLE
THROUGH
DISTRIBUTION



BOURNS®

TC86 6 mm Round Trimming Potentiometer

Features

- 6 mm Round / Single-Turn / Cermet Industrial / Open Frame
- Cross slot adjustment options
- Horizontal and vertical mounting styles
- Dust resistant/splash resistant covers
- Front and top adjust styles
- RoHS compliant¹

Electrical Characteristics


Standard Resistance Range
.....100 ohms to 1 megohm
(see standard resistance table)
Resistance Tolerance±20 % std.
(tighter tolerance available)
Absolute Minimum Resistance
≤ 500 Ohms 10 ohms max.
> 500 Ohms 2 % max. of TR
Contact Resistance Variation 5 % max.
Resolution Infinite
Adjustment Angle 240 ° ±20 °

Environmental Characteristics

Power Rating (100 VDC max.)
70 °C 0.3 watt
Temperature Range-30 °C to +85 °C
Temperature Coefficient±250 ppm/°C
Humidity 95 % RH
TRS ±5 %
Load Life 500 hours @ 70 °C
TRS ±5 %
Rotational Cycling 50 cycles
TRS ±10 %

Physical Characteristics

Torque 30-300 gf-cm
Mechanical Angle 240 ° ±20 °
Marking Part marking code
Standard Packaging 200 pcs./bag
Adjustment Tool H-90
Aqueous cleaning not recommended





OBSOLETE


Specifications are subject to change without notice.
¹RoHS Directive 2002/95/EC Jan 27 2003 including Annex.
Customers should verify actual device performance in
their specific applications. REV 09/04

Product Dimensions


Top Adjust Common Dimensions




TC86P




TC86F




Side Adjust Common Dimensions



TC86W




TC86K




DIMENSIONS: MM/(INCHES)
TOLERANCES: ±.25/(±.010) EXCEPT WHERE NOTED

TC86 – Suggested PCB Layout and Ordering Information

Suggested PCB Layout – Style F



Suggested PCB Layout – Styles K, P, W



Standard Resistance Table

Resistance (Ohms)	Resistance Code
100	101
200	201
500	501
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
50,000	503
100,000	104
200,000	204
500,000	504
1,000,000	105

Popular distribution resistance values listed in **boldface**.

How To Order

Model TC86 W - 1 - 103
 Style _____
 Standard Product Indicator _____
 Resistance Code _____

OBSOLETE

Specifications are subject to change without notice. Customers should verify actual device performance in their specific applications.