







RECOMMENDED
CABLE STRIPPING DIM'S

REV.	DATE	ECR NO.	DESCRIPTION
NC	06/10/09	XXXXXX	INITIAL RELEASE



1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .043"
OR CONTACT PIN TO SOLDER

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING					APPROVALS		DATE		Amphenol Connex										
					DRAWN M.ZHANG		06/10/09												
					CHECKED				PART DESCRIPTION BNC CRIMP JACK (FOR BELDEN 1855A CABLE)										
					ISSUED														
					SHEET 1 OF 1														
					PART NO.				112989										
					CAD FILE		C:/CONNEX/112989.DWG		DWG. NO.		112989.DWG		REV.	NC	SIZE	A	SCALE	NA	
4	FERRULE	COPPER	NICKEL	1															
3	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1															
2	INSULATOR	PTFE	NATURAL	1															
1	BODY	BRASS	NICKEL	1															
DESCRIPTION		MATERIAL		FINISH	QTY														