



DO NOT SCALE

DIMENSIONS IN mm

METRIC

THIRD ANGLE


PROJECTION



NOTES :

1 PLATING : 2,54 μ m SnPb (93/7) MIN. ALL OVER
UNDERLAYER 1,25 μ m Ni ALL OVER.

2 MATERIAL THICKNESS 0,8 mm .



RECOMMENDED BOARD
LAYOUT

PLATED THROUGH HOLE SPECIFICATION	
DRILLED HOLE	1,6 $\pm$ 0,025
Cu- THICKNESS	25-75 μ m
SnPb-THICKNESS	4-10 μ m
FINISHED HOLE	1,39 $^{+0,15}_{-0,18}$
FINISHED HOLE (AFTER REFLOW)	1,36 $^{+0,15}_{-0,18}$

1
FINISH

PHOSPHORBRONZE

216905-1

MATERIAL

PARTNUMBER

CUSTOMER
DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

AMP

AMP-HOLLAND B.V.

's-Hertogenbosch, The Netherlands.

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION - 19

© COPYRIGHT 19- BY AMP-HOLLAND B.V.

ALL INTERNATIONAL RIGHTS RESERVED.

AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR
PATENTS PENDING.

DR.
S.MEEUWSEN

DATE
15-02-90

WIRE RANGE

NAME

REV. DATE
D M Y

CHK.
R.V.LOKVEN

DATE
03-04-90

INSUL. RANGE

POWER TERMINAL FOR
POSITIVE LOCK RECEPTACLE
(1,6 P.C.BOARD THICKNESS)

19 02 91

APP.
L.V.SOEST

DATE
03-04-90

SIZE
A4

SHEET
1 OF 1

DWG. No.

C-216905

REV. LTR.
B