


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	C	REVISED PER ECN-25-354023	18NOV2025	SN DR



- 1 WIRE RANGE IS FOR 1/0 AWG STANDARD WIRE CROSS SECTIONAL AREA RANGE: 83,700-119,500 CMA, STRANDED WIRE.
 - 2 TERMINAL BODY MATERIAL THK IS 1.778±0.076 [0.070±0.003].
 - 3 RECOMMENDED OPERATING TEMP -65°C [-85°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING
 - 4 HEAT SHRINK TUBING SHELF LIFE OF 144 MONTHS FROM DATE CODE ON LABEL
- △5 TERMINAL BODY PRODUCT SPECIFICATION 108-32046. APPLICATION SPECIFICATION 114-2162.

1	1-1196717-9	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 15.88[0.625]MIN IDX44.45±3.05[1.75±0.12] RT555-5/8-0-SP
1	323180	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [0.000300] MIN EXT THK PER SAE AMS QQ-N-290
QTY	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 08DEC09	STE TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK T MICHELUTTI 08DEC09		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHELUTTI 08DEC09	NAME	
0 PLC ± -		PRODUCT SPEC	HEAT RESISTANT TERMINAL KIT	
1 PLC ± -		APPLICATION SPEC	WIRE SIZE: 1/0 AWG	
2 PLC ± -			SIZE	CAGE CODE
3 PLC ± 0.127 [0.005]			A3	00779
4 PLC ± -			DRAWING NO	RESTRICTED TO
ANGLES ± 1°			C-696647	-
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	SCALE 3:1	SHEET 1 OF 1
CUSTOMER DRAWING			REV C	