





REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1876	A	RELEASED	EO	07/25/06	SA	07/25/06	HO	07/25/06



PANEL CUTOUT



MATERIAL:

Shell: Steel, Tin Plated
Insulator: PBT +30% Fiber Glass, Black
UL94V-0 Rated
Contact: Brass, Stamped-Pin
Gold-Plated on Contact Area
Tin-Plated on Solder Cup

SPECIFICATIONS:

Current Rating: 5 Amps
Contact Resistance: 15 miliohms Max.
Insulator Resistance: 1000 Megohms Min.
Voltage: 500 VAC for 1 Minute
Temperature: -50°C to +100°C

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

Unless Otherwise Specified

.X ± 0.35 [0.014]
.XX ± 0.15 [0.006]

DRAWN BY:

EKLAS ODISH

CHECKED BY:

SAMI ALNADI

APPROVED BY:

HISHAM ODISH

DATE:

07/25/06

DATE:

07/25/06

DATE:

07/25/06

DRAWING TITLE:

26 Pin High Density D-Sub Socket

SIZE

A

DWG. NO.

SPC15191

ELECTRONIC FILE

79K4794.DWG

REV

A

SCALE: NTS

U.O.M.: mm [INCHES]

SHEET: 1 OF 1