

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2000

© COPYRIGHT 2000

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

GW

-

P

LTR

DESCRIPTION

DATE

DWN

APVD



A

-

05APR2001

CM

KM




2:1

2. Mating face according to DIN 47297 and CECC 22230

1 Supplied as loose part

V23614-B263-P76	9-1393670-2	02Y(ST)CY 0.45/2.0	2.15	5.2	Dielectric	PTFE	
					Outer Con.	Cu Be	1µm Au min in contact area
					Center Con.	Brass	1µm Au min in contact area
V23614-B202-P25	9-1393670-1	ST 214	3.8	7.93	Dielectric	PTFE	
					Outer Con.	Cu Be	1µm Au min in contact area
					Center Con.	Brass	1µm Au min in contact area
V23614-A263-P76	7-1393670-0	02Y(ST)CY 0.45/2.0	2.15	5.2	Dielectric	PTFE	
					Outer Con.	Cu Be	1µm Au min in contact area
					Center Con.	Brass	1µm Au min in contact area
V23614-A263-P34A	5-1419149-0	Pirelli s353/164	2.35	6.4	Dielectric	PTFE	
					Outer Con.	Cu Be	1µm Au min in contact area
					Center Con.	Brass	1µm Au min in contact area
V23600-A263-P71	2-1393670-6	RG179 B/U RG316/U	1.7	3.6	Dielectric	PTFE	
					Outer Con.	Cu Be	1µm Au min in contact area
					Center Con.	Brass	1µm Au min in contact area
Old Nr	Tyco Nr	Cable type	Dim a	Dim b	Description	Material	Plating



1:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:



MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±

FINISH

-

DWN MOROBE 2APR2001

CHK MATTHEEUS 3APR2001

APVD BOZZER 5APR2001

PRODUCT SPEC

108-71032

APPLICATION SPEC

114-71010

WEIGHT

-

tyco
ElectronicsTyco Electronics
Oostkamp - Belgium

NAME

CABLE ANGLE PLUG
1.0/2.3 50/75 Ohm
-

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-2-1393670-6

RESTRICTED TO

-

SCALE 10/1

SHEET 1 OF 1

REV A