






Technical drawing showing a cross-section of a mechanical assembly. The drawing includes the following dimensions and features:

- Overall width: 3.77 [$.148$]
- Feature 8: A triangular feature with a width of 2.72 [$.107$].
- Feature 7: A triangular feature with a width of 2.54 [$.100$] TYP.
- Feature 5: A triangular feature with a width of 2.92 ± 0.25 [$.115 \pm .010$] TYP.
- Feature 4: A feature with a width of 4 ± 0.25 [$0 \pm .010$].
- Feature 3: A feature with a width of 2.54 [$.100$] TYP.
- Feature 2: A feature with a width of 2.92 ± 0.25 [$.115 \pm .010$] TYP.
- Feature 1: A feature with a width of 2.54 [$.100$] TYP.




SUPERSEDED BY 7-534206-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002		 TE Connectivity	
		CHK J.OLSON 06NOV02			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME J.OLSON 06NOV02 RECEPTACLE ASSEMBLY, MOD II, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		APVD J.OLSON 06NOV02 PRODUCT SPEC 108-25022			
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC 114-25018			
MATERIAL		WEIGHT -			
		FINISH		SIZE A2	
		CUSTOMER DRAWING		CAGE CODE 00779	
				DRAWING NO C-534206	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 of 2	
				REV R7	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

	$\triangle_{1,1}$	99.06[3.900]	101.60[4.000]	80	$\triangle_{1,2}$	9-534206-0
	$\triangle_{1,1}$	96.52[3.800]	99.06[3.900]	78	$\triangle_{1,2}$	8-534206-9
	$\triangle_{1,1}$	93.98[3.700]	96.52[3.800]	76	$\triangle_{1,2}$	8-534206-8
	$\triangle_{1,1}$	91.44[3.600]	93.98[3.700]	74	$\triangle_{1,2}$	8-534206-7
	$\triangle_{1,1}$	88.90[3.500]	91.44[3.600]	72	$\triangle_{1,2}$	8-534206-6
	$\triangle_{1,1}$	86.36[3.400]	88.90[3.500]	70	$\triangle_{1,2}$	8-534206-5
	$\triangle_{1,1}$	83.82[3.300]	86.36[3.400]	68	$\triangle_{1,2}$	8-534206-4
	$\triangle_{1,1}$	81.28[3.200]	83.82[3.300]	66	$\triangle_{1,2}$	8-534206-3
	$\triangle_{1,1}$	78.74[3.100]	81.28[3.200]	64	$\triangle_{1,2}$	8-534206-2
	$\triangle_{1,1}$	76.20[3.000]	78.74[3.100]	62	$\triangle_{1,2}$	8-534206-1
	$\triangle_{1,1}$	73.66[2.900]	76.20[3.000]	60	$\triangle_{1,2}$	8-534206-0
	$\triangle_{1,1}$	71.12[2.800]	73.66[2.900]	58	$\triangle_{1,2}$	7-534206-9
	$\triangle_{1,1}$	68.58[2.700]	71.12[2.800]	56	$\triangle_{1,2}$	7-534206-8
	$\triangle_{1,1}$	66.04[2.600]	68.58[2.700]	54	$\triangle_{1,2}$	7-534206-7
	$\triangle_{1,1}$	63.50[2.500]	66.04[2.600]	52	$\triangle_{1,2}$	7-534206-6
	$\triangle_{1,1}$	60.96[2.400]	63.50[2.500]	50	$\triangle_{1,2}$	7-534206-5
	$\triangle_{1,1}$	58.42[2.300]	60.96[2.400]	48	$\triangle_{1,2}$	7-534206-4
	$\triangle_{1,1}$	55.88[2.200]	58.42[2.300]	46	$\triangle_{1,2}$	7-534206-3
	$\triangle_{1,1}$	53.34[2.100]	55.88[2.200]	44	$\triangle_{1,2}$	7-534206-2
	$\triangle_{1,1}$	50.80[2.000]	53.34[2.100]	42	$\triangle_{1,2}$	7-534206-1
	$\triangle_{1,1}$	48.26[1.900]	50.80[2.000]	40	$\triangle_{1,2}$	7-534206-0
	$\triangle_{1,1}$	45.72[1.800]	48.26[1.900]	38	$\triangle_{1,2}$	6-534206-9
	$\triangle_{1,1}$	43.18[1.700]	45.72[1.800]	36	$\triangle_{1,2}$	6-534206-8
	$\triangle_{1,1}$	40.64[1.600]	43.18[1.700]	34	$\triangle_{1,2}$	6-534206-7
	$\triangle_{1,1}$	38.10[1.500]	40.64[1.600]	32	$\triangle_{1,2}$	6-534206-6
	$\triangle_{1,1}$	35.56[1.400]	38.10[1.500]	30	$\triangle_{1,2}$	6-534206-5
	$\triangle_{1,1}$	33.02[1.300]	35.56[1.400]	28	$\triangle_{1,2}$	6-534206-4
	$\triangle_{1,1}$	30.48[1.200]	33.02[1.300]	26	$\triangle_{1,2}$	6-534206-3
	$\triangle_{1,1}$	27.94[1.100]	30.48[1.200]	24	$\triangle_{1,2}$	6-534206-2
	$\triangle_{1,1}$	25.40[1.000]	27.94[1.100]	22	$\triangle_{1,2}$	6-534206-1
	$\triangle_{1,1}$	22.86[.900]	25.40[1.000]	20	$\triangle_{1,2}$	6-534206-0
	$\triangle_{1,1}$	20.32[.800]	22.86[.900]	18	$\triangle_{1,2}$	5-534206-9
	$\triangle_{1,1}$	17.78[.700]	20.32[.800]	16	$\triangle_{1,2}$	5-534206-8
	$\triangle_{1,1}$	15.24[.600]	17.78[.700]	14	$\triangle_{1,2}$	5-534206-7
	$\triangle_{1,1}$	12.70[.500]	15.24[.600]	12	$\triangle_{1,2}$	5-534206-6
$\triangle_{9,1}$	$\triangle_{1,1}$	10.16[.400]	12.70[.500]	10	$\triangle_{1,2}$	5-534206-5
$\triangle_{9,2}$	$\triangle_{1,1}$	7.62[.300]	10.16[.400]	8	$\triangle_{1,2}$	5-534206-4
$\triangle_{9,3}$	$\triangle_{1,1}$	5.08[.200]	7.62[.300]	6	$\triangle_{1,2}$	5-534206-3
$\triangle_{9,4}$	$\triangle_{1,1}$	2.54[.100]	5.08[.200]	4	$\triangle_{1,2}$	5-534206-2
$\triangle_{9,5}$	$\triangle_{1,1}$	-	2.54[.100]	2	$\triangle_{6,1}\triangle_{1,2}$	5-534206-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002 CHK J.OLSON 06NOV02		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± ±		NAME RECEPTACLE ASSEMBLY, MOD II, DOUBLE ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
		APVD J.OLSON 06NOV02 PRODUCT SPEC 108-25022 APPLICATION SPEC 114-25018		SIZE A2	
MATERIAL 		FINISH  		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C=534206	
		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 4:1	
				SHEET 2 of 2	
				REV R7	