

(3,81 mm) .150"



UPS-04-01-01-L-RA-LC

UPS-08-04.0-01-L-V



UPS-04-07.0-03-L-PV

UPS SERIES

DUAL LEAF 20 A POWER SOCKET

SPECIFICATIONS

For complete specifications see www.samtec.com?UPS

Insulator Material:

Black LCP

Contact Material:

BeCu

Plating:

Sn or Au over 50µ" (1.27 µm) Ni

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

Voltage Rating:

375 VAC/530 VDC

RoHS Compliant:

Yes

Lead-Free Solderable:

Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




Mates with:
UPT

UPT-V/UPS-V	
PINS	CURRENT RATING (PER CONTACT)
1	23 A
2	18.6 A
3	17.5 A
4	16.7 A
ALL	14 A
-L PLATING	

UPT-RA/UPS-RA	
PINS	CURRENT RATING (PER CONTACT)
1	23.5 A
2	20.1 A
3	16.9 A
4	15.5 A
ALL	13.3 A
-L PLATING	

Dual leaf blade contacts

Up to 8 Power Pins



Optional Locking Clip

(3,81 mm) .150" pitch

Vertical, Right Angle or Press Fit



• Locking clip option

ALSO AVAILABLE (MOQ Required)

- Solder leads for (2,36 mm) .093" thick board
- Contact Samtec.


TOOLING

Press fit tooling available.
Contact Samtec.

UPS	POWER PINS	LEAD STYLE	TAIL LENGTH	PLATING OPTION	TAIL	OTHER OPTION
-02, -04, -06, -08		-01 = RA only -04.0 = (04,0 mm) .157" (-V & -PV only) -07.0 = (07,0 mm) .276" (-V & -PV only)	-01 = Use with (1,60 mm) .062" Thick PCB (-V & -RA only) -03 = Use with (1,60 mm) .062" Thick PCB (-PV only)	-L = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail -T = Matte Tin (-RA option only)	-V = Vertical (Not available with -T plating) -RA = Right Angle -PV = Press Fit, Vertical	-LC = Locking Clip (Manual placement required) Not available with -PV option

LEAD STYLE	A	B
-04.0	(3,75) .148	(6,75) .266

LEAD STYLE	A	B
-04.0	(3,75) .148	(6,75) .266
-07.0	(6,75) .266	(9,75) .384



MATED HEIGHT*	
UPS LEAD STYLE	UPT LEAD STYLE
-03.0	(7,00) .276
-04.0	(7,00) .276
-07.0	(10,00) .394

*Processing conditions will affect mated height.

Note: Some sizes, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685