

Honeywell Sensing and Control



Home > Products > Conductive Plastic Potentiometers > 380 > Product Page

380C31MEG



Actual product appearance may vary.

380 Series Industrial Potentiometer, Conductive Plastic Element, Solder lug Terminals, 2 W Power Rating, 1 MΩ Resistance Value

▼ Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

Features

Robust nickel-plated brass shaft and bushings
Conductive plastic element
Linear taper
100,000 cycle rotational life

Potential Applications

Manual controls (throttle, joystick)
Electric vehicles
Personal mobility
Off-road vehicles
Welding and heating
Telecommunications

Description

The 380 Series is a robust 2 watt potentiometer that offers the advantages of a conductive plastic element and a 100,000 cycle rotational life. Special tapers and element designs available on a special order.

Supporting Documentation



[Accessory: Knobs and Dial Plate](#)

Product Specifications	
Potentiometer Type	Industrial
Element Type	Conductive Plastic
Terminal	Solder lug
Power Rating	2 W
Resistance Value	1 MΩ
Resistance Tolerance	± 10 %
Linearity	± 5 %
Bushing Thread	9,53 mm [0.375 in] x 32 NEF-2A
Bushing Length	9,53 mm [0.375 in]
Bushing Type	Standard
Shaft Diameter	6,35 mm [0.25 in]
Shaft Length	22,23 mm [0.875 in]
Shaft Ending	Slotted
Body	27.8 mm [1.094 in] diameter max.

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

Product Search

Part number search:

Use (*) to expand search

→ Specification Search

	except at terminal standoff
Electrical Taper	Linear
Operating Temperature	-55 °C to 120 °C [-67 °F to 248 °F]
Working Voltage (Max.)	500 V
Rotational Life	100000 cycles
Mechanical Rotation	312°
Availability	Global
Series Name	380
UNSPSC Code	4111363300
UNSPSC Commodity	4111363300 Potentiometers

[Terms & Conditions](#) | [Privacy Statement](#) | [Site Map](#)