

Digitale Bügelmeßschraube

mit HITEC Datenausgang

DIN 863/1

Ablese Teile mattverchromt

HM-Messflächen

einschließlich Etui

Funktionen:

on/off, mm/inch, hold,

ABS/INC, Tol

> mm <	 mm	 inch	 mm	No.	€	
0 - 25	0,001	0,00005	6,5	190-00		
25 - 50	0,001	0,00005	6,5	190-01		
50 - 75	0,001	0,00005	6,5	190-02		
75 - 100	0,001	0,00005	6,5	190-03		

Digital micrometer

with HITEC data output

DIN 863/1

satin chromed reading parts

carbide tipped

individually packed

Micromètres digitaux

avec sortie de données HITEC

DIN 863/1

vernier et échelle chromés mats

surfaces de mesure en carbure

emballés à l'unité



Digitale Bügelmeßschraube

mit HITEC Datenausgang

DIN 863/1

HM-Messflächen

einschließlich Etui

Funktionen:

on/off, mm/inch, hold,

ABS/INC, Tol

> mm <	 mm	 inch	 mm	No.	€	
0 - 25	0,001	0,00005	6,5	200-39		
25 - 50	0,001	0,00005	6,5	200-49		
50 - 75	0,001	0,00005	6,5	200-55		
75 - 100	0,001	0,00005	6,5	200-56		

Digital micrometer

with HITEC data output

DIN 863/1

carbide tipped

individually packed

Micromètres digitaux

avec sortie de données HITEC

DIN 863/1

surfaces de mesure en carbure

emballés à l'unité



Digitale Bügelmeßschraube spritzwasserfest

mit HITEC Datenausgang

DIN 863/1

HM-Messflächen

einschließlich Etui

Funktionen:

Zero, mm/inch

> mm <	 mm	 inch	 mm	No.	€	
0 - 25	0,001	0,00005	6,5	200-57		
25 - 50	0,001	0,00005	6,5	200-58		

Digital micrometer water resistant

with HITEC data output

DIN 863/1

carbide tipped

individually packed

Micromètres digitaux imperméables

avec sortie de données HITEC

DIN 863/1

surfaces de mesure en carbure

emballés à l'unité



> mm <



Messbereich

Ablese mm / inch

Spindel

Range

Reading mm / inch

Spindle diam.

Capacité

Lecture mm / inch

Diam. broche