




Features

- Recommended for reflow soldering
- Rotor design compatible with pick and place and automatic adjustment equipment
- 3 mm size meets EIA/EIAJ standard trimmer footprint
- RoHS compliant* - see [processing information](#) on RoHS compliant surface mount trimmers

- For trimmer applications/processing guidelines, [click here](#)

TC33 - 3 mm SMD Trimpot® Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range 100 ohms to 1 megohm
(see standard resistance table)
Resistance Tolerance $\pm 25\%$ std.
Absolute Minimum Resistance
≤ 1 K Ohms 20 ohms max.
> 1 K Ohms 2 % max. of TR
Contact Resistance Variation 5 % max.
Resolution Essentially infinite
Adjustment Angle 200 ° min.

Environmental Characteristics

Power Rating (50 VDC max.)
70 °C 0.1 watt
Temperature Range -40 °C to +100 °C
Temperature Coefficient ± 250 ppm/°C
Humidity +40 °C, 95 %RH
TRS max. $\pm 5\%$
Load Life
..... @ 70 °C rated power 1000 hours
TRS $\pm 5\%$

Rotational Cycling
..... 20 cycles, TRS $\pm 10\%$

Physical Characteristics

Torque 0.98-11.76 mN-m max.
Mechanical Angle Continuous
Marking Part marking code
Standard Packaging ... 2000 pcs./7 " reel
Adjustment Tool H-90

Aqueous cleaning not recommended.

How To Order


TC33 B - 1 - 103 E

Model _____
Style _____
Standard Product Indicator _____
TC33B:
-1 = Single Slot Bottom Adjust
TC33X:
-1 = Continuous Rotation
-2 = Rotational Stop
Resistance Code _____
Embossed Tape Designator _____
E = 2000 pcs./7 " Reel (B Style)
E = 2500 pcs./7 " Reel (X Style)
G = 9000 pcs./13 " Reel (X Style)

*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011. Specifications are subject to change without notice. The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.



Product Dimensions

TC33X-1




Mounting Note:
The gray area can be used to apply cement to hold the unit in place during board processing, if required.

Recommended Land Pattern




TC33X-2



Mounting Note:
The gray area can be used to apply cement to hold the unit in place during board processing, if required.

Recommended Land Pattern



DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$

TOLERANCES: $\pm \frac{0.3}{(.010)}$ EXCEPT WHERE NOTED

BOURNS®

"Trimpot" is a registered trademark of Bourns, Inc.
Specifications are subject to change without notice.
It can and do vary in different applications and actual
device performance may vary over time.