

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	—		B	REV PER 0S14-0113-03	07APR03	KW	KW

D

C

B


A

D

C



B

A



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.08 [.003]

- 1 BRASS PER ASTM-B-16
- 2 PTFE PER ASTM-D-1710
- 3 BERYLLIUM COPPER PER ASTM-B-196
- 4 GOLD PLATE PER MIL-G-45204



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	—
1 PLC	±	—
2 PLC	±	0.15 [.006]
3 PLC	±	—
4 PLC	±	—
ANGLES	±	5°
FINISH	—	—

APPROVALS:

DWN	RMF	21NOV01
CHK	RMF	21NOV01
APVD	RMF	21NOV01

PRODUCT SPEC
108-2084

APPLICATION SPEC
—

WEIGHT
0.45g/.016oz

CUSTOMER DRAWING

Tyco Electronics Corporation
Middletown, PA 17057

NAME
MMCX JACK, RIGHT ANGLE, PCB

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1408151

RESTRICTED TO
—

SCALE
20:1

SHEET
1

OF
1

REV
B

1408151

1408151-1

PART NUMBER