



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00		D2	REVISED PER ECO-11-005033	25MAR11	RK	HMR

D

C


B

A




1. MATERIAL: HOUSING – NYLON, COLOR: BLACK, UL 94V–0.
OVERMOLDED TERMINAL ARRAY – PBT, BROWN.
TERMINALS – 0.33[.013] THICK PHOS BRONZE PLATED WITH 1.27 μ m[.000050] MINIMUM HARD GOLD IN LOCALIZED AREA AND 3.81 μ m[.000150] MINIMUM MATTE TIN IN SOLDER AREA OVER 1.27 μ m[.000050] MINIMUM NICKEL UNDERPLATE.
SHIELD – 0.254[.010] THICK COPPER ALLOY PLATED WITH 1.27 μ m[.000050] MINIMUM NICKEL AND 2.03 μ m [0.000080] MINIMUM HOT TIN DIP ON PCB GROUND TABS.

- 2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
- 3 SAME AS NOTE 1 EXCEPT OVERMOLDED TERMINAL ARRAY – HTN, NATURAL.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE (TOP)
SCALE 4:1

4] [4] OBSOLETE	2.54[.100]	3.05[.120]	NONE	NONE	1-5406203-2
	3.56[.140]	3.94[.155]	(A) (B) (C)	ALL THREE	5406203-3
	3.56[.140]	3.94[.155]	(B)	(1) MIDDLE	-5406203-2-
	3.56[.140]	3.94[.155]	NONE	NONE	5406203-1
	DIM. Z	DIM. A	HOLES USED	NO. OF REAR TABS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SPRINKLE/LA.MAYER CHK J.WESTMAN APVD S.FLICKINGER PRODUCT SPEC 108-1163-2 APPLICATION SPEC 114-2048 WEIGHT -	01JUNE2005 01JUNE2005 01JUNE2005	 TE Connectivity				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.01] 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -	NAME		MODULAR JACK ASSEMBLY, 4 PORT, 8 POSITION, SHIELDED, REVERSE PANEL GROUND TABS, CATEGORY 5				
	MATERIAL SEE NOTE 1 & 3	FINISH SEE NOTE 1 & 3	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
			A2	00779	C-5406203	-		
CUSTOMER DRAWING			SCALE	2:1	SHEET	1 OF 1	REV	D2