

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		P1	REVISED PER ECO-11-005033	21MAR11	RK	HMR

- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: HOUSING-POLYCARBONATE,CLEAR.
TERMINAL-0.36[.014] THICK PHOSPHOR BRONZE PLATED WITH 1.27μm[.000050] THICK GOLD IN LOCALIZED GOLD PLATE AREA, GOLD FLASH OVER THE REMAINDER, OVER 2.54μm[.000100] THICK NICKEL UNDERPLATE.
- 3

PLUG WILL ACCEPT 24 OR 26 AWG SOLID WIRE HAVING AN INSULATION DIAMETER RANGE OF 0.89-0.99[.035-.039] AND A MAXIMUM OVAL CABLE JACKET OF 2.29 X 6.61 [.09 X .260].
- 4


TERMINATED DIMENSION 6.15[.242] MAXIMUM.
- 6

1000 ASSEMBLIES PER PACKAGE.
- 7



100 ASSEMBLIES PER PACKAGE.
- 8

25 ASSEMBLIES PER PACKAGE
- 9

REELED PRODUCT ON STRIP DOES NOT HAVE VOID CORING ILLUSTRATED ON THIS DRAWING.



OBSOLETE	<div>8</div> <div>3</div>	5-555042-4
	<div>7</div> <div>3</div>	5-555042-3
	<div>6</div> <div>3</div>	5-555042-2
	REELED <div>3</div> <div>9</div>	555042-1
	PACKAGED	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	12DEC2007	<div><div></div><div>TE Connectivity</div></div>		
		CHK	12DEC2007			
		APVD	12DEC2007	NAME		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
			108-1163			
	0 PLC ± -		APPLICATION SPEC			
	1 PLC ± -					
	2 PLC ± -		114-6016			
	3 PLC ± -					
MATERIAL	4 PLC ± -		SIZE			
	ANGLES ± -		CAGE CODE			
FINISH		WEIGHT			DRAWING NO	RESTRICTED TO
-		-			A2 00779 C-555042	-
CUSTOMER DRAWING				SCALE	SHEET	REV
				4:1	1 of 1	P1