


## Performance Data

(Typical values for batteries stored at +25 °C for one year)


|                                   |                          |
|-----------------------------------|--------------------------|
| System                            | Lithium Thionyl Chloride |
| Nominal voltage                   | 3.6 V                    |
| Nominal capacity                  | 2.2 Ah                   |
| Nominal current                   | 2 mA                     |
| Max. continuous discharge current | 60 mA                    |
| Pulse current capability          | 140 mA                   |
| Anode surface area                | 14 cm <sup>2</sup>       |
| Lithium content                   | 0.65 g                   |
| Weight                            | 18 g                     |
| Volume                            | 8 cm <sup>3</sup>        |
| Temperature range                 | -55 °C ... +85 °C        |




## Typical Discharge Curves at +25 °C




## Available Capacity




## Operating Voltage




## Pulse Discharge Characteristics at +25 °C




### SL-760/S




### SL-760/T




### SL-760/P



### SL-760/PR



### SL-760/PT



## Available Terminations

| Termination              | Catalogue No. |
|--------------------------|---------------|
| SL-760/S Standard        | 11 1 07601 00 |
| SL-760/T Tags            | 11 1 07602 00 |
| SL-760/P Pins            | 11 1 07603 00 |
| SL-760/PR Pins radial    | 11 1 07606 00 |
| SL-760/PT Polarized tags | 11 1 07608 00 |



**WARNING:**  
Fire, explosion, and severe burn hazard. Do not recharge, disassemble, heat above 100 °C, incinerate, or expose contents to water.