

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

FT

0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	P1	REVISED PER ECO-09-020935	05SEP09	KK	AEG

LENGTH MIN

17.5[.69]

STYLE C

(STRIP)

17.5[.69]

15°

STYLE B

(FREE DIA)

NOTES:

1. FINISH: GOLD PLATE 10uIN MINIMUM.

2. FINISH: SILVER PLATE 200 uIN MINIMUM.

3. FINISH: NICKEL PLATE 40 uIN MINIMUM.

4. FINISH: NICKEL PLATE 100 uIN MINIMUM.

5.

6.

7.

8 NESTED AND WELDED 13 AND 14 LOUVERED BAND.

9.

10.

11. PLATING NOTES ARE TO BE INTEREPRETED AS FOLLOWS:
6-8 AS 6 OVER 8.

12. PRODUCT IS SOLD BY THE FOOT. MINIMUM ORDER LENGTH IS 3 FEET.

13 PRELIMINRY PART NUMBER.

14 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

14	OBSOLETE	[.72]	B	[.050]	BeCu	19.7[.775]		2-3	23	0.15[.006]	--	5-192007-1
		[.72]	B	[.052]	BeCu	19.7[.775]		2-3	23	0.20[.008]	--	5-192007-0
		-	C	[.052]	BeCu	-	NOTE 12	2-3	-	0.20[.008]	--	4-192007-9
		[.50]	8 B	--	BeCu	12.7[.500]		PREPL	8 27	0.10[.004]	--	4-192007-8
		[1.42]	B	[.048]	BeCu	38.1[1.500]		UNPL	45	0.08[.003]	--	4-192007-7
		[1.04]	B	[.048]	BeCu	28.5[1.121]		UNPL	33	0.08[.003]	--	4-192007-6
		[.82]	B	[.048]	BeCu	22.2[.875]		UNPL	26	0.08[.003]	--	4-192007-5
		[1.42]	B	[.050]	BeCu	38.1[1.500]		2-3	45	0.15[.006]	--	4-192007-4
												4-192007-3
		[1.71]	B	[.050]	BeCu	44.4[1.750]		2-3	54	0.15[.006]	01305	4-192007-2
		[1.42]	B	[.048]	BeCu	38.1[1.500]		2-3	45	0.08[.003]	01284	4-192007-1
		[1.39]	B	[.050]	BeCu	34.9[1.375]		2-3	44	0.10[.004]	01307	4-192007-0
		[1.32]	B	[.052]	BeCu	34.9[1.375]		2-3	42	0.20[.008]	01196	3-192007-9
		[1.32]	B	[.050]	BeCu	34.9[1.375]		2-3	42	0.15[.006]	01309	3-192007-8
		[1.07]	B	[.050]	BeCu	28.6[1.129]		2-3	34	0.15[.006]	01301	3-192007-7
		[1.04]	B	[.048]	BeCu	28.5[1.121]		2-3	33	0.08[.003]	01285	3-192007-6
		[1.00]	B	[.050]	BeCu	27.1[1.068]		2-3	32	0.15[.006]	01263	3-192007-5
											01187	3-192007-4
											01201	3-192007-3
		[.94]	B	[.052]	BeCu	25.4[1.000]		2-3	30	0.20[.008]	01178	3-192007-2
		[.94]	B	[.050]	BeCu	25.4[1.000]		2-3	30	0.15[.006]	01177	3-192007-1
		[.94]	B	[.050]	BeCu	25.4[1.000]		UNPL	30	0.15[.006]	01240	3-192007-0
		[1.70]	B	[.050]	BeCu	22.2[.875]		2-3	26	0.15[.006]	01170	2-192007-9
		[.78]	B	[.050]	BeCu	22.2[.875]		2-3	25	0.15[.006]	01169	2-192007-8
		[.81]	B	[.050]	BeCu	22.2[.875]		2-3	26	0.10[.004]	01276	2-192007-7
		[.81]	B	[.048]	BeCu	22.2[.875]		2-3	26	0.08[.003]	01302	2-192007-6
		[.69]	B	[.052]	BeCu	19[.750]		2-3	22	0.20[.008]	01318	2-192007-5
		[.65]	B	[.050]	BeCu	17.4[.687]		2-3	21	0.15[.006]	01150	2-192007-4
		[.56]	B	[.050]	BeCu	15.9[.625]		2-3	18	0.15[.006]	01298	2-192007-3
		[.53]	B	[.052]	BeCu	15.7[.620]		2-3	17	0.20[.008]	01313	2-192007-2
											01146	2-192007-1
		--	C	[.050]	BeCu	--	NOTE 12	1-3	--	0.15[.006]	--	2-192007-0
		[.53]	B	[.050]	BeCu	15.7[.620]		2-3	17	0.15[.006]	01145	1-192007-9
		[.53]	B	[.050]	BeCu	15.7[.620]		UNPL	17	0.15[.006]	01241	1-192007-8
		[.50]	B	[.050]	BeCu	12.7[.500]		1-3	14	0.15[.006]	01290	1-192007-7
		[.50]	B	[.050]	BeCu	12.7[.500]		4	14	0.15[.006]	01291	1-192007-6
		[.50]	B	[.050]	BeCu	12.7[.500]		2-3	14	0.15[.006]	01138	1-192007-4
		[.50]	B	[.050]	BeCu	12.7[.500]		UNPL	14	0.15[.006]	01235	1-192007-3
		[.50]	B	[.046]	BeCu	12.7[.500]		UNPL	14	0.08[.003]	01296	1-192007-2
		[.43]	B	[.050]	BeCu	11.1[.437]		2-3	12	0.15[.006]	01133	1-192007-1
		[.34]	B	[.050]	BeCu	7.9[.312]		2-3	9	0.15[.006]	01115	1-192007-0
		[.30]	B	[.050]	BeCu	7.9[.312]		2-3	8	0.15[.006]	01119	192007-9
		--	C	[.050]	BeCu	--	4.90 IN	2-3	49	0.15[.006]	01038	192007-8
		--	C	[.050]	BeCu	--	NOTE 12	2-3	--	0.15[.006]	01010	192007-7
		--	C	[.050]	BeCu	--	66 FT	UNPL	--	0.15[.006]	--	192007-6
		--	C	[.050]	BeCu	--	66 FT	UNPL	--	0.15[.006]	01019	192007-5
		--	C	[.050]	BeCu	--	66 FT	2-3	--	0.10[.004]	01016	192007-4
		--	C	[.050]	BeCu	--	66 FT	UNPL	--	0.10[.004]	01018	192007-3
		--	C	[.046]	BeCu	--	66 FT	2-3	--	0.08[.003]	01000	192007-2
		--	C	[.046]	BeCu	--	NOTE 12	UNPL	--	0.08[.003]	01024	192007-1
(FREE DIA)	STYLE	LH	MAT'L	MATING PIN Ø REF	LENGTH	PLATING	NUM LOUV	MAT'L THK	REF	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.5[.02]
3 PLC ± 0.25[.010]
4 PLC ± -
ANGLES ± -
FINISH SEE TABLE

MATERIAL
SEE TABLE

SEE TABLE

DWN
S.URICH
CHK
G.STEINHAUER
APVD
G.STEINHAUER

25JAN01
25JAN01
25JAN01

PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105

NAME
CONTACT BAND, MALE

SIZE
A2

CAGE CODE
00779

DRAWING NO
192007

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
P1

AMP 1471-9 REV 31MAR2000