




1. FOR MATING CONTACT SEE DRAWING 745288.

2. TO BE USED FOR REPLACEMENT ONLY.

3

GOLD PLATED FOR LENGTH OF 3.81 [.150] MIN FROM MATING END, GOLD FLASH IN MATED AREA. 2.54μm [.000100] MIN TIN-LEAD ON AREA L, ALL OVER 1.27μm [.000050] MIN NICKEL.

4

GOLD PLATED FOR LENGTH OF 3.81 [.150] MIN FROM MATING END, 0.76μm [.000030] MIN GOLD IN MATED AREA. 2.54μm [.000100] MIN TIN-LEAD ON AREA L, ALL OVER 1.27μm [.000050] MIN NICKEL.

5

GOLD PLATED FOR LENGTH OF 3.81 [.150] MIN FROM MATING END, GOLD FLASH IN MATED AREA AND AREA L, ALL OVER 1.27μm [.000050] MIN NICKEL. GOLD PLATING ON EDGE CARRIER NOT REQUIRED.

6

GOLD PLATED IN LOCALIZED GOLD PLATE AREA AS FOLLOWS:
0.76μm [.000030] MIN GOLD IN MATED AREA 2.54μm [.000100] MIN TIN ON AREA L, ALL OVER 1.27μm [.000050] MIN NICKEL UNDERPLATE.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE, 0.76μm [.000030] MIN TOTAL IN MATED AREA, 2.54μm [.000100] MIN TIN ON AREA L, ALL OVER 1.27μm [.000050] MIN NICKEL UNDERPLATE.

AS SHOWN	21.67[.853]	6	5-745287-4
PER DETAIL Z	33.07[1.302]	6	5-745287-0
PER DETAIL Z	27.43[1.080]	6	4-745287-7
OBSOLETE	AS SHOWN	5	4-745287-2
OBSOLETE	AS SHOWN	4	2-745287-0
SUPERSEDED BY 2-745287-0		3	1-745287-8
OBSOLETE	PER DETAIL Z	4	1-745287-2
OBSOLETE	PER DETAIL Z	3	1-745287-0
OBSOLETE	PER DETAIL Z	4	745287-8
OBSOLETE	PER DETAIL Z	3	745287-6
OBSOLETE	AS SHOWN	4	745287-4
OBSOLETE	AS SHOWN	3	745287-2

RETENTION TINES		A	FINISH	PART NO
DWN	01/29/91	TE Connectivity		
CHK	2-6-91	NAME		
APVD	-	PRODUCT SPEC		
APPLICATION SPEC		SIZE		
WEIGHT		CAGE CODE		
CUSTOMER DRAWING		DRAWING NO		
SCALE		SHEET		
10:1		1 of 1		
REV		L1		