




2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68, SUBPART F.

 SUGGESTED PANEL OPENING DIMENSIONS.

4 SUGGESTED CLEARANCE BETWEEN TOP OF CONNECTOR AND TOP PANEL OPENING.

5. 0.051[.002] WHITE POLYESTER INSULATOR APPLIED TO BACK OF HOUSING.



6 SEE TABLE FOR COLOR OF LEDS AND NUMBER REQUIRED.

7. THIS MODULAR JACK WITH INTEGRATED LED IS NOT IR REFLOW SOLDERING PROCESS COMPATIBLE.

 PACKAGED 30 PIECES PER TUBE. SEE DETAIL "A".

9 MANUFACTURING DATE CODE:
LOCATED APPROX. AS SHOWN.
FIRST 2 DIGITS = LAST 2 DIGITS OF YEAR.
NEXT 2 DIGITS = MANUFACTURING WORK WEEK.
LAST DIGIT = DAY OF WEEK WITH SUNDAY = 1.

10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PRINTED CIRCUIT BOARD
(COMPONENT SIDE)

		TIN-LEAD	2.54 [.100]	△8	TUBE	GREEN	YELLOW	7-406507-4
		MATTE TIN	3.05 [.120]		TRAY	ORANGE/GREEN	ORANGE/GREEN	3-406507-7
△0	OBSOLETE	MATTE TIN	3.05 [.120]		TRAY	GREEN	GREEN	3-406507-5
△0	OBSOLETE	MATTE TIN	3.05 [.120]		TRAY	GREEN	YELLOW	3-406507-4
△0	OBSOLETE	MATTE TIN	3.05 [.120]		TRAY	YELLOW	GREEN	3-406507-1
		MATTE TIN	2.54 [.100]	△8	TUBE	GREEN	YELLOW	2-406507-4
		MATTE TIN	2.54 [.100]		TRAY	ORANGE/GREEN	ORANGE/GREEN	1-406507-7
△0	OBSOLETE	MATTE TIN	2.54 [.100]		TRAY	YELLOW	YELLOW	1-406507-6
		MATTE TIN	2.54 [.100]		TRAY	GREEN	GREEN	1-406507-5
		MATTE TIN	2.54 [.100]		TRAY	GREEN	YELLOW	1-406507-4
△0	OBSOLETE	MATTE TIN	2.54 [.100]		TRAY	YELLOW	—	1-406507-3
△0	OBSOLETE	MATTE TIN	2.54 [.100]		TRAY	—	GREEN	1-406507-2
		MATTE TIN	2.54 [.100]		TRAY	YELLOW	GREEN	1-406507-1
△0	OBSOLETE	TIN-LEAD	2.54 [.100]		TRAY	ORANGE/GREEN	ORANGE/GREEN	406507-7
		TIN-LEAD	2.54 [.100]		TRAY	YELLOW	YELLOW	406507-6
	OBSOLETE	TIN-LEAD	2.54 [.100]		TRAY	GREEN	GREEN	406507-5
		TIN-LEAD	2.54 [.100]		TRAY	GREEN	YELLOW	406507-4
△0	OBSOLETE	TIN-LEAD	2.54 [.100]		TRAY	YELLOW	—	406507-3
△0	OBSOLETE	TIN-LEAD	2.54 [.100]		TRAY	—	GREEN	406507-2
		TIN-LEAD	2.54 [.100]		TRAY	YELLOW	GREEN	406507-1
	△1	TERMINAL LEAD PLATING	DIM B SOLDER TAIL LENGTH		PACKAGING	POSITION 2	POSITION 1	
						INDICATOR COLOR		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SPRINKLE	15SEP97	 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK T. SPRINKLE	15SEP97		
	TOLERANCES (UNLESS OTHERWISE SPECIFIED)		APVD M. DERSTINE	09C079	NAME INVERTED MODULAR JACK ASSEMBLY, 1X1, SHIELDED, PANEL GROUND, LED, INSULATOR
	0 PLC ± -		PRODUCT SPEC		
	1 PLC ± -		108-1163-4		
	2 PLC ± 0.25[.01]		APPLICATION SPEC		
	3 PLC ± 0.13[.005]		114-2154		
4 PLC ± -		SIZE CASE CODE DRAWING NO		RESTRICTED TO	
MATERIAL 	FINISH 	WEIGHT —		A1	00779 C-406507
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 1	REV K4