



Choose a configuration (s), specify the quantity and click the 'Add to cart' button.

- Click 'View order' to proceed to the order screen, confirm the amount required and complete your purchase.

- Click 'Back to results' to look at other products.

More Information

- how to order
- how to pay
- carriage methods
- terms and conditions
- technical data

1790

Section: **Cable**

Sub Section: **Van Damme audio cable range**

Product: **Van Damme ofc balanced patch cable**

 Continue Shopping

 View order

 Add to cart

Van Damme ofc balanced patch cable

This Van Damme OFC patch cable type has been specifically designed as a reduced diameter two-core microphone cable with an overall braid. The idea for this is in the application of patch leads using bantam plugs. In order to be terminated correctly, an O.D. of exactly 4.85mm is needed to anchor the cable into the back of the bantam plug, by either crimping on a ferrule (Neutrik type) or screwing into the threaded back part of the body (Switchcraft or ADC type). Other than the reduced diameter and overall braid, the cable has the same specification as the standard Van Damme microphone cable giving the same outstanding performance and handling. This cable is also ideal for use with mid/DIN plugs such as Preh or Delttron. These connector types will only accept cables with diameters of 5.00mm or smaller.



The cable is available in ten different colours that may be used for length or application coding.

Stock

Code Configuration

268-006	Balanced patch black
268-007	Balanced patch blue
268-009	Balanced patch red
268-004	Balanced patch green
268-018	Balanced patch grey
268-010	Balanced patch yellow
268-056	Balanced patch white

- 268-058 Balanced patch orange
- 268-060 Balanced patch brown
- 268-062 Balanced patch purple



Balanced Patch Technical Specification

Pair conductor:	28 x 0.10mm (0.22mm ²) 24 AWG high purity OFC
Pair insulation:	Cross linked polyethylene (XLPE)
Pair colours:	1 x red/1 x green - 1.00mm diameter
Braid screen:	96 x 0.12mm - 95% coverage high purity tinned OFC
Overall jacket:	Abrasion resistant anti-kink PVC/Neoprene composite
Jacket colour:	Black - RAL 9005 Green - RAL 6001 Blue - RAL 5002 Grey - RAL 7031 Red - RAL 3001 Yellow - RAL 1021 White - RAL 9010 Orange - RAL 2009 Brown - RAL 8012 Purple - RAL 4004
Temp. range:	-25°C ~ +70°C
D.C. resistance:	< 84W/km
Capacitance:	< 100pF per metre core to core < 165pF per metre cores to screen
Voltage rating:	250V
Weight:	34kg/km
O.D.:	4.85mm ±0.10mm
Max. reel size:	100m
Construction:	Twin conductors of plain (non-tinned) Oxygen Free Copper with cross linked polyethylene (XLPE) insulation twisted together with natural cotton fillers underneath a tightly

woven braid OFC screen giving 95% optical coverage.
Oversheathed with a very flexible matt PVC/Neoprene outer jacket.

Available cut to any length. Priced per metre.

**E-mail: webmaster@vdc-trading.com Call: +44 (0)20 7700 8777 (9.00 am - 5.00 pm)
All contents © VDC Trading Ltd. All rights reserved**