







PRODUCT NUMBER  
SEE TABLE



|             |              |      |            |            |                                       |            |                               |
|-------------|--------------|------|------------|------------|---------------------------------------|------------|-------------------------------|
| mat'l. code |              |      |            | surface    | tolerance                             | projection | product family                |
|             |              |      |            | ISO 1302 ✓ | ISO 406<br>ISO 1101                   | ISO 1101   | QUICKIE                       |
| ltr         | ecn          | no   | dr         | date       | tolerances unless otherwise specified | INCH/MM    | title                         |
| BA          | N08-0073     | 0001 | 4/28/08    | 4/28/08    | XX±.01/XX±0.3                         | INCH/MM    | HEADER, QUICKIE               |
| BB          | N09-0007     | R.B  | 2009/01/12 | 2009/01/12 | XXX±.005/XXX±0.13                     | INCH/MM    | SEA-HORSE, VERTICAL           |
| BC          | ELX-N-012097 | J.Z  | 2012-07-04 | 2012-07-04 | XXXX±.0020/XXXX±0.051                 | scale 1:1  |                               |
| BD          | ELX-N-13354  | DCS  | 2012-11-02 | 2012-11-02 | M. CORNMANN                           | 8/21/90    | dwg no                        |
| BE          | ELX-N-17979  | TIM  | 2014-06-17 | 2014-06-17 | M. SMYK                               | 8/21/90    | sheet 1 of 23 size            |
|             |              |      |            |            | chr                                   | M. SMYK    | 65863 A3                      |
|             |              |      |            |            | appd                                  | M. SMYK    | type Product Customer Drawing |
| sheet       | revision     | BE   | BE         | BE         | BE                                    | BE         | BE                            |
| index       | sheet        | 1    | 2          | 3          | 4                                     | 5          | 6                             |

NOTES:

- HOUSING MAT'L: HIGH TEMPERTURE THERMOPLASTIC. UL94V-0.  
COLOR : BLACK
- PIN MATERIAL: PHOSPHOR-BRONZE
- 3 LBS/1.36 KG MIN. RETENTION.
- TO DETERMINE DIMENSION:  
N = NUMBER OF POSITIONS.  
EXAMPLE: 10 POS., (N-1) x .100[2.54]=.900[22.87]
- RETENTIVE LEG:  
RETENTION FEATURE AVAILABLE ON CONNECTORS WITH .105/2.67, .120/3.05  
OR .150/3.81 TAIL LENGTH. RETENTION P/N INCLUDES THE LETTER "R"  
AFTER THE EXISTING P/N.  
EXAMPLE : 65863-XXX FOR EXISTING P/N  
65863-XXXR FOR RETENTION P/N  
RETENTION FEATURE LOCATION IS MANUFACTURERS OPTION.  
5LB/2.3KG MAX INSERTION FORCE AND .25LB./1KG MIN RETENTION FORCE  
PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARD AND RECOMMENDED  
HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER.  
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
- 1° MAX DRAFT PERMISSIBLE ON ALL SURFACES UNLESS OTHERWISE SPECIFIED.
- PLATING ON LEAD-IN PORTION OF PIN IS MANUFACTURING OPTION.
- L.P. LATCHES TO BE USED WITH FEMALE CONNECTOR WITHOUT STRAIN RELIEF, ,  
STANDARD LATCHES TO BE USED WITH FEMALE CONNECTOR WITH STRAIN RELIEF.
- RECOMMENDED MOUNTING SCREW SIZE : #2-56 FILLISTER HEAD MACHINE SCREW,  
1/4" LONG FOR 1/16" AND 3/32" BOARD, 5/16" LONG FOR 1/8" BOARD.
- DASH -7XX IS POLARIZED (PIN MISSING).
- UNDERPLATING: 50μ"/1.27μm Ni.
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER  
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- FOR POLARIZATION, SPECIFY POSITION NUMBER (i.e.. 03= PIN 3) TO OMIT PIN.  
OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE  
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm  
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES  
IF THEY ARE AVAILABLE.
- "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND  
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT  
ENVIRONMENTS."
- PLATING OPTIONS:  
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL,  
OPTIONALLY TIN ON TAIL.
- THE PART NUMBER IN THE DASH NUMBER WITH A LETTER "S" WILL HAVE A  
SPECIAL SEA HORSE USED.
- LEAD FREE PLATING: 100u"~160u"/2.54u~4.06u PURE Sn.
- 65863-XXXP, P-DESIGNATE ORIENTATION POST.(SEE PAGE 23)
- 65863-XXXF, F-PLATING FOUR SIDES ON CONTACT AREA.(SEE PAGE 23)



|             |     |          |    |      |                                       |            |        |                                  |  |  |                                                                                                     |  |                                                                                       |       |                 |  |  |  |
|-------------|-----|----------|----|------|---------------------------------------|------------|--------|----------------------------------|--|--|-----------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|-------|-----------------|--|--|--|
| mat'l. code |     |          |    |      | surface<br>ISO 1302 ✓                 |            |        | tolerance<br>ISO 406<br>ISO 1101 |  |  | projection<br> |  | product family<br>QUICKIE                                                             |       |                 |  |  |  |
| ltr         | ecn | no       | dr | date | tolerances unless otherwise specified |            |        |                                  |  |  |                                                                                                     |  |  | title |                 |  |  |  |
| BE          |     |          |    |      | angles                                |            | linear | .XXX±.01/.XXX±.03                |  |  | INCH/MM                                                                                             |  |                                                                                       |       |                 |  |  |  |
|             |     |          |    |      | 0°±2°                                 |            |        | .XXX±.005/.XXX±.013              |  |  | HEADER, QUICKIE                                                                                     |  |                                                                                       |       |                 |  |  |  |
|             |     |          |    |      |                                       |            |        | .XXX±.0020/.XXX±0.051            |  |  | SEA-HORSE, VERTICAL                                                                                 |  |                                                                                       |       |                 |  |  |  |
|             |     |          |    |      | dr                                    | M. CORNMAN |        | 8/21/90                          |  |  |                |  | dwg no                                                                                |       | sheet2 of23size |  |  |  |
|             |     |          |    |      | enr                                   | M. SMYK    |        | 8/21/90                          |  |  |                                                                                                     |  | 65863                                                                                 |       | A3              |  |  |  |
|             |     |          |    |      | chr                                   | M. SMYK    |        | 8/21/90                          |  |  |                                                                                                     |  | type Product Customer Drawing                                                         |       |                 |  |  |  |
|             |     |          |    |      | appd                                  | M. SMYK    |        | 8/21/90                          |  |  |                                                                                                     |  |                                                                                       |       |                 |  |  |  |
| sheet       |     | revision |    |      |                                       |            |        |                                  |  |  |                                                                                                     |  |                                                                                       |       |                 |  |  |  |
| index       |     | sheet    |    |      |                                       |            |        |                                  |  |  |                                                                                                     |  |                                                                                       |       |                 |  |  |  |







1

2

3

4

5

6

PRODUCT NO  
NOTE 12,13

SIZE

LATCH  
NOTE  
8

DIM B

DIM D

TERMINAL PLATING

STYLE

65863-109

2x5

NO

.400/10,160

.105/ 2,67

30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni

A

↑ -110

2x7

↑

.600/15,240

↑

↑

C

-111

2x8

.700/17,780

D

-112

2x10

.900/22,860

↑

-113

2x13

1.200/30,480

-114

2x17

1.600/40,640

-115

2x20

1.900/48,260

-116

2x25

2.400/60,960

↓

-117

2x30

NO

2.900/73,660

D

-118

2x5

STD

.400/10,160

A

-119

2x7

↑

.600/15,240

C

-120

2x8

.700/17,780

D

-121

2x10

.900/22,860

↑

-122

2x13

1.200/30,480

-123

2x17

1.600/40,640

-124

2x20

1.900/48,260

-125

2x25

↓

2.400/60,960

-126

2x30

STD

2.900/73,660

.105/ 2,67

-127

2x20

NO

1.900/48,260

.150/ 3,81

↓

-128

2x20

STD

1.900/48,260

↑

D

-129

2x5

NO

.400/10,160

A

-130

2x7

↑

.600/15,240

C

-131

2x8

.700/17,780

D

-132

2x10

.900/22,860

↑

-133

2x13

1.200/30,480

-134

2x17

1.600/40,640

-135

2x20

1.900/48,260

-136

2x25

↓

2.400/60,960

↓

-137

2x30

NO

2.900/73,660

D

-138

2x5

STD

.400/10,160

A

-139

2x7

↑

.600/15,240

C

-140

2x8

.700/17,780

D

-141

2x10

.900/22,860

↑

-142

2x13

1.200/30,480

↓ -143

2x17

↓

1.600/40,640

↓

65863-144

2x20

STD

1.900/48,260

.150/ 3,81

30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni

D

mat'l. code

surface  
ISO 1302 ✓

tolerance  
ISO 406  
ISO 1101

projection  
INCH/MM

product family  
QUICKIE

ltr

ecn no

dr

date

tolerances unless otherwise specified

linear

angles

0°±2°

dr

M. CORNMAN

8/21/90

enr

M. SMYK

8/21/90

chr

M. SMYK

8/21/90

appd

M. SMYK

8/21/90

scale 1:1

FCI

dwg no

sheet6 of23

size

65863

A3

type

Product Customer Drawing

BE

revision

sheet

index

sheet

form: A3

1

2

3

4

5

6

Copyright FCI

FCIconnect.com

FCI

Released

Printed: Jun 19, 2014

D

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

1

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE 8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|-----------------|--------------|------------|---------------------------------------------|-------|
| 65863-181                | 2x8  | LP              | .700/17,780  | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| ↑ -182                   | 2x8  | ↑               | .700/17,780  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           | ↑     |
| -183                     | 2x10 |                 | .900/22,860  | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -184                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -185                     | ↑    |                 | ↑            | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -186                     | ↑    |                 | ↑            | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -187                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -188                     | 2x10 |                 | .900/22,860  | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -189                     | 2x13 |                 | 1.200/30,480 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -190                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -191                     | ↑    |                 | ↑            | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -192                     | ↓    |                 | ↓            | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -193                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -194                     | 2x13 |                 | 1.200/30,480 | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -195                     | 2x17 |                 | 1.600/40,640 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -196                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -197                     | ↑    |                 | ↑            | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -198                     | ↑    |                 | ↑            | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -199                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -200                     | 2x17 |                 | 1.600/40,640 | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -201                     | 2x20 |                 | 1.900/48,260 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -202                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -203                     | ↑    |                 | ↑            | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -204                     | ↑    |                 | ↑            | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -205                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -206                     | 2x20 |                 | 1.900/48,260 | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -207                     | 2x25 |                 | 2.400/60,960 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -208                     | ↑    |                 | ↑            | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -209                     | ↑    |                 | ↑            | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -210                     | ↑    |                 | ↑            | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -211                     | ↓    |                 | ↓            | .675/17,15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -212                     | 2x25 |                 | 2.400/60,960 | .675/17,15 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| -213                     | 2x30 |                 | 2.900/73,660 | .105/ 2,67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -214                     | 2x30 |                 | 2.900/73,660 | .105/ 2,67 | 120u"~200u"/3.04um~5.08umTIN/LEAD           |       |
| ↓ -215                   | 2x30 | ↓               | 2.900/73,660 | .150/ 3,81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | ↓     |
| 65863-216                | 2x30 | LP              | 2.900/73,660 | .150/ 3,81 | 120u"~200u"/3.04um~5.08umTIN/LEAD           | D     |

|             |  |                |  |                       |  |                                  |  |                                                                                                     |  |                           |  |  |  |
|-------------|--|----------------|--|-----------------------|--|----------------------------------|--|-----------------------------------------------------------------------------------------------------|--|---------------------------|--|--|--|
| mat'l. code |  |                |  | surface<br>ISO 1302 ✓ |  | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |  | product family<br>QUICKIE |  |  |  |
| ltr         |  | ecn no         |  | dr                    |  | date                             |  | tolerances unless otherwise specified                                                               |  | title                     |  |  |  |
| BE          |  |                |  |                       |  |                                  |  | angles linear                                                                                       |  | INCH/MM                   |  |  |  |
|             |  |                |  |                       |  |                                  |  | 0±2"                                                                                                |  | scale 1:1                 |  |  |  |
|             |  |                |  |                       |  |                                  |  | dr M. CORNMAN                                                                                       |  | 8/21/90                   |  |  |  |
|             |  |                |  |                       |  |                                  |  | enr M. SMYK                                                                                         |  | 8/21/90                   |  |  |  |
|             |  |                |  |                       |  |                                  |  | chr M. SMYK                                                                                         |  | 8/21/90                   |  |  |  |
|             |  |                |  |                       |  |                                  |  | appd M. SMYK                                                                                        |  | 8/21/90                   |  |  |  |
| sheet index |  | revision sheet |  |                       |  |                                  |  |                                                                                                     |  |                           |  |  |  |

|             |  |                |  |  |  |  |  |  |  |  |  |  |  |
|-------------|--|----------------|--|--|--|--|--|--|--|--|--|--|--|
| sheet index |  | revision sheet |  |  |  |  |  |  |  |  |  |  |  |
|             |  |                |  |  |  |  |  |  |  |  |  |  |  |



4 PDS: Rev :BE STATUS: Released Printed: Jun 19, 201









1

2

3

4

5

6

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|------------|---------------------------------------------|-------|
| 65863-396                | 2x5  | LP                 | .400/10.160  | .105/ 2,67 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u NI | A     |
| -397                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -398                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -399                     |      | LP                 |              | .150/ 3,81 |                                             | A     |
| -400                     |      | NO                 |              | .105/ 2,67 |                                             | B     |
| -401                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -402                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -403                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -404                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -405                     | 2x5  | LP                 | .400/10.160  | .150/ 3,81 |                                             | B     |
| -406                     | 2x7  | NO                 | .600/15.240  | .105/ 2,67 |                                             | C     |
| -407                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -408                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -409                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -410                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -411                     | 2x7  | LP                 | .600/15.240  | .150/ 3,81 |                                             | C     |
| -412                     | 2x8  | NO                 | .700/17.780  | .105/ 2,67 |                                             | D     |
| -413                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -414                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -415                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -416                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -417                     | 2x8  | LP                 | .700/17.780  | .150/ 3,81 |                                             |       |
| -418                     | 2x10 | NO                 | .900/22.860  | .105/ 2,67 |                                             |       |
| -419                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -420                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -421                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -422                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -423                     | 2x10 | LP                 | .900/22.860  | .150/ 3,81 |                                             |       |
| -424                     | 2x13 | NO                 | 1.200/30.480 | .105/ 2,67 |                                             |       |
| -425                     |      | STD                |              | .105/ 2,67 |                                             |       |
| -426                     |      | LP                 |              | .105/ 2,67 |                                             |       |
| -427                     |      | NO                 |              | .150/ 3,81 |                                             |       |
| -428                     |      | STD                |              | .150/ 3,81 |                                             |       |
| -429                     | 2x13 | LP                 | 1.200/30.480 | .150/ 3,81 |                                             |       |
| 65863-430                | 2x17 | NO                 | 1.600/40.640 | .105/ 2,67 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u NI | D     |

FCIconnect.com

Copyright FCI

| mat'l. code |                | surface    |      | tolerance                             |            | projection                    |  | product family                |  |
|-------------|----------------|------------|------|---------------------------------------|------------|-------------------------------|--|-------------------------------|--|
|             |                | ISO 1302 ✓ |      | ISO 406<br>ISO 1101                   |            |                               |  | QUICKIE                       |  |
| ltr         | ecn no         | dr         | date | tolerances unless otherwise specified |            | INCH/MM                       |  | title                         |  |
| BE          |                |            |      | angles                                | linear     | X.XX ± .01 / X.XX ± .03       |  | HEADER, QUICKIE               |  |
|             |                |            |      |                                       |            | X.XX ± .005 / X.XX ± .013     |  | SEA-HORSE, VERTICAL           |  |
|             |                |            |      | 0°±2°                                 |            | X.XXX ± .0020 / X.XXX ± .0051 |  | scale 1:1                     |  |
|             |                |            |      | dr                                    | M. CORNMAN | 8/21/90                       |  | dwg no sheet 14 of 23 size    |  |
|             |                |            |      | enr                                   | M. SMYK    | 8/21/90                       |  | 65863 A3                      |  |
|             |                |            |      | chr                                   | M. SMYK    | 8/21/90                       |  | type Product Customer Drawing |  |
|             |                |            |      | appd                                  | M. SMYK    | 8/21/90                       |  |                               |  |
| sheet index | revision sheet |            |      |                                       |            |                               |  |                               |  |

form: A3

1

2

3

4

5

6

PDS: Rev :BE

STATUS: Released

Printed: Jun 19, 2014

| PRODUCT NO<br>NOTES 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | PIN<br>STYLE | MISSING |
|---------------------------|------|--------------------|--------------|------------|---------------------------------------------|--------------|---------|
| 65863-431                 | 2x17 | STD                | 1.600/40.640 | .105/ 2,67 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D            | NONE    |
| -432                      |      | LP                 |              | .105/ 2,67 |                                             |              |         |
| -433                      |      | NO                 |              | .150/ 3,81 |                                             |              |         |
| -434                      |      | STD                |              | .150/ 3,81 |                                             |              |         |
| -435                      | 2x17 | LP                 | 1.600/40.640 | .150/ 3,81 |                                             |              |         |
| -436                      | 2x20 | NO                 | 1.900/48.260 | .105/ 2,67 |                                             |              |         |
| -437                      |      | STD                |              | .105/ 2,67 |                                             |              |         |
| -438                      |      | LP                 |              | .105/ 2,67 |                                             |              |         |
| -439                      |      | NO                 |              | .150/ 3,81 |                                             |              |         |
| -440                      |      | STD                |              | .150/ 3,81 |                                             |              |         |
| -441                      | 2x20 | LP                 | 1.900/48.260 | .150/ 3,81 |                                             |              |         |
| -442                      | 2x25 | NO                 | 2.400/60.960 | .105/ 2,67 |                                             |              |         |
| -443                      |      | STD                |              | .105/ 2,67 |                                             |              |         |
| -444                      |      | LP                 |              | .105/ 2,67 |                                             |              |         |
| -445                      |      | NO                 |              | .150/ 3,81 |                                             |              |         |
| -446                      |      | STD                |              | .150/ 3,81 |                                             |              |         |
| -447                      | 2x25 | LP                 | 2.400/60.960 | .150/ 3,81 |                                             |              |         |
| -448                      | 2x30 | NO                 | 2.900/73.660 | .105/ 2,67 |                                             |              |         |
| -449                      |      | STD                |              | .105/ 2,67 |                                             |              |         |
| -450                      |      | LP                 |              | .105/ 2,67 |                                             |              |         |
| -451                      |      | NO                 |              | .150/ 3,81 |                                             |              |         |
| -452                      |      | STD                |              | .150/ 3,81 |                                             |              |         |
| -453                      | 2x30 | LP                 | 2.900/73.660 | .150/ 3,81 |                                             |              |         |
| -454                      | 2x12 | NO                 | 1.100/27.940 | .105/ 2,67 |                                             |              |         |
| -455                      | 2x12 | STD                |              |            |                                             |              |         |
| -456                      | 2x12 | LP                 |              |            |                                             |              |         |
| -456S                     | 2x12 | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -457                      | 2x12 | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -458                      |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -459                      |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -460                      |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -461                      |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -462                      |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |              |         |
| -463                      |      | NO                 |              |            | 120u"-200u"/3.04u-5.08uTIN/LEAD             |              |         |
| -464                      |      | STD                |              |            | 120u"-200u"/3.04u-5.08uTIN/LEAD             |              |         |
| 65863-465                 | 2x12 | LP                 | 1.100/27.940 | .105/ 2,67 | 120u"-200u"/3.04u-5.08uTIN/LEAD             | D            | NONE    |

NOTE 18

NOTE 16,19

NOTE 16,19

NOTE 16,19

|             |                |    |      |                                       |            |                                  |  |                                                                                                     |        |                                                                                       |                                                 |  |  |
|-------------|----------------|----|------|---------------------------------------|------------|----------------------------------|--|-----------------------------------------------------------------------------------------------------|--------|---------------------------------------------------------------------------------------|-------------------------------------------------|--|--|
| mat'l. code |                |    |      | surface<br>ISO 1302 ✓                 |            | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |        | product family<br>QUICKIE                                                             |                                                 |  |  |
| ltr         | ecn no         | dr | date | tolerances unless otherwise specified |            |                                  |  |                                                                                                     |        |  | title<br>HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |  |  |
| BE          |                |    |      | angles                                | linear     | XXX±.01 / XXX±.3                 |  | scale 1:1                                                                                           |        |                                                                                       |                                                 |  |  |
|             |                |    |      |                                       |            | XXX±.005 / XXX±.013              |  |                                                                                                     |        |                                                                                       |                                                 |  |  |
|             |                |    |      | 0°±2'                                 |            | XXX±.0020 / XXX±0.051            |  |                                                                                                     |        |                                                                                       |                                                 |  |  |
|             |                |    |      | dr                                    | M. CORNMAN | 8/21/90                          |  |                | dwg no |                                                                                       | sheet15 of23size                                |  |  |
|             |                |    |      | engr                                  | M. SMYK    | 8/21/90                          |  |                                                                                                     | 65863  |                                                                                       | A3                                              |  |  |
|             |                |    |      | chr                                   | M. SMYK    | 8/21/90                          |  |                                                                                                     |        |                                                                                       |                                                 |  |  |
|             |                |    |      | appd                                  | M. SMYK    | 8/21/90                          |  |                                                                                                     |        |                                                                                       |                                                 |  |  |
| sheet index | revision sheet |    |      |                                       |            |                                  |  |                                                                                                     |        |                                                                                       |                                                 |  |  |

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE 8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|-----------------|--------------|------------|---------------------------------------------|-------|
| 65863-466                | 2x12 | NO              | 1.100/27.940 | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -467                     |      | STD             |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -468                     |      | LP              |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -469                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -470                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -471                     |      | LP              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -472                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -473                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -474                     |      | LP              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -475                     |      | NO              |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -476                     |      | STD             |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -477                     |      | LP              |              | .150/3.81  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -478                     |      | NO              |              | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -479                     |      | STD             |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -480                     |      | LP              |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -481                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -482                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -483                     |      | LP              |              | .105/2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -484                     |      | NO              |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -485                     |      | STD             |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -486                     |      | LP              |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -487                     |      | NO              |              | .675/17.15 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -488                     |      | STD             |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -489                     |      | LP              |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -490                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -491                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -492                     |      | LP              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -493                     |      | NO              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -494                     |      | STD             |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -495                     |      | LP              |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -496                     |      | NO              |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -497                     |      | STD             |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -498                     | 2x12 | LP              | 1.100/27.940 | .675/17.15 | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -499                     | 2x15 | NO              | 1.400/35.560 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| 65863-500                | 2x15 | STD             | 1.400/35.560 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

|             |        |                |      |                                       |            |                                  |  |                                                                                                     |  |                                                                                       |                                                 |  |  |  |
|-------------|--------|----------------|------|---------------------------------------|------------|----------------------------------|--|-----------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|-------------------------------------------------|--|--|--|
| mat'l. code |        |                |      | surface<br>ISO 1302 ✓                 |            | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |  | product family<br>QUICKIE                                                             |                                                 |  |  |  |
| ltr         | ecn no | dr             | date | tolerances unless otherwise specified |            |                                  |  |                                                                                                     |  |  | title<br>HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |  |  |  |
| BE          |        |                |      | angles                                |            | linear                           |  | .XXX±.01/.XXX±.03<br>.XXX±.005/.XXX±.013<br>.XXX±.0020/.XXX±0.051                                   |  |                                                                                       |                                                 |  |  |  |
|             |        |                |      | 0°±2'                                 |            |                                  |  | scale 1:1                                                                                           |  | dwg no<br>sheet16 of23size<br>65863A3                                                 |                                                 |  |  |  |
|             |        |                |      | dr                                    | M. CORNMAN | 8/21/90                          |  |                |  |                                                                                       |                                                 |  |  |  |
|             |        |                |      | enr                                   | M. SMYK    | 8/21/90                          |  |                                                                                                     |  |                                                                                       |                                                 |  |  |  |
|             |        |                |      | chr                                   | M. SMYK    | 8/21/90                          |  |                                                                                                     |  |                                                                                       |                                                 |  |  |  |
|             |        |                |      | appd                                  | M. SMYK    | 8/21/90                          |  |                                                                                                     |  |                                                                                       |                                                 |  |  |  |
| sheet index |        | revision sheet |      |                                       |            |                                  |  |                                                                                                     |  | type Product Customer Drawing                                                         |                                                 |  |  |  |
|             |        |                |      |                                       |            |                                  |  |                                                                                                     |  |                                                                                       |                                                 |  |  |  |



| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|------------|---------------------------------------------|-------|
| 65863-501                | 2x15 | LP                 | 1.400/35.560 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -502                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -503                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -504                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -505                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -506                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -507                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -508                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -509                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -510                     |      | LP                 |              | .105/2.67  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -511                     |      | NO                 |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -512                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -513                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -514                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -515                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -516                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -517                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -518                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -519                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -520                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -521                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -522                     |      | LP                 |              | .150/3.81  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -523                     |      | NO                 |              | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -524                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -525                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -526                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -527                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -528                     |      | LP                 |              | .105/2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -529                     |      | NO                 |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -530                     |      | STD                |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -531                     |      | LP                 |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -532                     |      | NO                 |              | .675/17.15 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -533                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -534                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| 65863-535                | 2x15 | NO                 | 1.400/35.560 | .675/17.15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

[illegible]

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D      | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|------------|---------------------------------------------|-------|
| 65863-536                | 2x15 | STD                | 1.400/35.560 | .675/17.15 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -537                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -538                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -539                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -540                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -541                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -542                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -543                     | 2x15 | LP                 | 1.400/35.560 | .675/17.15 | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -544                     | 2x22 | NO                 | 2.100/53.340 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -545                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -546                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -547                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -548                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -549                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -550                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -551                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -552                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -553                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -554                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -555                     |      | LP                 |              | .105/2.67  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -556                     |      | NO                 |              | .150/3.81  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -557                     |      | STD                |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -558                     |      | LP                 |              |            | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -559                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -560                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -561                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -562                     |      | NO                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -563                     |      | STD                |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -564                     |      | LP                 |              |            | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -565                     |      | NO                 |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -566                     |      | STD                |              |            | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -567                     |      | LP                 |              | .150/3.81  | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -568                     |      | NO                 |              | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -569                     |      | STD                |              | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| 65863-570                | 2x22 | LP                 | 2.100/53.340 | .105/2.67  | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16,19

NOTE 16.19

NOTE 16,19

NOTE 16.19

|                    |  |                |  |                                       |  |                                  |  |                                                                                                     |  |                                        |  |  |  |
|--------------------|--|----------------|--|---------------------------------------|--|----------------------------------|--|-----------------------------------------------------------------------------------------------------|--|----------------------------------------|--|--|--|
| mat'l. code        |  |                |  | surface<br>ISO 1302 ✓                 |  | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |  | product family<br>QUICKIE              |  |  |  |
| ltr ecn no dr date |  |                |  | tolerances unless otherwise specified |  |                                  |  |                                                                                                     |  | title                                  |  |  |  |
| BE                 |  |                |  | angles                                |  | linear                           |  | INCH/MM                                                                                             |  | HEADER, QUICKIE<br>SEA-HORSE, VERTICAL |  |  |  |
|                    |  |                |  |                                       |  | XXX±.01/XXX±.03                  |  | scale 1:1                                                                                           |  |                                        |  |  |  |
|                    |  |                |  |                                       |  | XXX±.005/XXX±.013                |  |                                                                                                     |  |                                        |  |  |  |
|                    |  |                |  | 0°±2'                                 |  | XXX±.002/XXX±.005                |  |                                                                                                     |  | dwg no sheet18 of23size<br>65863A3     |  |  |  |
|                    |  |                |  | dr                                    |  | M. CORNMAN 8/21/90               |  |                |  |                                        |  |  |  |
|                    |  |                |  | engr                                  |  | M. SMYK 8/21/90                  |  |                                                                                                     |  |                                        |  |  |  |
|                    |  |                |  | chr                                   |  | M. SMYK 8/21/90                  |  |                                                                                                     |  |                                        |  |  |  |
|                    |  |                |  | appd                                  |  | M. SMYK 8/21/90                  |  |                                                                                                     |  |                                        |  |  |  |
| sheet index        |  | revision sheet |  |                                       |  |                                  |  |                                                                                                     |  | type Product Customer Drawing          |  |  |  |
|                    |  |                |  |                                       |  |                                  |  |                                                                                                     |  |                                        |  |  |  |



| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D       | TERMINAL PLATING                            | STYLE |
|--------------------------|------|--------------------|--------------|-------------|---------------------------------------------|-------|
| 65863-605                | 2X32 | STD                | 3.100/78.740 | .105/2.67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -606                     |      | LP                 |              |             | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -607                     |      | NO                 |              |             | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -608                     |      | STD                |              |             | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -609                     |      | LP                 |              |             | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -610                     |      | NO                 |              |             | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -611                     |      | STD                |              |             | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -612                     | 2X32 | LP                 | 3.100/78.740 | .105/2.67   | 120u-200u"/3.04u-5.08u TIN/LEAD             |       |
| -613                     | 2x20 | NO                 | 1.900/48.260 | .105/ 2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -614                     | 2x20 | STD                | 1.900/48.260 | .105/ 2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -615                     | 2x20 | LP                 | 1.900/48.260 | .105/ 2.67  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -616                     | 2x25 | NO                 | 2.400/60.960 | .450/ 11.43 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -617                     | 2x17 | NO                 | 1.600/40.640 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -618                     | 2x17 | STD                | 1.600/40.640 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -619                     | 2x17 | LP                 | 1.600/40.640 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -620                     | 2X32 | STD                | 3.100/78.740 | .105/2.67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -621                     | 2X32 | NO                 | 3.100/78.740 |             |                                             |       |
| -622                     | 2x15 | STD                | 1.400/35.560 |             |                                             |       |
| -623                     | 2x15 | NO                 | 1.400/35.560 |             |                                             |       |
| -624                     | 2x22 | STD                | 2.100/53.340 |             |                                             |       |
| -625                     | 2x22 | NO                 | 2.100/53.340 | .105/2.67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -626                     | 2x25 | NO                 | 2.400/60.960 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -627                     | 2x25 | STD                | 2.400/60.960 |             |                                             |       |
| -628                     | 2x25 | LP                 | 2.400/60.960 |             |                                             |       |
| -629                     | 2x20 | NO                 | 1.900/48.260 |             |                                             |       |
| -630                     | 2x20 | STD                | 1.900/48.260 |             |                                             |       |
| -631                     | 2x20 | LP                 | 1.900/48.260 | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -632                     | 2x20 | STD                | 1.900/48.260 | .105/2.67   | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni |       |
| -633                     | 2x8  | STD                | .700/17.78   | .150/ 3.81  | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -634                     | 2x7  | NO                 | .600/15.24   | .236/ 5.99  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | C     |
| -635                     | 2x5  | STD                | .400/10.16   | .520/13.21  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | A     |
| -636                     | 2x8  | NO                 | .700/17.78   | .150/ 3.81  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -637                     | 2x8  | STD                | .700/17.78   | .150/ 3.81  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| -638                     | 2x10 | NO                 | .800/20.32   | .150/ 3.81  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |
| 65863-639                | 2x10 | STD                | .800/20.32   | .150/ 3.81  | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     |

NOTE 16,19

NOTE 16,19

NOTE 16,19

**CUSTOMER SPECIAL**

A

A

B

E

C

C

D

□

form: A3

1

2

3

4

IS:

20

4 PDS: Rev :BE

STATUS: Released

Printed: Jun 19, 2014

|             |     |                |    |                       |  |                                       |            |                                                                                                     |  |                                                                                       |  |                                                                                                      |  |
|-------------|-----|----------------|----|-----------------------|--|---------------------------------------|------------|-----------------------------------------------------------------------------------------------------|--|---------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------|--|
| mat'l. code |     |                |    | surface<br>ISO 1302 ✓ |  | tolerance<br>ISO 406<br>ISO 1101      |            | projection<br> |  | product family<br>QUICKIE                                                             |  |                                                                                                      |  |
| ltr         | ecn | no             | dr | date                  |  | tolerances unless otherwise specified |            |                                                                                                     |  |                                                                                       |  |                                                                                                      |  |
| BE          |     |                |    |                       |  | angles                                | linear     | 0.01/0.03<br>0.005/0.013<br>0.020/0.051                                                             |  | INCH/MM                                                                               |  | title<br><br>HEADER, QUICKIE<br>SEA-HORSE, VERTICAL<br><br>dwg no<br>sheet20 of23size<br>65863<br>A3 |  |
|             |     |                |    |                       |  | 0±2'                                  |            |                                                                                                     |  | scale 1:1                                                                             |  |                                                                                                      |  |
|             |     |                |    |                       |  | dr                                    | M. CORNMAN | 8/21/90                                                                                             |  |  |  |                                                                                                      |  |
|             |     |                |    |                       |  | enrg                                  | M. SMYK    | 8/21/90                                                                                             |  |                                                                                       |  |                                                                                                      |  |
|             |     |                |    |                       |  | chr                                   | M. SMYK    | 8/21/90                                                                                             |  |                                                                                       |  |                                                                                                      |  |
|             |     |                |    |                       |  | appd                                  | M. SMYK    | 8/21/90                                                                                             |  |                                                                                       |  |                                                                                                      |  |
| sheet index |     | revision sheet |    |                       |  |                                       |            |                                                                                                     |  |                                                                                       |  |                                                                                                      |  |



FCIconnect.com

Copyright FCI

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE 8 | DIM B        | DIM D     | TERMINAL PLATING                            | STYLE | PIN<br>MISSING |
|--------------------------|------|-----------------|--------------|-----------|---------------------------------------------|-------|----------------|
| 65863-640                | 2x12 | NO              | 1.100/ 27.94 | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | NONE           |
| -641                     | 2x12 | STD             | 1.100/ 27.94 |           |                                             |       |                |
| -642                     | 2x15 | NO              | 1.400/ 35.56 |           |                                             |       |                |
| -643                     | 2x15 | STD             | 1.400/ 35.56 |           |                                             |       |                |
| -644                     | 2x30 | NO              | 2.900/ 73.66 |           |                                             |       |                |
| -645                     | 2x30 | STD             | 2.900/ 73.66 |           |                                             |       |                |
| -646                     | 2x25 | STD             | 2.400/ 60.96 |           |                                             | D     |                |
| -647                     | 2x5  | STD             | .400/ 10.16  |           |                                             | A     |                |
| -648                     | 2x7  | STD             | .600/ 15.24  |           |                                             | C     |                |
| -649                     | 2x13 | STD             | 1.120/ 30.48 |           |                                             | D     |                |
| -650                     | 2x17 | STD             | 1.600/ 40.64 |           |                                             | D     |                |
| -651                     | 2x5  | NO              | .400/ 10.16  |           |                                             | A     |                |
| -652                     | 2x7  | NO              | .600/ 15.24  |           |                                             | C     |                |
| -653                     | 2x13 | NO              | 1.120/ 30.48 |           |                                             | D     |                |
| -654                     | 2x17 | NO              | 1.600/ 40.64 | .150/3.81 |                                             | D     |                |
| -655                     | 2x5  | STD             | .400/ 10.16  | .175/4.45 |                                             | A     |                |
| -656                     | 2x7  |                 | .600/ 15.24  |           |                                             | C     |                |
| -657                     | 2x13 |                 | 1.120/ 30.48 |           |                                             | D     |                |
| -658                     | 2x17 | STD             | 1.600/ 40.64 | .175/4.45 |                                             | D     |                |
| -659                     | 2x5  | NO              | .400/ 10.16  | .250/6.35 |                                             | A     |                |
| -660                     | 2x7  | LP              | .600/ 15.24  | .236/5.99 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | C     | NONE           |
| -715                     | 2x8  | LP              | .700/ 17.78  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 3              |
| -716                     | 2x8  | LP              | .700/ 17.78  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 14             |
| -717                     | 2X20 | LP              | 1.900/48.26  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 20             |
| -717S                    | 2X20 | LP              | 1.900/48.26  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 20             |
| -733                     | 2x17 | LP              | 1.600/ 40.14 | .105/2.67 | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 5              |
| -734                     | 2x17 | STD             | 1.600/ 40.64 | .105/2.67 | 50u"/1.27u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 5              |
| -735                     | 2x10 | LP              | .900/ 22.86  | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 16             |
| -736                     | 2x10 | LP              | .900/ 22.86  |           | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 19             |
| -737                     | 2x5  | LP              | .400/ 10.16  |           | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | A     | 10             |
| -738                     | 2X20 | LP              | 1.900/48.26  |           | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 8              |
| -739                     | 2X25 | LP              | 2.400/60.96  |           |                                             | D     | 25             |
| -740                     | 2X12 | LP              | 1.100/ 27.94 |           |                                             | D     | 20             |
| -741                     | 2X17 | LP              | 1.600/ 40.64 |           |                                             | D     | 5              |
| -741S                    | 2X17 | LP              | 1.600/ 40.64 |           |                                             | D     | 5              |
| -742                     | 2X5  | LP              | .400/ 10.16  |           |                                             | A     | 2              |
| 65863-743                | 2X17 | LP              | 1.600/ 40.64 | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 3              |

NOTE 18

NOTE 18

|                    |  |                |  |                                       |  |                                  |  |                                                                                                     |  |                               |  |  |  |
|--------------------|--|----------------|--|---------------------------------------|--|----------------------------------|--|-----------------------------------------------------------------------------------------------------|--|-------------------------------|--|--|--|
| mat'l. code        |  |                |  | surface<br>ISO 1302 ✓                 |  | tolerance<br>ISO 406<br>ISO 1101 |  | projection<br> |  | product family<br>QUICKIE     |  |  |  |
| ltr ecn no dr date |  |                |  | tolerances unless otherwise specified |  |                                  |  |                                                                                                     |  | title                         |  |  |  |
| BE                 |  |                |  | angles                                |  | linear                           |  | INCH/MM                                                                                             |  | HEADER, QUICKIE               |  |  |  |
|                    |  |                |  |                                       |  | XXX±.01/XXX±.0.3                 |  |                                                                                                     |  | SEA-HORSE, VERTICAL           |  |  |  |
|                    |  |                |  |                                       |  | XXX±.005/XXX±.0.13               |  |                                                                                                     |  |                               |  |  |  |
|                    |  |                |  | 0°±2°                                 |  | XXX±.0020/XXX±.0.051             |  | scale 1:1                                                                                           |  |                               |  |  |  |
|                    |  |                |  | dr                                    |  | M. CORNMAN                       |  | 8/21/90                                                                                             |  | dwg no sheet21 of23size       |  |  |  |
|                    |  |                |  | engr                                  |  | M. SMYK                          |  | 8/21/90                                                                                             |  | 65863 A3                      |  |  |  |
|                    |  |                |  | chr                                   |  | M. SMYK                          |  | 8/21/90                                                                                             |  |                               |  |  |  |
|                    |  |                |  | appd                                  |  | M. SMYK                          |  | 8/21/90                                                                                             |  | type Product Customer Drawing |  |  |  |
| sheet index        |  | revision sheet |  |                                       |  |                                  |  |                                                                                                     |  |                               |  |  |  |

1

2

3

4

5

6

| PRODUCT NO<br>NOTE 12,13 | SIZE | LATCH<br>NOTE<br>8 | DIM B        | DIM D     | TERMINAL PLATING                            | STYLE | MISSING<br>PIN |
|--------------------------|------|--------------------|--------------|-----------|---------------------------------------------|-------|----------------|
| 65863-744                | 2x17 | LP                 | 1.600/ 40.64 | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 3, 5           |
| 65863-744S               | 2x17 | LP                 | 1.600/ 40.64 | .150/3.81 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 3, 5           |
| 65863-843                | 2x5  | N/A                | .400/ 10.16  | .120/3.05 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | A     |                |
| -844                     | 2x7  |                    | .600/ 15.24  |           |                                             | C     |                |
| -845                     | 2x10 |                    | .900/ 22.86  |           |                                             | D     |                |
| -846                     | 2x15 |                    | 1.400/ 35.56 |           |                                             |       |                |
| -847                     | 2x17 |                    | 1.600/ 40.64 |           |                                             |       |                |
| -848                     | 2X20 |                    | 1.900/ 48.26 |           |                                             |       |                |
| -849                     | 2X25 |                    | 2.400/ 60.96 |           |                                             |       |                |
| -850                     | 2x30 | N/A                | 2.900/ 73.66 |           |                                             | D     |                |
| -851                     | 2x5  | STD                | .400/ 10.16  |           |                                             | A     |                |
| -852                     | 2x7  |                    | .600/ 15.24  |           |                                             | C     | N/A            |
| -853                     | 2x10 |                    | .900/ 22.86  |           |                                             | D     |                |
| -854                     | 2x15 |                    | 1.400/ 35.56 |           |                                             |       |                |
| -855                     | 2x17 |                    | 1.600/ 40.64 |           |                                             |       |                |
| -856                     | 2X20 |                    | 1.900/ 48.26 |           |                                             |       |                |
| -857                     | 2X25 |                    | 2.400/ 60.96 |           |                                             |       |                |
| -858                     | 2x30 | STD                | 2.900/ 73.66 |           |                                             | D     |                |
| -859                     | 2x5  | L/P                | .400/ 10.16  |           |                                             | A     |                |
| -860                     | 2x7  |                    | .600/ 15.24  |           |                                             | C     |                |
| -861                     | 2x10 |                    | .900/ 22.86  |           |                                             | D     |                |
| -861S                    | 2x10 |                    | .900/ 22.86  |           |                                             | D     |                |
| -862                     | 2x15 |                    | 1.400/ 35.56 |           |                                             |       |                |
| -863                     | 2x17 |                    | 1.600/ 40.64 |           |                                             |       |                |
| -864                     | 2X20 |                    | 1.900/ 48.26 |           |                                             |       |                |
| -865                     | 2X25 |                    | 2.400/ 60.96 |           |                                             |       |                |
| 65863-866                | 2x30 | L/P                | 2.900/ 73.66 | .120/3.05 |                                             | D     |                |
| 65863-867S               | 2x12 | L/P                | 1.100/ 27.94 | .105/2.67 | 15u"/0.38u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 24             |
| 65863-868S               | 2x12 | L/P                | 1.100/ 27.94 | .105/2.67 | 30u"/0.76u MIN (NOTE 17) OVER 50u"/1.27u Ni | D     | 24             |

NOTE 18

NOTE 18

NOTE 18

NOTE 18

mat'l. code

surface  
ISO 1302 ✓

tolerance  
ISO 406  
ISO 1101

projection  
INCH/MM

product family  
QUICKIE

ltr  
BE

ecn no

dr

date

tolerances unless otherwise specified

angles  
0°±2°

linear  
XXX±.01/XXX±.03  
XXX±.005/XXX±.013  
XXXX±.0020/XXXX±.0051

dr  
M. CORNMAN 8/21/90

enr  
M. SMYK 8/21/90

chr  
M. SMYK 8/21/90

appd  
M. SMYK 8/21/90

sheet index

revision sheet

scale 1:1

FCI

dwg no  
65863

sheet 22 of 23

size  
A3

type  
Product Customer Drawing

form: A3

1

2

3

4

5

6

PDS: Rev :BE

STATUS: Released

Printed: Jun 19, 2014



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[65863-515LF](#)